

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643623

Luminaire Tested: ML5615LSVWFL9FS1E - 692W - 1500LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643623
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-108)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 692W - 1500LM - 3500K
Description: ML56 RR, MILKY OPTIC, 6" WHITE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1664.2 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643623

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692W - 1500LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643623

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692W - 1500LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89																			
2	104	97	92	87	101	95	91	86	92	88	84	89	86	83	86	83	81	79																			
3	96	88	81	76	94	87	80	76	84	79	74	81	77	73	79	75	72	70																			
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	63																			
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	50																			
7	73	61	54	49	72	61	53	48	59	53	48	58	52	48	57	51	47	46																			
8	69	57	49	44	67	56	49	44	55	48	44	54	48	44	53	47	43	42																			
9	64	52	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	59	48	42	37	47	41	37	47	41	37	46	40	37	35																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52364
5°	52113
10°	51435
15°	50574
20°	49494
25°	48233
30°	46520
35°	44343
40°	39417
45°	29825
50°	20332
55°	13983
60°	10460
65°	8743
70°	7902
75°	7307
80°	6219
85°	5158

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29825 cd/sqm



TEST NUMBER: P643623

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692W - 1500LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	5.4
10°-20°	250.9	15.1
20°-30°	366.3	22.0
30°-40°	409.1	24.6
40°-50°	297.7	17.9
50°-60°	136.9	8.2
60°-70°	68.2	4.1
70°-80°	36.0	2.2
80°-90°	9.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	706.9	42.5
0°-40°	1116.0	67.1
0°-60°	1550.6	93.2
0°-90°	1664.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1664.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	955	
5°	947	90
15°	891	251
25°	797	366
35°	663	409
45°	385	298
55°	146	137
65°	67	68
75°	34	36
85°	8	9
90°	0	



TEST NUMBER: P643623

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692W - 1500LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	955.2
2.5°	951.9
5°	947.0
7.5°	937.1
10°	924.0
12.5°	909.2
15°	891.1
17.5°	869.7
20°	848.4
22.5°	823.7
25°	797.4
27.5°	766.2
30°	734.9
32.5°	700.4
35°	662.6
37.5°	613.3
40°	550.8
42.5°	471.9
45°	384.7
47.5°	304.2
50°	238.4
52.5°	185.8
55°	146.3
57.5°	116.7
60°	95.4
62.5°	78.9
65°	67.4
67.5°	57.5
70°	49.3
72.5°	41.1
75°	34.5
77.5°	26.3
80°	19.7
82.5°	13.2
85°	8.2
87.5°	3.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)