

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643207

Luminaire Tested: ML5615LSVWFL759FS1E - 594WB - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643207
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-78)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 594WB - 900LM - 3000K
Description: ML56 RR, 75D TIR OPTIC, 5" WHITE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1131.5 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643207
CATALOG NUMBER: ML5615LSVWFL759FS1E - 594WB - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643207

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594WB - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83																			
3	99	92	86	81	97	90	85	80	87	83	79	85	81	78	83	79	77	75																			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68																			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62																			
6	82	72	65	60	81	71	64	60	69	64	59	68	63	59	67	62	58	57																			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																			
8	73	62	55	50	72	61	55	50	60	54	50	59	54	50	58	53	50	48																			
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	50	46	44																			
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58764
5°	59717
10°	61562
15°	64024
20°	64954
25°	61790
30°	55576
35°	44686
40°	30833
45°	18365
50°	11618
55°	8065
60°	6173
65°	4987
70°	4039
75°	3142
80°	1864
85°	906

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18365 cd/sqm



TEST NUMBER: P643207

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594WB - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.4	6.4
10°-20°	220.9	19.5
20°-30°	323.2	28.6
30°-40°	285.3	25.2
40°-50°	135.3	12.0
50°-60°	54.7	4.8
60°-70°	27.3	2.4
70°-80°	11.0	1.0
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	616.5	54.5
0°-40°	901.8	79.7
0°-60°	1091.8	96.5
0°-90°	1131.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1131.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	744	
5°	754	72
15°	783	221
25°	709	323
35°	464	285
45°	164	135
55°	59	55
65°	27	27
75°	10	11
85°	1	1
90°	0	



TEST NUMBER: P643207

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594WB - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	744.4
2.5°	747.4
5°	753.6
7.5°	760.8
10°	768.0
12.5°	776.2
15°	783.4
17.5°	784.5
20°	773.2
22.5°	746.4
25°	709.4
27.5°	665.2
30°	609.7
32.5°	541.8
35°	463.7
37.5°	381.4
40°	299.2
42.5°	225.2
45°	164.5
47.5°	123.4
50°	94.6
52.5°	73.0
55°	58.6
57.5°	47.3
60°	39.1
62.5°	32.9
65°	26.7
67.5°	22.6
70°	17.5
72.5°	13.4
75°	10.3
77.5°	7.2
80°	4.1
82.5°	2.1
85°	1.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)