

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643208

Luminaire Tested: ML5615LSVWFL759FS1E - 594WB - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643208
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-78)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 594WB - 900LM - 3500K
Description: ML56 RR, 75D TIR OPTIC, 5" WHITE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1162.2 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643208

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594WB - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643208

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594WB - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91															
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83				83															
3	99	92	86	81	97	90	85	80	87	83	79	85	81	78	83	79	77	75				75															
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68				68															
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62				62															
6	82	72	65	60	81	71	64	60	69	64	59	68	63	59	67	62	58	57				57															
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52				52															
8	73	62	55	50	72	61	55	50	60	54	50	59	54	50	58	53	50	48				48															
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	50	46	44				44															
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41				41															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60358
5°	61342
10°	63237
15°	65773
20°	66718
25°	63471
30°	57089
35°	45901
40°	31667
45°	18867
50°	11937
55°	8285
60°	6331
65°	5137
70°	4155
75°	3233
80°	1909
85°	996

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18867 cd/sqm



TEST NUMBER: P643208

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594WB - 900LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.4	6.4
10°-20°	226.9	19.5
20°-30°	332.0	28.6
30°-40°	293.1	25.2
40°-50°	139.0	12.0
50°-60°	56.1	4.8
60°-70°	28.0	2.4
70°-80°	11.3	1.0
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	633.3	54.5
0°-40°	926.4	79.7
0°-60°	1121.5	96.5
0°-90°	1162.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1162.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	765	
5°	774	74
15°	805	227
25°	729	332
35°	476	293
45°	169	139
55°	60	56
65°	28	28
75°	11	11
85°	1	1
90°	0	



TEST NUMBER: P643208

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594WB - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	764.6
2.5°	767.8
5°	774.1
7.5°	781.5
10°	788.9
12.5°	797.4
15°	804.8
17.5°	805.8
20°	794.2
22.5°	766.7
25°	728.7
27.5°	683.3
30°	626.3
32.5°	556.6
35°	476.3
37.5°	391.8
40°	307.3
42.5°	231.3
45°	169.0
47.5°	126.7
50°	97.2
52.5°	75.0
55°	60.2
57.5°	48.6
60°	40.1
62.5°	33.8
65°	27.5
67.5°	23.2
70°	18.0
72.5°	13.7
75°	10.6
77.5°	7.4
80°	4.2
82.5°	2.1
85°	1.1
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)