

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643639

Luminaire Tested: ML5615LSVWFL9FS1E - 693BB - 1500LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-110)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 693BB - 1500LM - 4000K
Description: ML56 RR, MILKY OPTIC, 6" BLACK BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1370.3 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.21
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643639

CATALOG NUMBER: ML5615LSVWFL9FS1E - 693BB - 1500LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P643639

CATALOG NUMBER: ML5615LSVWFL9FS1E - 693BB - 1500LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83																			
3	99	91	85	81	97	90	84	80	87	82	79	84	81	77	82	79	76	74																			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67																			
5	86	77	70	64	85	76	69	64	74	68	63	72	67	63	70	66	62	61																			
6	81	70	63	58	79	70	63	58	68	62	57	66	61	57	65	60	57	55																			
7	76	65	58	53	74	64	57	53	63	57	52	61	56	52	60	55	52	50																			
8	71	60	53	48	70	59	53	48	58	52	48	57	52	48	56	51	47	46																			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	43	42																			
10	63	52	45	41	62	51	45	40	50	44	40	50	44	40	49	44	40	39																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46701
5°	46588
10°	46342
15°	45840
20°	45265
25°	44476
30°	43184
35°	41164
40°	36046
45°	25483
50°	14771
55°	7598
60°	3487
65°	1141
70°	289
75°	381
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25483 cd/sqm



TEST NUMBER: P643639

CATALOG NUMBER: ML5615LSVWFL9FS1E - 693BB - 1500LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.4	5.9
10°-20°	227.8	16.6
20°-30°	337.9	24.7
30°-40°	378.8	27.6
40°-50°	254.6	18.6
50°-60°	77.7	5.7
60°-70°	11.4	0.8
70°-80°	1.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	646.1	47.2
0°-40°	1024.9	74.8
0°-60°	1357.2	99.0
0°-90°	1370.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1370.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	852	
5°	847	80
15°	808	228
25°	735	338
35°	615	379
45°	329	255
55°	80	78
65°	9	11
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P643639

CATALOG NUMBER: ML5615LSVWFL9FS1E - 693BB - 1500LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	851.9
2.5°	850.2
5°	846.6
7.5°	841.3
10°	832.5
12.5°	820.1
15°	807.7
17.5°	793.6
20°	775.9
22.5°	756.5
25°	735.3
27.5°	710.5
30°	682.2
32.5°	652.2
35°	615.1
37.5°	565.6
40°	503.7
42.5°	422.4
45°	328.7
47.5°	243.9
50°	173.2
52.5°	118.4
55°	79.5
57.5°	51.3
60°	31.8
62.5°	17.7
65°	8.8
67.5°	3.5
70°	1.8
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)