

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643217

Luminaire Tested: ML5615LSVWFL759FS1E - 596WB - 1500LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643217
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-81)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 596WB - 1500LM - 3000K
Description: ML56 RR, 75D TIR OPTIC, 5" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1751.2 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.1
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643217

CATALOG NUMBER: ML5615LSVWFL759FS1E - 596WB - 1500LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643217

CATALOG NUMBER: ML5615LSVWFL759FS1E - 596WB - 1500LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92																			
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	85	79	74	92	84	78	73	82	77	73	80	75	72	78	74	71	69																			
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63																			
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58																			
7	78	67	61	56	76	67	60	56	65	60	55	64	59	55	63	58	55	53																			
8	73	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	50	49																			
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45																			
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92077
5°	93443
10°	96447
15°	100294
20°	101884
25°	97275
30°	87799
35°	71544
40°	50124
45°	29830
50°	17685
55°	10790
60°	7326
65°	4184
70°	2216
75°	1952
80°	2182
85°	1449

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29830 cd/sqm



TEST NUMBER: P643217

CATALOG NUMBER: ML5615LSVWFL759FS1E - 596WB - 1500LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.4	6.5
10°-20°	346.1	19.8
20°-30°	508.5	29.0
30°-40°	456.4	26.1
40°-50°	218.2	12.5
50°-60°	75.1	4.3
60°-70°	24.2	1.4
70°-80°	7.0	0.4
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	968.0	55.3
0°-40°	1424.4	81.3
0°-60°	1717.7	98.1
0°-90°	1751.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1751.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1166	
5°	1179	113
15°	1227	346
25°	1117	509
35°	742	456
45°	267	218
55°	78	75
65°	22	24
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P643217

CATALOG NUMBER: ML5615LSVWFL759FS1E - 596WB - 1500LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1166.4
2.5°	1171.2
5°	1179.2
7.5°	1192.0
10°	1203.2
12.5°	1216.0
15°	1227.2
17.5°	1228.8
20°	1212.8
22.5°	1172.8
25°	1116.8
27.5°	1046.4
30°	963.2
32.5°	862.4
35°	742.4
37.5°	614.4
40°	486.4
42.5°	366.4
45°	267.2
47.5°	196.8
50°	144.0
52.5°	104.0
55°	78.4
57.5°	60.8
60°	46.4
62.5°	33.6
65°	22.4
67.5°	14.4
70°	9.6
72.5°	8.0
75°	6.4
77.5°	4.8
80°	4.8
82.5°	3.2
85°	1.6
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)