

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643688

Luminaire Tested: ML5615LSVWFL9FS1E - 693WB - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643688
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-109)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 693WB - 900LM - 3500K
Description: ML56 RR, MILKY OPTIC, 6" WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1056.6 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.22
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643688

CATALOG NUMBER: ML5615LSVWFL9FS1E - 693WB - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643688

CATALOG NUMBER: ML5615LSVWFL9FS1E - 693WB - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89																			
2	103	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	80	79																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70																			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62																			
5	83	73	65	59	81	71	64	59	70	63	58	68	62	58	66	61	57	56																			
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50																			
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45																			
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	48	43	39	38																			
10	60	48	41	37	59	48	41	36	47	41	36	46	40	36	45	40	36	34																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31867
5°	31818
10°	31596
15°	31192
20°	30768
25°	30244
30°	29441
35°	28295
40°	25340
45°	19335
50°	12980
55°	8889
60°	6600
65°	5487
70°	5081
75°	5147
80°	5020
85°	4655

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19335 cd/sqm



TEST NUMBER: P643688

CATALOG NUMBER: ML5615LSVWFL9FS1E - 693WB - 900LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.9	5.2
10°-20°	155.1	14.7
20°-30°	229.9	21.8
30°-40°	260.9	24.7
40°-50°	192.1	18.2
50°-60°	87.1	8.2
60°-70°	43.0	4.1
70°-80°	25.3	2.4
80°-90°	8.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	439.8	41.6
0°-40°	700.7	66.3
0°-60°	979.9	92.7
0°-90°	1056.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1056.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	581	
5°	578	55
15°	550	155
25°	500	230
35°	423	261
45°	249	192
55°	93	87
65°	42	43
75°	24	25
85°	7	9
90°	0	



TEST NUMBER: P643688

CATALOG NUMBER: ML5615LSVWFL9FS1E - 693WB - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	581.3
2.5°	581.3
5°	578.2
7.5°	573.9
10°	567.6
12.5°	559.1
15°	549.6
17.5°	540.1
20°	527.4
22.5°	514.8
25°	500.0
27.5°	483.0
30°	465.1
32.5°	445.0
35°	422.8
37.5°	392.1
40°	354.1
42.5°	304.4
45°	249.4
47.5°	196.6
50°	152.2
52.5°	118.4
55°	93.0
57.5°	74.0
60°	60.2
62.5°	49.7
65°	42.3
67.5°	35.9
70°	31.7
72.5°	27.5
75°	24.3
77.5°	20.1
80°	15.9
82.5°	12.7
85°	7.4
87.5°	3.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)