

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643304

Luminaire Tested: ML5615LSVWFL759FS1E - 693SNB - 1200LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-88)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 693SNB - 1200LM - 4000K
Description: ML56 RR, 75D TIR OPTIC, 6" SATIN NICKLE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1544.2 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643304
CATALOG NUMBER: ML5615LSVWFL759FS1E - 693SNB - 1200LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P643304

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693SNB - 1200LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			77
4	94	86	80	75	92	85	79	75	83	78	74	81	76	73	79	75	72	70			70
5	89	80	73	68	87	79	72	68	77	71	67	75	70	67	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	68	64	61	59			59
7	79	68	62	57	77	68	61	57	66	61	57	65	60	56	64	59	56	54			54
8	74	64	57	53	73	63	57	52	62	56	52	61	56	52	60	55	52	50			50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59003
5°	59944
10°	61756
15°	64024
20°	64639
25°	61364
30°	54831
35°	44102
40°	30278
45°	17630
50°	10064
55°	6050
60°	3311
65°	934
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17630 cd/sqm



TEST NUMBER: P643304

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693SNB - 1200LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.7	6.8
10°-20°	317.8	20.6
20°-30°	461.6	29.9
30°-40°	405.1	26.2
40°-50°	186.2	12.1
50°-60°	59.2	3.8
60°-70°	9.5	0.6
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	884.1	57.3
0°-40°	1289.2	83.5
0°-60°	1534.6	99.4
0°-90°	1544.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1544.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1076	
5°	1089	105
15°	1128	318
25°	1014	462
35°	659	405
45°	227	186
55°	63	59
65°	7	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P643304

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693SNB - 1200LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1076.3
2.5°	1080.7
5°	1089.3
7.5°	1100.8
10°	1109.4
12.5°	1119.5
15°	1128.1
17.5°	1126.7
20°	1108.0
22.5°	1067.7
25°	1014.5
27.5°	948.3
30°	866.2
32.5°	771.3
35°	659.0
37.5°	539.6
40°	423.1
42.5°	316.6
45°	227.4
47.5°	164.0
50°	118.0
52.5°	83.5
55°	63.3
57.5°	46.0
60°	30.2
62.5°	14.4
65°	7.2
67.5°	1.4
70°	1.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)