

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643325

Luminaire Tested: ML5615LSVWFL759FS1E - 693TBZB - 1500LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643325
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-89)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 693TBZB - 1500LM - 5000K
Description: ML56 RR, 75D TIR OPTIC, 6" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1870.9 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643325
CATALOG NUMBER: ML5615LSVWFL759FS1E - 693TBZB - 1500LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P643325

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693TBZB - 1500LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65	65	65	65
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59	59	59	59
7	79	69	62	57	77	68	62	57	67	61	57	65	60	56	64	60	56	55	55	55	55
8	74	64	57	53	73	63	57	53	62	56	52	61	56	52	60	55	52	50	50	50	50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47	47	47	47
10	67	56	49	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71606
5°	72854
10°	75077
15°	77952
20°	78681
25°	74623
30°	66776
35°	53538
40°	36604
45°	21266
50°	11778
55°	7101
60°	3684
65°	921
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21266 cd/sqm



TEST NUMBER: P643325

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693TBZB - 1500LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.2	6.8
10°-20°	386.7	20.7
20°-30°	561.9	30.0
30°-40°	492.4	26.3
40°-50°	223.4	11.9
50°-60°	69.2	3.7
60°-70°	10.1	0.5
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1075.8	57.5
0°-40°	1568.1	83.8
0°-60°	1860.8	99.5
0°-90°	1870.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1870.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1306	
5°	1324	127
15°	1374	387
25°	1234	562
35°	800	492
45°	274	223
55°	74	69
65°	7	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P643325

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693TBZB - 1500LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1306.2
2.5°	1313.3
5°	1323.9
7.5°	1336.3
10°	1348.7
12.5°	1361.1
15°	1373.5
17.5°	1371.7
20°	1348.7
22.5°	1300.9
25°	1233.7
27.5°	1154.0
30°	1054.9
32.5°	938.1
35°	800.0
37.5°	656.7
40°	511.5
42.5°	380.5
45°	274.3
47.5°	194.7
50°	138.1
52.5°	99.1
55°	74.3
57.5°	53.1
60°	33.6
62.5°	15.9
65°	7.1
67.5°	1.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)