

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643736

Luminaire Tested: ML5615LSWFL559FS1E - 591WB - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643736
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-47)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 591WB - 1200LM - 2700K
Description: ML56 RR, 55D TIR OPTIC, 5" DEADFRONT TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1426.6 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643736
CATALOG NUMBER: ML5615LSWFL559FS1E - 591WB - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P643736

CATALOG NUMBER: ML5615LSWFL559FS1E - 591WB - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93															
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85															
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78				78															
4	95	87	81	77	94	86	81	76	84	79	76	82	78	75	80	77	74	72				72															
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	67				67															
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62															
7	81	71	64	60	79	70	64	60	69	63	59	68	63	59	66	62	59	57				57															
8	76	66	60	56	75	66	60	55	65	59	55	64	59	55	63	58	55	53				53															
9	73	62	56	52	71	62	56	52	61	55	51	60	55	51	59	54	51	50				50															
10	69	59	53	48	68	58	52	48	57	52	48	57	52	48	56	51	48	47				47															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118443
5°	113483
10°	107605
15°	101650
20°	91744
25°	77616
30°	63142
35°	49331
40°	36861
45°	24270
50°	11335
55°	4693
60°	2795
65°	1644
70°	1177
75°	1159
80°	1137
85°	1177

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24270 cd/sqm



TEST NUMBER: P643736

CATALOG NUMBER: ML5615LSWFL559FS1E - 591WB - 1200LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.9	9.4
10°-20°	345.9	24.2
20°-30°	407.4	28.6
30°-40°	321.0	22.5
40°-50°	166.2	11.7
50°-60°	37.0	2.6
60°-70°	9.6	0.7
70°-80°	4.0	0.3
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	887.2	62.2
0°-40°	1208.1	84.7
0°-60°	1411.3	98.9
0°-90°	1426.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1426.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1500	
5°	1432	134
15°	1244	346
25°	891	407
35°	512	321
45°	217	166
55°	34	37
65°	9	10
75°	4	4
85°	1	2
90°	0	



TEST NUMBER: P643736

CATALOG NUMBER: ML5615LSWFL559FS1E - 591WB - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1500.4
2.5°	1481.4
5°	1432.1
7.5°	1384.1
10°	1342.4
12.5°	1295.6
15°	1243.8
17.5°	1174.2
20°	1092.1
22.5°	997.3
25°	891.1
27.5°	787.5
30°	692.7
32.5°	600.4
35°	511.9
37.5°	432.3
40°	357.7
42.5°	286.9
45°	217.4
47.5°	144.1
50°	92.3
52.5°	55.6
55°	34.1
57.5°	22.8
60°	17.7
62.5°	12.6
65°	8.8
67.5°	6.3
70°	5.1
72.5°	3.8
75°	3.8
77.5°	3.8
80°	2.5
82.5°	2.5
85°	1.3
87.5°	1.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)