

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643777

Luminaire Tested: ML5615LSWFL559FS1E - 592SC - 900LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P643777  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-48)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSWFL559FS1E - 592SC - 900LM - 3000K  
Description: ML56 RR, 55D TIR OPTIC, 5" SPECULAR CLEAR TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1159.2 lumens  
Efficiency: N/A  
Efficacy: 110.4 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.88  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P643777

CATALOG NUMBER: ML5615LSWFL559FS1E - 592SC - 900LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P643777

CATALOG NUMBER: ML5615LSWFL559FS1E - 592SC - 900LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80																			
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74																			
5	91	82	76	72	89	82	76	72	80	75	71	78	74	70	76	73	70	68																			
6	86	77	71	66	85	76	70	66	75	70	66	73	69	65	72	68	65	63																			
7	82	72	66	62	80	71	66	61	70	65	61	69	64	61	68	64	60	59																			
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55																			
9	74	64	58	53	73	63	57	53	62	57	53	61	56	53	60	56	53	51																			
10	70	60	54	50	69	60	54	50	59	54	50	58	53	50	57	53	50	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	101526
5°	97191
10°	91798
15°	87283
20°	77883
25°	64978
30°	52614
35°	40851
40°	29586
45°	17918
50°	5944
55°	2684
60°	805
65°	187
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17918 cd/sqm



TEST NUMBER: P643777

CATALOG NUMBER: ML5615LSWFL559FS1E - 592SC - 900LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.5	9.9
10°-20°	295.9	25.5
20°-30°	341.9	29.5
30°-40°	264.7	22.8
40°-50°	121.6	10.5
50°-60°	19.2	1.7
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	752.3	64.9
0°-40°	1016.9	87.7
0°-60°	1157.8	99.9
0°-90°	1159.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1159.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1286	
5°	1226	114
15°	1068	296
25°	746	342
35°	424	265
45°	160	122
55°	20	19
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P643777

CATALOG NUMBER: ML5615LSWFL559FS1E - 592SC - 900LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1286.1
2.5°	1268.7
5°	1226.5
7.5°	1182.2
10°	1145.2
12.5°	1111.2
15°	1068.0
17.5°	1004.2
20°	927.1
22.5°	840.6
25°	746.0
27.5°	657.5
30°	577.2
32.5°	500.1
35°	423.9
37.5°	351.9
40°	287.1
42.5°	225.3
45°	160.5
47.5°	88.5
50°	48.4
52.5°	29.8
55°	19.5
57.5°	11.3
60°	5.1
62.5°	2.1
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)