

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643351

Luminaire Tested: ML5615LSVWFL759FS1E - 694TBZB - 1500LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P643351  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-91)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSVWFL759FS1E - 694TBZB - 1500LM - 2700K  
Description: ML56 RR, 75D TIR OPTIC, 6" TUSCON BRONZE GIMBAL TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1707.3 lumens  
Efficiency: N/A  
Efficacy: 99.8 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 17.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P643351

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694TBZB - 1500LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P643351

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694TBZB - 1500LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91					91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83					83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75					75			
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68					68			
5	88	78	71	66	86	77	71	66	75	69	65	73	68	65	72	67	64	62					62			
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57					57			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	54	62	58	54	52					52			
8	73	62	55	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48					48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45					45			
10	65	54	48	44	64	54	48	43	53	47	43	52	47	43	51	47	43	42					42			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	62616
5°	63713
10°	66003
15°	68797
20°	69265
25°	65332
30°	57939
35°	46070
40°	31581
45°	18676
50°	11931
55°	8315
60°	6304
65°	5241
70°	4231
75°	3283
80°	1957
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18676 cd/sqm



TEST NUMBER: P643351

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694TBZB - 1500LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.4	6.5
10°-20°	340.9	20.0
20°-30°	491.5	28.8
30°-40°	424.0	24.8
40°-50°	198.7	11.6
50°-60°	81.4	4.8
60°-70°	40.7	2.4
70°-80°	16.6	1.0
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	943.8	55.3
0°-40°	1367.8	80.1
0°-60°	1647.9	96.5
0°-90°	1707.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1707.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1142	
5°	1158	111
15°	1212	341
25°	1080	491
35°	688	424
45°	241	199
55°	87	81
65°	40	41
75°	16	17
85°	2	2
90°	0	



TEST NUMBER: P643351  
CATALOG NUMBER: ML5615LSVWFL759FS1E - 694TBZB - 1500LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1142.2
2.5°	1146.9
5°	1157.8
7.5°	1170.2
10°	1185.7
12.5°	1199.7
15°	1212.2
17.5°	1210.6
20°	1187.3
22.5°	1142.2
25°	1080.1
27.5°	1005.5
30°	915.3
32.5°	808.1
35°	688.4
37.5°	562.6
40°	441.3
42.5°	329.5
45°	240.9
47.5°	181.8
50°	139.9
52.5°	108.8
55°	87.0
57.5°	71.5
60°	57.5
62.5°	48.2
65°	40.4
67.5°	34.2
70°	26.4
72.5°	20.2
75°	15.5
77.5°	10.9
80°	6.2
82.5°	3.1
85°	1.6
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)