

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643362

Luminaire Tested: ML5615LSVWFL759FS1E - 694WB - 1200LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-90)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 694WB - 1200LM - 3000K
Description: ML56 RR, 75D TIR OPTIC, 6" WHITE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1436.2 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643362
CATALOG NUMBER: ML5615LSVWFL759FS1E - 694WB - 1200LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643362

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694WB - 1200LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																			
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68																			
5	88	78	71	66	86	77	71	66	75	69	65	73	68	65	72	67	64	62																			
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57																			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	54	62	58	54	53																			
8	73	62	56	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48																			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45																			
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52890
5°	53736
10°	55666
15°	58082
20°	58338
25°	54898
30°	48729
35°	38809
40°	26428
45°	15730
50°	10089
55°	6958
60°	5416
65°	4384
70°	3542
75°	2754
80°	1642
85°	818

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15730 cd/sqm



TEST NUMBER: P643362

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694WB - 1200LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.0	6.5
10°-20°	287.5	20.0
20°-30°	413.3	28.8
30°-40°	356.5	24.8
40°-50°	166.7	11.6
50°-60°	68.4	4.8
60°-70°	34.2	2.4
70°-80°	13.9	1.0
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	794.8	55.3
0°-40°	1151.3	80.2
0°-60°	1386.3	96.5
0°-90°	1436.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1436.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	965	
5°	976	94
15°	1023	288
25°	908	413
35°	580	356
45°	203	167
55°	73	68
65°	34	34
75°	13	14
85°	1	2
90°	0	



TEST NUMBER: P643362

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694WB - 1200LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	964.8
2.5°	968.7
5°	976.5
7.5°	988.3
10°	1000.0
12.5°	1013.0
15°	1023.4
17.5°	1019.5
20°	1000.0
22.5°	960.9
25°	907.6
27.5°	845.2
30°	769.8
32.5°	680.1
35°	579.9
37.5°	472.0
40°	369.3
42.5°	275.7
45°	202.9
47.5°	152.1
50°	118.3
52.5°	91.0
55°	72.8
57.5°	59.8
60°	49.4
62.5°	40.3
65°	33.8
67.5°	28.6
70°	22.1
72.5°	16.9
75°	13.0
77.5°	9.1
80°	5.2
82.5°	2.6
85°	1.3
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)