

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643363

Luminaire Tested: ML5615LSVWFL759FS1E - 694WB - 1200LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P643363  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-90)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSVWFL759FS1E - 694WB - 1200LM - 3500K  
Description: ML56 RR, 75D TIR OPTIC, 6" WHITE GIMBAL TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1475.3 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P643363

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694WB - 1200LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P643363

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694WB - 1200LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																			
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68																			
5	88	78	71	66	86	77	71	66	75	69	65	73	68	65	72	67	64	62																			
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57																			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	54	62	58	54	53																			
8	73	62	56	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48																			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45																			
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	54332
5°	55200
10°	57180
15°	59660
20°	59925
25°	56392
30°	50052
35°	39866
40°	27144
45°	16157
50°	10371
55°	7149
60°	5570
65°	4501
70°	3638
75°	2838
80°	1673
85°	818

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16157 cd/sqm



TEST NUMBER: P643363

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694WB - 1200LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.6	6.5
10°-20°	295.3	20.0
20°-30°	424.5	28.8
30°-40°	366.2	24.8
40°-50°	171.2	11.6
50°-60°	70.3	4.8
60°-70°	35.1	2.4
70°-80°	14.3	1.0
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	816.4	55.3
0°-40°	1182.6	80.2
0°-60°	1424.1	96.5
0°-90°	1475.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1475.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	991	
5°	1003	97
15°	1051	295
25°	932	425
35°	596	366
45°	208	171
55°	75	70
65°	35	35
75°	13	14
85°	1	2
90°	0	



TEST NUMBER: P643363

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694WB - 1200LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	991.1
2.5°	995.1
5°	1003.1
7.5°	1015.2
10°	1027.2
12.5°	1040.5
15°	1051.2
17.5°	1047.2
20°	1027.2
22.5°	987.1
25°	932.3
27.5°	868.2
30°	790.7
32.5°	698.6
35°	595.7
37.5°	484.9
40°	379.3
42.5°	283.2
45°	208.4
47.5°	156.3
50°	121.6
52.5°	93.5
55°	74.8
57.5°	61.4
60°	50.8
62.5°	41.4
65°	34.7
67.5°	29.4
70°	22.7
72.5°	17.4
75°	13.4
77.5°	9.4
80°	5.3
82.5°	2.7
85°	1.3
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)