

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643372

Luminaire Tested: ML5615LSVWFL759FS1E - 694WB - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-90)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 694WB - 900LM - 3000K
Description: ML56 RR, 75D TIR OPTIC, 6" WHITE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1135.6 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643372

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694WB - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643372

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694WB - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																			
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68																			
5	88	78	71	66	86	77	71	66	75	69	65	73	68	65	72	67	64	62																			
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57																			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	54	62	58	54	53																			
8	73	62	56	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48																			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45																			
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	51	47	43	42																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41822
5°	42488
10°	44009
15°	45920
20°	46122
25°	43406
30°	38531
35°	30684
40°	20896
45°	12435
50°	7983
55°	5505
60°	4287
65°	3463
70°	2805
75°	2182
80°	1294
85°	629

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12435 cd/sqm



TEST NUMBER: P643372

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694WB - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.3	6.5
10°-20°	227.3	20.0
20°-30°	326.8	28.8
30°-40°	281.9	24.8
40°-50°	131.8	11.6
50°-60°	54.1	4.8
60°-70°	27.0	2.4
70°-80°	11.0	1.0
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.4	55.3
0°-40°	910.3	80.2
0°-60°	1096.2	96.5
0°-90°	1135.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1135.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	763	
5°	772	74
15°	809	227
25°	718	327
35°	458	282
45°	160	132
55°	58	54
65°	27	27
75°	10	11
85°	1	1
90°	0	



TEST NUMBER: P643372

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694WB - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	762.9
2.5°	766.0
5°	772.1
7.5°	781.4
10°	790.6
12.5°	800.9
15°	809.1
17.5°	806.1
20°	790.6
22.5°	759.8
25°	717.6
27.5°	668.3
30°	608.7
32.5°	537.7
35°	458.5
37.5°	373.2
40°	292.0
42.5°	218.0
45°	160.4
47.5°	120.3
50°	93.6
52.5°	72.0
55°	57.6
57.5°	47.3
60°	39.1
62.5°	31.9
65°	26.7
67.5°	22.6
70°	17.5
72.5°	13.4
75°	10.3
77.5°	7.2
80°	4.1
82.5°	2.1
85°	1.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)