

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643857

Luminaire Tested: ML5615LSWFL559FS1E - 594SNB - 1200LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643857
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-56)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 594SNB - 1200LM - 3000K
Description: ML56 RR, 55D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1481.7 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643857
CATALOG NUMBER: ML5615LSWFL559FS1E - 594SNB - 1200LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643857

CATALOG NUMBER: ML5615LSWFL559FS1E - 594SNB - 1200LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92																											
2	107	101	97	93	105	100	96	92	96	93	90	93	91	88	91	88	87	85																											
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																											
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																											
5	90	81	74	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																											
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63	61																											
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																											
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53																											
9	72	62	56	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49																											
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	47	46																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121806
5°	116700
10°	110755
15°	104731
20°	94760
25°	80003
30°	64865
35°	50401
40°	37273
45°	24404
50°	11667
55°	6262
60°	4105
65°	3400
70°	3001
75°	1983
80°	1182
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24404 cd/sqm



TEST NUMBER: P643857

CATALOG NUMBER: ML5615LSWFL559FS1E - 594\$NB - 1200LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.7	9.3
10°-20°	356.6	24.1
20°-30°	420.3	28.4
30°-40°	327.6	22.1
40°-50°	167.5	11.3
50°-60°	45.4	3.1
60°-70°	18.6	1.3
70°-80°	7.2	0.5
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	914.7	61.7
0°-40°	1242.3	83.8
0°-60°	1455.2	98.2
0°-90°	1481.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1481.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1543	
5°	1473	138
15°	1282	357
25°	918	420
35°	523	328
45°	219	168
55°	46	45
65°	18	19
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P643857

CATALOG NUMBER: ML5615LSWFL559FS1E - 594\$NB - 1200LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1543.0
2.5°	1523.5
5°	1472.7
7.5°	1423.3
10°	1381.7
12.5°	1336.1
15°	1281.5
17.5°	1211.2
20°	1128.0
22.5°	1030.4
25°	918.5
27.5°	813.1
30°	711.6
32.5°	615.4
35°	523.0
37.5°	438.4
40°	361.7
42.5°	287.5
45°	218.6
47.5°	145.7
50°	95.0
52.5°	65.0
55°	45.5
57.5°	33.8
60°	26.0
62.5°	22.1
65°	18.2
67.5°	15.6
70°	13.0
72.5°	9.1
75°	6.5
77.5°	3.9
80°	2.6
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)