

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643398

Luminaire Tested: ML5615LSVWFL9FS1E - 591WB - 1500LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643398
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-93)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 591WB - 1500LM - 3500K
Description: ML56 RR, MILKY OPTIC, 5" DEADFRONT TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1677.4 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643398

CATALOG NUMBER: ML5615LSVWFL9FS1E - 591WB - 1500LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643398

CATALOG NUMBER: ML5615LSVWFL9FS1E - 591WB - 1500LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68																			
4	89	78	71	65	87	77	70	65	75	69	64	73	67	63	71	66	62	61																			
5	82	71	64	58	81	70	63	58	68	62	57	66	61	56	65	60	56	54																			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49																			
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44																			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																			
9	63	51	44	39	62	50	43	38	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69602
5°	69480
10°	69097
15°	68576
20°	67727
25°	66502
30°	64810
35°	61715
40°	55328
45°	44176
50°	32471
55°	23727
60°	18141
65°	15037
70°	13641
75°	13512
80°	14184
85°	14854

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 44176 cd/sqm



TEST NUMBER: P643398

CATALOG NUMBER: ML5615LSVWFL9FS1E - 591WB - 1500LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.2	5.0
10°-20°	236.3	14.1
20°-30°	351.4	20.9
30°-40°	396.3	23.6
40°-50°	304.8	18.2
50°-60°	158.8	9.5
60°-70°	82.0	4.9
70°-80°	47.0	2.8
80°-90°	17.6	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	670.9	40.0
0°-40°	1067.2	63.6
0°-60°	1530.7	91.3
0°-90°	1677.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1677.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	882	
5°	877	83
15°	839	236
25°	764	351
35°	640	396
45°	396	305
55°	172	159
65°	80	82
75°	44	47
85°	16	18
90°	0	



TEST NUMBER: P643398

CATALOG NUMBER: ML5615LSVWFL9FS1E - 591WB - 1500LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	881.7
2.5°	880.1
5°	876.8
7.5°	870.3
10°	862.0
12.5°	850.6
15°	839.1
17.5°	822.6
20°	806.2
22.5°	786.5
25°	763.5
27.5°	738.9
30°	711.0
32.5°	678.1
35°	640.4
37.5°	594.4
40°	536.9
42.5°	469.6
45°	395.7
47.5°	323.5
50°	264.4
52.5°	211.8
55°	172.4
57.5°	139.6
60°	114.9
62.5°	95.2
65°	80.5
67.5°	69.0
70°	59.1
72.5°	50.9
75°	44.3
77.5°	37.8
80°	31.2
82.5°	24.6
85°	16.4
87.5°	8.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)