

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643418

Luminaire Tested: ML5615LSVWFL9FS1E - 592H - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643418
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-95)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 592H - 900LM - 3500K
Description: ML56 RR, MILKY OPTIC, 5" HAZE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1035.9 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.97
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643418
CATALOG NUMBER: ML5615LSVWFL9FS1E - 592H - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643418

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592H - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92															
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84															
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77															
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71				71															
5	89	80	73	68	87	79	73	68	77	72	68	75	71	67	74	70	66	65				65															
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	64	61	60				60															
7	79	69	62	58	78	68	62	57	67	61	57	66	61	57	64	60	56	55				55															
8	75	64	58	53	73	64	57	53	63	57	53	61	56	53	60	56	52	51				51															
9	71	60	54	49	70	60	53	49	59	53	49	58	53	49	57	52	49	47				47															
10	67	56	50	46	66	56	50	46	55	50	46	54	49	46	54	49	45	44				44															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76320
5°	74686
10°	70291
15°	64506
20°	58939
25°	53742
30°	48247
35°	40832
40°	29833
45°	18633
50°	10635
55°	5822
60°	3000
65°	1382
70°	739
75°	336
80°	500
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18633 cd/sqm



TEST NUMBER: P643418

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592H - 900LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	8.5
10°-20°	221.2	21.4
20°-30°	283.0	27.3
30°-40°	259.5	25.0
40°-50°	133.5	12.9
50°-60°	40.7	3.9
60°-70°	8.4	0.8
70°-80°	1.7	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	592.0	57.2
0°-40°	851.5	82.2
0°-60°	1025.6	99.0
0°-90°	1035.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1035.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	967	
5°	942	88
15°	789	221
25°	617	283
35°	424	259
45°	167	133
55°	42	41
65°	7	8
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P643418

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592H - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	966.8
2.5°	960.4
5°	942.5
7.5°	913.9
10°	876.9
12.5°	833.6
15°	789.3
17.5°	744.9
20°	701.6
22.5°	659.3
25°	617.0
27.5°	573.7
30°	529.3
32.5°	479.7
35°	423.7
37.5°	358.2
40°	289.5
42.5°	224.0
45°	166.9
47.5°	121.5
50°	86.6
52.5°	60.2
55°	42.3
57.5°	28.5
60°	19.0
62.5°	11.6
65°	7.4
67.5°	4.2
70°	3.2
72.5°	2.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)