

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643885

Luminaire Tested: ML5615LSWFL559FS1E - 594TBZB - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 594TBZB - 900LM - 5000K
Description: ML56 RR, 55D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1293.0 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643885
CATALOG NUMBER: ML5615LSWFL559FS1E - 594TBZB - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P643885
 CATALOG NUMBER: ML5615LSWFL559FS1E - 594TBZB - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92																			
2	107	101	97	93	105	100	96	92	96	93	90	93	91	88	91	88	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53																			
9	72	62	56	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49																			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106318
5°	101763
10°	96559
15°	91288
20°	82655
25°	69951
30°	56715
35°	44070
40°	32471
45°	21334
50°	10341
55°	5478
60°	3584
65°	2970
70°	2354
75°	1739
80°	1046
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21334 cd/sqm



TEST NUMBER: P643885

CATALOG NUMBER: ML5615LSWFL559FS1E - 594TBZB - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.1	9.3
10°-20°	311.0	24.0
20°-30°	367.0	28.4
30°-40°	286.0	22.1
40°-50°	146.3	11.3
50°-60°	39.8	3.1
60°-70°	16.1	1.2
70°-80°	6.1	0.5
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	798.1	61.7
0°-40°	1084.1	83.8
0°-60°	1270.2	98.2
0°-90°	1293.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1293.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1347	
5°	1284	120
15°	1117	311
25°	803	367
35°	457	286
45°	191	146
55°	40	40
65°	16	16
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P643885

CATALOG NUMBER: ML5615LSWFL559FS1E - 594TBZB - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1346.8
2.5°	1329.7
5°	1284.2
7.5°	1242.1
10°	1204.6
12.5°	1164.8
15°	1117.0
17.5°	1056.7
20°	983.9
22.5°	898.6
25°	803.1
27.5°	709.8
30°	622.2
32.5°	536.9
35°	457.3
37.5°	382.2
40°	315.1
42.5°	251.4
45°	191.1
47.5°	126.3
50°	84.2
52.5°	56.9
55°	39.8
57.5°	29.6
60°	22.7
62.5°	19.3
65°	15.9
67.5°	13.6
70°	10.2
72.5°	8.0
75°	5.7
77.5°	3.4
80°	2.3
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)