

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643433

Luminaire Tested: ML5615LSVWFL9FS1E - 592SC - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-94)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 592SC - 900LM - 3500K
Description: ML56 RR, MILKY OPTIC, 5" SPECULAR CLEAR TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1068.2 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.95
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643433
CATALOG NUMBER: ML5615LSVWFL9FS1E - 592SC - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643433

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592SC - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	79	78																			
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71																			
5	90	81	74	69	88	80	74	69	78	73	69	76	71	68	74	70	67	66																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61																			
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	65	61	58	56																			
8	76	65	59	54	74	65	59	54	64	58	54	63	57	54	62	57	54	52																			
9	72	61	55	51	70	61	55	50	60	54	50	59	54	50	58	53	50	48																			
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82067
5°	82713
10°	79606
15°	71060
20°	62123
25°	54752
30°	48338
35°	41034
40°	30266
45°	18755
50°	10120
55°	5092
60°	2337
65°	990
70°	485
75°	336
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18755 cd/sqm



TEST NUMBER: P643433

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592SC - 900LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	9.2
10°-20°	242.6	22.7
20°-30°	289.0	27.1
30°-40°	260.9	24.4
40°-50°	134.2	12.6
50°-60°	36.4	3.4
60°-70°	6.0	0.6
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	629.6	58.9
0°-40°	890.6	83.4
0°-60°	1061.1	99.3
0°-90°	1068.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1068.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1040	
5°	1044	98
15°	870	243
25°	629	289
35°	426	261
45°	168	134
55°	37	36
65°	5	6
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P643433

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592SC - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1039.6
2.5°	1041.7
5°	1043.8
7.5°	1030.1
10°	993.1
12.5°	937.1
15°	869.5
17.5°	802.9
20°	739.5
22.5°	680.4
25°	628.6
27.5°	577.9
30°	530.3
32.5°	479.6
35°	425.8
37.5°	362.4
40°	293.7
42.5°	228.2
45°	168.0
47.5°	120.4
50°	82.4
52.5°	54.9
55°	37.0
57.5°	24.3
60°	14.8
62.5°	8.5
65°	5.3
67.5°	2.1
70°	2.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)