

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643436

Luminaire Tested: ML5615LSVWFL9FS1E - 592W - 1200LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P643436  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-96)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSVWFL9FS1E - 592W - 1200LM - 2700K  
Description: ML56 RR, MILKY OPTIC, 5" WHITE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1233.0 lumens  
Efficiency: N/A  
Efficacy: 92.0 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P643436

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592W - 1200LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P643436

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592W - 1200LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70																			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	62	58	66	61	58	56																			
6	78	67	59	54	76	66	59	53	64	58	53	63	57	53	61	56	52	50																			
7	73	61	54	49	72	61	54	48	59	53	48	58	52	48	57	52	48	46																			
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42																			
9	65	53	46	41	63	52	45	41	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	39997
5°	39869
10°	39417
15°	38752
20°	37990
25°	37169
30°	35695
35°	32237
40°	25698
45°	18234
50°	13262
55°	10274
60°	8870
65°	8198
70°	7694
75°	7223
80°	6377
85°	4780

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18234 cd/sqm



TEST NUMBER: P643436

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592W - 1200LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.6	5.6
10°-20°	192.4	15.6
20°-30°	281.9	22.9
30°-40°	295.3	24.0
40°-50°	186.7	15.1
50°-60°	99.9	8.1
60°-70°	62.8	5.1
70°-80°	36.0	2.9
80°-90°	9.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	542.9	44.0
0°-40°	838.2	68.0
0°-60°	1124.8	91.2
0°-90°	1233.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1233.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	730	
5°	724	69
15°	683	192
25°	614	282
35°	482	295
45°	235	187
55°	108	100
65°	63	63
75°	34	36
85°	8	9
90°	0	



TEST NUMBER: P643436

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592W - 1200LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	729.6
2.5°	728.3
5°	724.5
7.5°	716.9
10°	708.1
12.5°	696.7
15°	682.8
17.5°	667.6
20°	651.2
22.5°	632.2
25°	614.5
27.5°	591.7
30°	563.9
32.5°	528.5
35°	481.7
37.5°	424.8
40°	359.1
42.5°	293.3
45°	235.2
47.5°	189.7
50°	155.5
52.5°	129.0
55°	107.5
57.5°	93.6
60°	80.9
62.5°	70.8
65°	63.2
67.5°	55.6
70°	48.0
72.5°	41.7
75°	34.1
77.5°	26.6
80°	20.2
82.5°	13.9
85°	7.6
87.5°	2.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)