

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643441

Luminaire Tested: ML5615LSVWFL9FS1E - 592W - 1500LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643441
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-96)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 592W - 1500LM - 2700K
Description: ML56 RR, MILKY OPTIC, 5" WHITE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1515.9 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643441

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592W - 1500LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P643441

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592W - 1500LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70																			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	62	58	66	61	58	56																			
6	78	67	59	54	76	66	59	53	64	58	53	63	57	53	61	56	52	50																			
7	73	61	54	49	72	61	54	48	59	53	48	58	52	48	57	52	48	46																			
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42																			
9	65	53	45	41	63	52	45	41	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49168
5°	49015
10°	48457
15°	47639
20°	46706
25°	45698
30°	43886
35°	39639
40°	31595
45°	22413
50°	16307
55°	12626
60°	10909
65°	10079
70°	9473
75°	8896
80°	7861
85°	5850

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22413 cd/sqm



TEST NUMBER: P643441

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592W - 1500LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.3	5.6
10°-20°	236.5	15.6
20°-30°	346.6	22.9
30°-40°	363.1	24.0
40°-50°	229.5	15.1
50°-60°	122.8	8.1
60°-70°	77.3	5.1
70°-80°	44.3	2.9
80°-90°	11.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	667.5	44.0
0°-40°	1030.6	68.0
0°-60°	1382.9	91.2
0°-90°	1515.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1515.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	897	
5°	891	84
15°	839	237
25°	756	347
35°	592	363
45°	289	230
55°	132	123
65°	78	77
75°	42	44
85°	9	11
90°	0	



TEST NUMBER: P643441

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592W - 1500LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	896.9
2.5°	895.4
5°	890.7
7.5°	881.4
10°	870.5
12.5°	856.5
15°	839.4
17.5°	820.8
20°	800.6
22.5°	777.2
25°	755.5
27.5°	727.5
30°	693.3
32.5°	649.8
35°	592.3
37.5°	522.3
40°	441.5
42.5°	360.6
45°	289.1
47.5°	233.2
50°	191.2
52.5°	158.6
55°	132.1
57.5°	115.0
60°	99.5
62.5°	87.1
65°	77.7
67.5°	68.4
70°	59.1
72.5°	51.3
75°	42.0
77.5°	32.6
80°	24.9
82.5°	17.1
85°	9.3
87.5°	3.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)