

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643473

Luminaire Tested: ML5615LSVWFL9FS1E - 593SNB - 1500LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643473
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-99)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 593SNB - 1500LM - 3500K
Description: ML56 RR, MILKY OPTIC, 5" SATIN NICKLE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1377.7 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.14
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643473

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593SNB - 1500LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643473

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593SNB - 1500LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82																			
3	99	91	85	81	97	90	84	80	87	82	79	84	81	77	82	79	76	74																			
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67																			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61																			
6	81	71	64	59	80	70	63	58	68	62	58	67	62	58	65	61	57	55																			
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51																			
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																			
9	68	56	50	45	66	56	49	45	55	49	45	54	48	44	53	48	44	43																			
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71449
5°	71199
10°	70708
15°	70072
20°	69129
25°	67669
30°	64983
35°	58255
40°	45363
45°	30444
50°	18765
55°	11299
60°	6742
65°	3997
70°	2285
75°	2013
80°	1500
85°	1449

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30444 cd/sqm



TEST NUMBER: P643473

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593SNB - 1500LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.3	6.2
10°-20°	241.6	17.5
20°-30°	356.7	25.9
30°-40°	370.2	26.9
40°-50°	214.9	15.6
50°-60°	78.1	5.7
60°-70°	22.7	1.6
70°-80°	6.9	0.5
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	683.6	49.6
0°-40°	1053.8	76.5
0°-60°	1346.8	97.8
0°-90°	1377.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1377.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	905	
5°	898	85
15°	857	242
25°	777	357
35°	604	370
45°	273	215
55°	82	78
65°	21	23
75°	7	7
85°	2	1
90°	0	



TEST NUMBER: P643473

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593SNB - 1500LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	905.1
2.5°	903.4
5°	898.5
7.5°	891.9
10°	882.1
12.5°	870.6
15°	857.4
17.5°	841.0
20°	822.9
22.5°	801.6
25°	776.9
27.5°	749.0
30°	712.9
32.5°	666.9
35°	604.5
37.5°	530.5
40°	440.2
42.5°	351.5
45°	272.7
47.5°	205.3
50°	152.8
52.5°	113.3
55°	82.1
57.5°	59.1
60°	42.7
62.5°	29.6
65°	21.4
67.5°	14.8
70°	9.9
72.5°	8.2
75°	6.6
77.5°	4.9
80°	3.3
82.5°	1.6
85°	1.6
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)