

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643941

Luminaire Tested: ML5615LSWFL559FS1E - 692H - 900LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643941
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-61)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 692H - 900LM - 2700K
Description: ML56 RR, 55D TIR OPTIC, 6" HAZE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1127.0 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643941
CATALOG NUMBER: ML5615LSWFL559FS1E - 692H - 900LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P643941

CATALOG NUMBER: ML5615LSWFL559FS1E - 692H - 900LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86																			
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79																			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73																			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67																			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62																			
7	81	71	65	61	80	71	65	60	69	64	60	68	63	60	67	63	59	58																			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54																			
9	73	63	57	52	72	62	56	52	61	56	52	60	56	52	60	55	52	50																			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66256
5°	63537
10°	59980
15°	56442
20°	51011
25°	43333
30°	35341
35°	27586
40°	20403
45°	13265
50°	5458
55°	2103
60°	987
65°	259
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13265 cd/sqm



TEST NUMBER: P643941

CATALOG NUMBER: ML5615LSWFL559FS1E - 692H - 900LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.8	9.6
10°-20°	276.8	24.6
20°-30°	327.5	29.1
30°-40°	257.9	22.9
40°-50°	129.8	11.5
50°-60°	23.9	2.1
60°-70°	2.9	0.3
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	712.1	63.2
0°-40°	969.9	86.1
0°-60°	1123.7	99.7
0°-90°	1127.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1127.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1209	
5°	1155	108
15°	994	277
25°	716	327
35°	412	258
45°	171	130
55°	22	24
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P643941

CATALOG NUMBER: ML5615LSWFL559FS1E - 692H - 900LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1208.6
2.5°	1194.6
5°	1154.6
7.5°	1113.5
10°	1077.5
12.5°	1038.5
15°	994.5
17.5°	938.5
20°	874.4
22.5°	799.4
25°	716.4
27.5°	635.3
30°	558.3
32.5°	484.2
35°	412.2
37.5°	345.2
40°	285.1
42.5°	226.1
45°	171.1
47.5°	111.1
50°	64.0
52.5°	35.0
55°	22.0
57.5°	15.0
60°	9.0
62.5°	4.0
65°	2.0
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)