

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643974

Luminaire Tested: ML5615LSWFL559FS1E - 692W - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643974
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-62)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 692W - 900LM - 4000K
Description: ML56 RR, 55D TIR OPTIC, 6" WHITE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1284.6 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643974
CATALOG NUMBER: ML5615LSWFL559FS1E - 692W - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P643974

CATALOG NUMBER: ML5615LSWFL559FS1E - 692W - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85																
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79			79																
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72																
5	90	81	75	71	89	80	75	70	79	74	70	77	72	69	75	71	68	67			67																
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62			62																
7	81	71	65	60	79	70	64	60	69	63	60	68	63	59	67	62	59	57			57																
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			53																
9	73	62	56	52	71	62	56	52	61	55	52	60	55	51	59	55	51	50			50																
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47			47																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74078
5°	71049
10°	67250
15°	63468
20°	57481
25°	48946
30°	40000
35°	31260
40°	23179
45°	15157
50°	6490
55°	2714
60°	1491
65°	882
70°	721
75°	720
80°	726
85°	692

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15157 cd/sqm



TEST NUMBER: P643974

CATALOG NUMBER: ML5615LSWFL559FS1E - 692W - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.7	9.4
10°-20°	311.3	24.2
20°-30°	369.6	28.8
30°-40°	292.6	22.8
40°-50°	148.7	11.6
50°-60°	30.2	2.4
60°-70°	7.2	0.6
70°-80°	3.3	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	801.6	62.4
0°-40°	1094.2	85.2
0°-60°	1273.1	99.1
0°-90°	1284.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1284.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1351	
5°	1291	121
15°	1118	311
25°	809	370
35°	467	293
45°	196	149
55°	28	30
65°	7	7
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P643974

CATALOG NUMBER: ML5615LSWFL559FS1E - 692W - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1351.3
2.5°	1335.4
5°	1291.1
7.5°	1247.9
10°	1208.1
12.5°	1167.2
15°	1118.3
17.5°	1055.8
20°	985.3
22.5°	901.2
25°	809.2
27.5°	717.1
30°	631.9
32.5°	548.9
35°	467.1
37.5°	393.2
40°	323.9
42.5°	258.0
45°	195.5
47.5°	128.4
50°	76.1
52.5°	43.2
55°	28.4
57.5°	20.5
60°	13.6
62.5°	9.1
65°	6.8
67.5°	4.5
70°	4.5
72.5°	3.4
75°	3.4
77.5°	2.3
80°	2.3
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)