

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643976

Luminaire Tested: ML5615LSWFL559FS1E - 693BB - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-64)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 693BB - 1200LM - 2700K
Description: ML56 RR, 55D TIR OPTIC, 6" BLACK BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1397.5 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643976

CATALOG NUMBER: ML5615LSWFL559FS1E - 693BB - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P643976

CATALOG NUMBER: ML5615LSWFL559FS1E - 693BB - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			93																
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			86																
3	101	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79			79																
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73			73																
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			67																
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62			62																
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58			58																
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54			54																
9	73	63	57	53	72	62	56	52	61	56	52	61	56	52	60	55	52	50			50																
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			47																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81726
5°	78274
10°	74247
15°	70029
20°	63344
25°	53967
30°	44057
35°	34298
40°	25355
45°	16482
50°	6797
55°	2542
60°	1107
65°	169
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16482 cd/sqm



TEST NUMBER: P643976

CATALOG NUMBER: ML5615LSWFL559FS1E - 693BB - 1200LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.1	9.5
10°-20°	343.5	24.6
20°-30°	407.4	29.2
30°-40°	321.1	23.0
40°-50°	161.3	11.5
50°-60°	28.6	2.0
60°-70°	2.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	884.1	63.3
0°-40°	1205.2	86.2
0°-60°	1395.1	99.8
0°-90°	1397.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1397.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1491	
5°	1422	133
15°	1234	344
25°	892	407
35°	512	321
45°	213	161
55°	27	29
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P643976

CATALOG NUMBER: ML5615LSWFL559FS1E - 693BB - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1490.8
2.5°	1473.0
5°	1422.4
7.5°	1376.9
10°	1333.8
12.5°	1288.3
15°	1233.9
17.5°	1165.5
20°	1085.8
22.5°	993.4
25°	892.2
27.5°	790.9
30°	696.0
32.5°	603.6
35°	512.5
37.5°	430.3
40°	354.3
42.5°	280.9
45°	212.6
47.5°	137.9
50°	79.7
52.5°	41.8
55°	26.6
57.5°	16.5
60°	10.1
62.5°	3.8
65°	1.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)