

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643546

Luminaire Tested: ML5615LSVWFL9FS1E - 594WB - 1500LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P643546  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-101)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSVWFL9FS1E - 594WB - 1500LM - 2700K  
Description: ML56 RR, MILKY OPTIC, 5" WHITE GIMBAL TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1705.8 lumens  
Efficiency: N/A  
Efficacy: 99.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.28  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 17.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P643546

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594WB - 1500LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P643546

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594WB - 1500LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	94	88	82	99	92	86	82	88	84	80	85	81	78	82	79	76	74																			
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	70	66	64																			
4	86	75	67	60	84	73	66	60	71	64	59	69	63	58	67	62	58	56																			
5	79	67	59	53	77	66	58	53	64	57	52	62	56	51	60	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																			
7	68	56	47	42	67	55	47	41	53	46	41	52	46	41	51	45	41	39																			
8	64	51	43	37	62	50	43	37	49	42	37	48	41	37	47	41	37	35																			
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31																			
10	56	43	36	31	55	43	36	31	42	35	31	41	35	31	40	34	30	29																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	58914
5°	58893
10°	58700
15°	58328
20°	57864
25°	56877
30°	55412
35°	53340
40°	50309
45°	46520
50°	41817
55°	36802
60°	31182
65°	26431
70°	22250
75°	18971
80°	16957
85°	15488

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 46520 cd/sqm



TEST NUMBER: P643546

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594WB - 1500LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.6	4.1
10°-20°	201.5	11.8
20°-30°	300.5	17.6
30°-40°	344.7	20.2
40°-50°	320.1	18.8
50°-60°	239.1	14.0
60°-70°	141.5	8.3
70°-80°	68.0	4.0
80°-90°	19.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	572.5	33.6
0°-40°	917.2	53.8
0°-60°	1476.3	86.5
0°-90°	1705.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1705.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	746	
5°	743	71
15°	714	201
25°	653	300
35°	554	345
45°	417	320
55°	267	239
65°	142	142
75°	62	68
85°	17	20
90°	0	



TEST NUMBER: P643546

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594WB - 1500LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	746.3
2.5°	746.3
5°	743.2
7.5°	738.5
10°	732.3
12.5°	724.5
15°	713.7
17.5°	702.8
20°	688.8
22.5°	671.7
25°	653.0
27.5°	632.8
30°	607.9
32.5°	581.5
35°	553.5
37.5°	520.9
40°	488.2
42.5°	452.4
45°	416.7
47.5°	377.8
50°	340.5
52.5°	303.2
55°	267.4
57.5°	231.7
60°	197.5
62.5°	167.9
65°	141.5
67.5°	116.6
70°	96.4
72.5°	79.3
75°	62.2
77.5°	49.8
80°	37.3
82.5°	26.4
85°	17.1
87.5°	10.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)