

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P644010

Luminaire Tested: ML5615LSWFL559FS1E - 693TBZB - 1200LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P644010  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-66)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSWFL559FS1E - 693TBZB - 1200LM - 5000K  
Description: ML56 RR, 55D TIR OPTIC, 6" TUSCON BRONZE BAFFLE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1595.1 lumens  
Efficiency: N/A  
Efficacy: 119.0 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P644010

CATALOG NUMBER: ML5615LSWFL559FS1E - 693TBZB - 1200LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P644010

CATALOG NUMBER: ML5615LSWFL559FS1E - 693TBZB - 1200LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62			
7	81	71	65	61	80	71	65	60	69	64	60	68	63	60	67	63	59	58			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	56	52	60	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	93046
5°	89203
10°	84551
15°	79671
20°	72165
25°	61425
30°	50261
35°	39177
40°	29026
45°	18847
50°	7855
55°	2886
60°	1261
65°	376
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18847 cd/sqm



TEST NUMBER: P644010

CATALOG NUMBER: ML5615LSWFL559FS1E - 693TBZB - 1200LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.6	9.5
10°-20°	391.0	24.5
20°-30°	464.2	29.1
30°-40°	366.6	23.0
40°-50°	184.6	11.6
50°-60°	33.3	2.1
60°-70°	3.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1006.8	63.1
0°-40°	1373.4	86.1
0°-60°	1591.3	99.8
0°-90°	1595.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1595.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1697	
5°	1621	152
15°	1404	391
25°	1016	464
35°	585	367
45°	243	185
55°	30	33
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P644010

CATALOG NUMBER: ML5615LSWFL559FS1E - 693TBZB - 1200LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1697.3
2.5°	1677.1
5°	1621.0
7.5°	1567.8
10°	1518.9
12.5°	1464.3
15°	1403.8
17.5°	1327.6
20°	1237.0
22.5°	1133.4
25°	1015.5
27.5°	900.4
30°	794.0
32.5°	687.5
35°	585.4
37.5°	491.9
40°	405.6
42.5°	322.2
45°	243.1
47.5°	156.8
50°	92.1
52.5°	48.9
55°	30.2
57.5°	20.1
60°	11.5
62.5°	5.8
65°	2.9
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)