

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P644032

Luminaire Tested: ML5615LSWFL559FS1E - 693WB - 900LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P644032  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-63)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSWFL559FS1E - 693WB - 900LM - 3000K  
Description: ML56 RR, 55D TIR OPTIC, 6" WHITE BAFFLE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1161.2 lumens  
Efficiency: N/A  
Efficacy: 110.6 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P644032  
CATALOG NUMBER: ML5615LSWFL559FS1E - 693WB - 900LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P644032  
 CATALOG NUMBER: ML5615LSWFL559FS1E - 693WB - 900LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93	
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85	
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78			78	
4	96	87	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72	
5	90	81	75	71	89	80	75	70	79	73	70	77	72	69	75	71	68	67			67	
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	67	63	62			62	
7	81	71	64	60	79	70	64	60	69	63	59	68	63	59	66	62	59	57			57	
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			53	
9	73	62	56	52	71	62	56	52	61	55	52	60	55	51	59	55	51	50			50	
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47			47	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	66859
5°	64060
10°	60793
15°	57253
20°	51892
25°	44162
30°	36126
35°	28282
40°	20975
45°	13792
50°	5961
55°	2456
60°	1349
65°	662
70°	657
75°	657
80°	663
85°	629

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13792 cd/sqm



TEST NUMBER: P644032

CATALOG NUMBER: ML5615LSWFL559FS1E - 693WB - 900LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.9	9.4
10°-20°	281.0	24.2
20°-30°	333.8	28.7
30°-40°	264.5	22.8
40°-50°	134.9	11.6
50°-60°	27.5	2.4
60°-70°	6.1	0.5
70°-80°	3.3	0.3
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	723.7	62.3
0°-40°	988.2	85.1
0°-60°	1150.5	99.1
0°-90°	1161.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1161.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1220	
5°	1164	109
15°	1009	281
25°	730	334
35°	423	265
45°	178	135
55°	26	27
65°	5	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P644032

CATALOG NUMBER: ML5615LSWFL559FS1E - 693WB - 900LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1219.6
2.5°	1204.2
5°	1164.1
7.5°	1126.0
10°	1092.1
12.5°	1053.0
15°	1008.8
17.5°	953.3
20°	889.5
22.5°	814.4
25°	730.1
27.5°	647.8
30°	570.7
32.5°	495.7
35°	422.6
37.5°	355.8
40°	293.1
42.5°	233.4
45°	177.9
47.5°	116.2
50°	69.9
52.5°	39.1
55°	25.7
57.5°	18.5
60°	12.3
62.5°	7.2
65°	5.1
67.5°	4.1
70°	4.1
72.5°	3.1
75°	3.1
77.5°	3.1
80°	2.1
82.5°	2.1
85°	1.0
87.5°	1.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)