

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643552

Luminaire Tested: ML5615LSVWFL9FS1E - 594WB - 900LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P643552  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-101)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSVWFL9FS1E - 594WB - 900LM - 3000K  
Description: ML56 RR, MILKY OPTIC, 5" WHITE GIMBAL TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1128.3 lumens  
Efficiency: N/A  
Efficacy: 107.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.28  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P643552

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594WB - 900LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P643552

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594WB - 900LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	94	88	82	99	92	86	82	88	84	80	85	81	78	82	79	76	74																			
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	70	66	64																			
4	86	75	67	60	84	73	66	60	71	64	59	69	63	58	67	62	58	56																			
5	79	67	59	53	77	66	58	53	64	57	52	62	56	51	60	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																			
7	68	56	47	42	67	55	47	41	53	46	41	52	46	41	51	45	41	39																			
8	64	51	43	37	62	50	43	37	49	42	37	48	41	37	47	41	37	35																			
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31																			
10	56	43	36	31	55	43	36	31	42	35	31	41	35	31	40	34	30	29																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	38973
5°	38956
10°	38829
15°	38583
20°	38274
25°	37628
30°	36653
35°	35281
40°	33275
45°	30768
50°	27657
55°	24347
60°	20619
65°	17484
70°	14726
75°	12536
80°	11229
85°	10235

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 30768 cd/sqm



TEST NUMBER: P643552

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594WB - 900LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.7	4.1
10°-20°	133.3	11.8
20°-30°	198.8	17.6
30°-40°	228.0	20.2
40°-50°	211.7	18.8
50°-60°	158.1	14.0
60°-70°	93.6	8.3
70°-80°	45.0	4.0
80°-90°	13.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	378.7	33.6
0°-40°	606.7	53.8
0°-60°	976.5	86.5
0°-90°	1128.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1128.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	494	
5°	492	47
15°	472	133
25°	432	199
35°	366	228
45°	276	212
55°	177	158
65°	94	94
75°	41	45
85°	11	13
90°	0	



TEST NUMBER: P643552

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594WB - 900LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	493.7
2.5°	493.7
5°	491.6
7.5°	488.5
10°	484.4
12.5°	479.3
15°	472.1
17.5°	464.9
20°	455.6
22.5°	444.3
25°	432.0
27.5°	418.6
30°	402.1
32.5°	384.7
35°	366.1
37.5°	344.5
40°	322.9
42.5°	299.3
45°	275.6
47.5°	249.9
50°	225.2
52.5°	200.6
55°	176.9
57.5°	153.2
60°	130.6
62.5°	111.1
65°	93.6
67.5°	77.1
70°	63.8
72.5°	52.5
75°	41.1
77.5°	32.9
80°	24.7
82.5°	17.5
85°	11.3
87.5°	7.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)