

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643554

Luminaire Tested: ML5615LSVWFL9FS1E - 594WB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-101)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 594WB - 900LM - 4000K
Description: ML56 RR, MILKY OPTIC, 5" WHITE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1247.1 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.28
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643554

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594WB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P643554

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594WB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	94	88	82	99	92	86	82	88	84	80	85	81	78	82	79	76	74																			
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	70	66	64																			
4	86	75	67	60	84	73	66	60	71	64	59	69	63	58	67	62	58	56																			
5	79	67	59	53	77	66	58	53	64	57	52	62	56	51	60	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																			
7	68	56	47	42	67	55	47	41	53	46	41	52	46	41	51	45	41	39																			
8	64	51	43	37	62	50	43	37	49	42	37	48	41	37	47	41	37	35																			
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31																			
10	56	43	36	31	55	43	36	31	42	35	31	41	35	31	40	34	30	29																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43070
5°	43060
10°	42917
15°	42644
20°	42306
25°	41582
30°	40518
35°	39001
40°	36779
45°	34005
50°	30567
55°	26907
60°	22798
65°	19314
70°	16272
75°	13878
80°	12411
85°	11322

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34005 cd/sqm



TEST NUMBER: P643554

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594WB - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	4.1
10°-20°	147.3	11.8
20°-30°	219.7	17.6
30°-40°	252.0	20.2
40°-50°	234.0	18.8
50°-60°	174.8	14.0
60°-70°	103.5	8.3
70°-80°	49.8	4.0
80°-90°	14.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	418.6	33.6
0°-40°	670.6	53.8
0°-60°	1079.3	86.5
0°-90°	1247.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1247.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	546	
5°	543	52
15°	522	147
25°	477	220
35°	405	252
45°	305	234
55°	196	175
65°	103	103
75°	46	50
85°	12	15
90°	0	



TEST NUMBER: P643554

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594WB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	545.6
2.5°	545.6
5°	543.4
7.5°	540.0
10°	535.4
12.5°	529.7
15°	521.8
17.5°	513.8
20°	503.6
22.5°	491.1
25°	477.4
27.5°	462.7
30°	444.5
32.5°	425.1
35°	404.7
37.5°	380.8
40°	356.9
42.5°	330.8
45°	304.6
47.5°	276.2
50°	248.9
52.5°	221.7
55°	195.5
57.5°	169.4
60°	144.4
62.5°	122.8
65°	103.4
67.5°	85.3
70°	70.5
72.5°	58.0
75°	45.5
77.5°	36.4
80°	27.3
82.5°	19.3
85°	12.5
87.5°	8.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)