

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643563

Luminaire Tested: ML5615LSVWFL9FS1E - 596WB - 1500LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643563
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-104)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 596WB - 1500LM - 3500K
Description: ML56 RR, MILKY OPTIC, 5" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1672.5 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.24
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643563
CATALOG NUMBER: ML5615LSVWFL9FS1E - 596WB - 1500LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643563

CATALOG NUMBER: ML5615LSVWFL9FS1E - 596WB - 1500LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89																			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78																			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	71	66	87	77	71	65	75	69	64	73	68	64	71	66	63	61																			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54																			
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40																			
9	63	51	44	39	62	50	43	39	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69215
5°	69226
10°	68840
15°	68176
20°	67315
25°	66075
30°	64509
35°	61715
40°	56008
45°	45649
50°	33478
55°	23961
60°	17888
65°	14420
70°	12510
75°	12017
80°	11956
85°	10416

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 45649 cd/sqm



TEST NUMBER: P643563

CATALOG NUMBER: ML5615LSVWFL9FS1E - 596WB - 1500LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	5.0
10°-20°	235.2	14.1
20°-30°	349.4	20.9
30°-40°	397.0	23.7
40°-50°	313.3	18.7
50°-60°	161.3	9.6
60°-70°	78.3	4.7
70°-80°	41.8	2.5
80°-90°	13.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	667.5	39.9
0°-40°	1064.5	63.6
0°-60°	1539.0	92.0
0°-90°	1672.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1672.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	877	
5°	874	83
15°	834	235
25°	759	349
35°	640	397
45°	409	313
55°	174	161
65°	77	78
75°	39	42
85°	12	13
90°	0	



TEST NUMBER: P643563

CATALOG NUMBER: ML5615LSVWFL9FS1E - 596WB - 1500LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	876.8
2.5°	876.8
5°	873.6
7.5°	867.0
10°	858.8
12.5°	847.3
15°	834.2
17.5°	819.4
20°	801.3
22.5°	781.6
25°	758.6
27.5°	735.6
30°	707.7
32.5°	676.5
35°	640.4
37.5°	597.7
40°	543.5
42.5°	479.5
45°	408.9
47.5°	336.6
50°	272.6
52.5°	218.4
55°	174.1
57.5°	139.6
60°	113.3
62.5°	92.0
65°	77.2
67.5°	64.0
70°	54.2
72.5°	46.0
75°	39.4
77.5°	32.8
80°	26.3
82.5°	19.7
85°	11.5
87.5°	4.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)