

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P644045

Luminaire Tested: ML5615LSWFL559FS1E - 694TBZB - 1500LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P644045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-68)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 694TBZB - 1500LM - 5000K
Description: ML56 RR, 55D TIR OPTIC, 6" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2012.4 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P644045
CATALOG NUMBER: ML5615LSWFL559FS1E - 694TBZB - 1500LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P644045

CATALOG NUMBER: ML5615LSWFL559FS1E - 694TBZB - 1500LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			92																
2	107	101	97	93	105	100	96	92	96	93	90	93	91	88	91	88	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63	61			61																
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57																
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53			53																
9	72	62	56	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49			49																
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114667
5°	109949
10°	104329
15°	98644
20°	89328
25°	75718
30°	61225
35°	47569
40°	35173
45°	23165
50°	11155
55°	5916
60°	3881
65°	3217
70°	2549
75°	1864
80°	1105
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23165 cd/sqm



TEST NUMBER: P644045

CATALOG NUMBER: ML5615LSWFL559FS1E - 694TBZB - 1500LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.9	9.3
10°-20°	483.7	24.0
20°-30°	571.2	28.4
30°-40°	445.3	22.1
40°-50°	227.8	11.3
50°-60°	61.9	3.1
60°-70°	25.1	1.2
70°-80°	9.5	0.5
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1241.8	61.7
0°-40°	1687.1	83.8
0°-60°	1976.8	98.2
0°-90°	2012.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2012.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2092	
5°	1998	187
15°	1738	484
25°	1252	571
35°	711	445
45°	299	228
55°	62	62
65°	25	25
75°	9	10
85°	0	1
90°	0	



TEST NUMBER: P644045

CATALOG NUMBER: ML5615LSWFL559FS1E - 694TBZB - 1500LM - 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2091.7
2.5°	2066.9
5°	1998.0
7.5°	1932.6
10°	1874.2
12.5°	1812.3
15°	1738.1
17.5°	1642.6
20°	1531.2
22.5°	1396.8
25°	1251.8
27.5°	1105.1
30°	967.2
32.5°	836.3
35°	710.8
37.5°	595.9
40°	491.5
42.5°	390.8
45°	298.8
47.5°	196.3
50°	130.8
52.5°	88.4
55°	61.9
57.5°	46.0
60°	35.4
62.5°	30.1
65°	24.8
67.5°	21.2
70°	15.9
72.5°	12.4
75°	8.8
77.5°	5.3
80°	3.5
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)