

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P644048

Luminaire Tested: ML5615LSWFL559FS1E - 694TBZB - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P644048
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-68)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 694TBZB - 900LM - 3500K
Description: ML56 RR, 55D TIR OPTIC, 6" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1202.4 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P644048

CATALOG NUMBER: ML5615LSWFL559FS1E - 694TBZB - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P644048

CATALOG NUMBER: ML5615LSWFL559FS1E - 694TBZB - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			92																
2	107	101	97	93	105	100	96	92	96	93	90	93	91	88	91	88	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63	61			61																
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57																
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53			53																
9	72	62	56	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49			49																
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68514
5°	65694
10°	62335
15°	58939
20°	53374
25°	45245
30°	36582
35°	28422
40°	21018
45°	13839
50°	6669
55°	3536
60°	2313
65°	1920
70°	1523
75°	1123
80°	663
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13839 cd/sqm



TEST NUMBER: P644048

CATALOG NUMBER: ML5615LSWFL559FS1E - 694TBZB - 900LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.7	9.3
10°-20°	289.0	24.0
20°-30°	341.3	28.4
30°-40°	266.0	22.1
40°-50°	136.1	11.3
50°-60°	37.0	3.1
60°-70°	15.0	1.2
70°-80°	5.7	0.5
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	742.0	61.7
0°-40°	1008.0	83.8
0°-60°	1181.1	98.2
0°-90°	1202.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1202.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1250	
5°	1194	112
15°	1038	289
25°	748	341
35°	425	266
45°	178	136
55°	37	37
65°	15	15
75°	5	6
85°	0	1
90°	0	



TEST NUMBER: P644048

CATALOG NUMBER: ML5615LSWFL559FS1E - 694TBZB - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1249.8
2.5°	1235.0
5°	1193.8
7.5°	1154.7
10°	1119.8
12.5°	1082.9
15°	1038.5
17.5°	981.4
20°	914.9
22.5°	834.6
25°	748.0
27.5°	660.3
30°	577.9
32.5°	499.7
35°	424.7
37.5°	356.0
40°	293.7
42.5°	233.5
45°	178.5
47.5°	117.3
50°	78.2
52.5°	52.8
55°	37.0
57.5°	27.5
60°	21.1
62.5°	18.0
65°	14.8
67.5°	12.7
70°	9.5
72.5°	7.4
75°	5.3
77.5°	3.2
80°	2.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)