

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P644133

Luminaire Tested: ML5615LSWW9FS1E - 692H WW - 1500LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P644133
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-132)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWW9FS1E - 692H WW - 1500LM - 3500K
Description: ML56 RR, WW OPTIC, 6" WW INSERT WITH HAZE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1064.2 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.12 / 1.23
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P644133

CATALOG NUMBER: ML5615LSWW9FS1E - 692H WW - 1500LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P644133

CATALOG NUMBER: ML5615LSWW9FS1E - 692H WW - 1500LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88	88	88	88	88	88		
	2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76	76	76	76	76	76		
	3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66	66	66	66	66	66		
	4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57	57	57	57	57	57		
	5	80	69	60	54	78	68	60	54	66	59	54	64	58	53	62	57	53	51	51	51	51	51	51		
	6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45	45	45	45	45	45		
	7	69	57	49	43	68	56	48	43	55	48	43	53	47	42	52	46	42	40	40	40	40	40	40		
	8	65	52	44	39	63	52	44	39	50	43	38	49	43	38	48	42	38	36	36	36	36	36	36		
	9	61	48	40	35	59	48	40	35	46	40	35	45	39	35	44	39	35	33	33	33	33	33	33		
	10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30	30	30	30	30	30		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	28199	28199	28199	28199	28199
5°	28483	28395	28032	27762	27674
10°	28635	28356	27716	27171	26987
15°	28445	28071	27140	26396	26113
20°	28183	27612	26363	25406	25115
25°	27733	27038	25447	24255	23953
30°	27251	26213	24238	22883	22573
35°	26722	25511	22874	21335	20786
40°	25634	24224	21404	19637	18935
45°	24080	22553	19622	17707	16816
50°	22140	20605	17935	15556	14439
55°	20100	18695	16019	13352	11937
60°	18014	16391	13870	10811	9012
65°	15566	14074	11506	8094	5759
70°	13175	11588	8687	5001	2629
75°	10781	9044	5571	1737	1038
80°	7766	6219	2589	505	505
85°	4151	3082	1006	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24080 cd/sqm



TEST NUMBER: P644133

CATALOG NUMBER: ML5615LSWW9FS1E - 692H WW - 1500LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.3	4.5
10°-20°	135.1	12.7
20°-30°	194.6	18.3
30°-40°	217.6	20.4
40°-50°	199.5	18.7
50°-60°	149.8	14.1
60°-70°	85.6	8.0
70°-80°	29.9	2.8
80°-90°	3.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	378.0	35.5
0°-40°	595.6	56.0
0°-60°	944.9	88.8
0°-90°	1064.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1064.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	514	514	514	514	514	
5°	518	516	509	504	503	49
15°	501	495	478	465	460	142
25°	458	447	421	401	396	211
35°	399	381	342	319	311	249
45°	311	291	253	228	217	239
55°	210	196	168	140	125	188
65°	120	108	89	62	44	119
75°	51	43	26	8	5	55
85°	7	5	2	0	0	10
90°	0	0	0	0	0	



TEST NUMBER: P644133

CATALOG NUMBER: ML5615LSWW9FS1E - 692H WW - 1500LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4
2.5°	517.6	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	514.4
5°	517.6	517.6	517.6	517.6	517.6	517.6	517.6	516.0	516.0	516.0	516.0
7.5°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	514.4	514.4	512.7	512.7
10°	514.4	514.4	514.4	512.7	512.7	512.7	512.7	512.7	511.1	511.1	509.4
12.5°	509.4	509.4	509.4	509.4	507.8	507.8	507.8	506.1	504.5	504.5	502.9
15°	501.2	502.9	502.9	501.2	501.2	501.2	501.2	499.6	497.9	496.3	494.6
17.5°	494.6	494.6	494.6	493.0	491.4	493.0	491.4	489.7	488.1	486.4	484.8
20°	483.1	483.1	481.5	481.5	481.5	481.5	479.8	478.2	476.6	474.9	473.3
22.5°	471.6	471.6	471.6	468.3	468.3	468.3	466.7	466.7	463.4	461.8	458.5
25°	458.5	458.5	458.5	456.8	455.2	453.6	455.2	451.9	450.3	447.0	447.0
27.5°	445.3	445.3	443.7	443.7	442.1	442.1	440.4	437.1	435.5	433.8	430.5
30°	430.5	430.5	428.9	428.9	427.3	425.6	425.6	422.3	420.7	417.4	414.1
32.5°	415.8	415.8	414.1	414.1	412.5	410.8	410.8	407.5	404.3	401.0	399.3
35°	399.3	399.3	397.7	397.7	396.0	394.4	392.8	389.5	387.8	382.9	381.2
37.5°	379.6	381.2	378.0	378.0	376.3	374.7	373.0	371.4	368.1	364.8	359.9
40°	358.2	356.6	356.6	355.0	353.3	353.3	351.7	348.4	346.7	341.8	338.5
42.5°	333.6	333.6	333.6	332.0	330.3	330.3	327.0	325.4	322.1	318.8	313.9
45°	310.6	310.6	308.9	308.9	305.7	305.7	304.0	300.7	299.1	294.2	290.9
47.5°	285.9	284.3	284.3	282.7	281.0	281.0	279.4	277.7	274.4	269.5	266.2
50°	259.6	259.6	259.6	258.0	256.4	256.4	254.7	251.4	249.8	246.5	241.6
52.5°	235.0	235.0	235.0	233.4	231.7	231.7	230.1	228.4	225.1	221.8	218.6
55°	210.3	210.3	210.3	208.7	208.7	205.4	205.4	203.8	200.5	197.2	195.6
57.5°	185.7	185.7	185.7	185.7	184.1	184.1	182.4	180.8	177.5	175.8	170.9
60°	164.3	162.7	162.7	161.0	161.0	159.4	157.8	156.1	154.5	151.2	149.5
62.5°	139.7	141.3	139.7	139.7	138.0	138.0	138.0	134.8	133.1	129.8	128.2
65°	120.0	120.0	120.0	120.0	116.7	116.7	116.7	113.4	111.7	111.7	108.5
67.5°	100.2	100.2	100.2	98.6	98.6	98.6	97.0	95.3	93.7	92.0	90.4
70°	82.2	82.2	82.2	80.5	80.5	78.9	78.9	77.2	75.6	75.6	72.3
72.5°	65.7	65.7	65.7	65.7	64.1	64.1	62.4	62.4	60.8	59.2	57.5
75°	50.9	50.9	50.9	49.3	49.3	49.3	47.7	47.7	46.0	44.4	42.7
77.5°	37.8	36.2	36.2	36.2	36.2	34.5	34.5	34.5	32.9	31.2	31.2
80°	24.6	24.6	24.6	24.6	24.6	23.0	23.0	23.0	21.4	21.4	19.7
82.5°	14.8	14.8	14.8	14.8	14.8	13.1	13.1	13.1	11.5	11.5	11.5
85°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	4.9	4.9	4.9
87.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P644133

CATALOG NUMBER: ML5615LSWW9FS1E - 692H WW - 1500LM - 3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4
2.5°	516.0	516.0	514.4	514.4	514.4	514.4	514.4	512.7	512.7	512.7	512.7
5°	516.0	514.4	512.7	512.7	512.7	512.7	511.1	511.1	511.1	509.4	509.4
7.5°	511.1	511.1	511.1	509.4	509.4	507.8	507.8	506.1	506.1	504.5	504.5
10°	507.8	506.1	506.1	504.5	504.5	502.9	502.9	499.6	497.9	497.9	496.3
12.5°	501.2	499.6	499.6	496.3	496.3	496.3	494.6	491.4	489.7	489.7	488.1
15°	493.0	491.4	489.7	486.4	486.4	484.8	483.1	481.5	479.8	478.2	476.6
17.5°	483.1	479.8	478.2	476.6	474.9	473.3	471.6	470.0	466.7	466.7	463.4
20°	471.6	468.3	466.7	463.4	461.8	461.8	458.5	455.2	453.6	451.9	448.6
22.5°	456.8	455.2	451.9	448.6	447.0	447.0	443.7	440.4	438.8	435.5	433.8
25°	443.7	438.8	437.1	433.8	432.2	432.2	428.9	425.6	422.3	420.7	417.4
27.5°	427.3	424.0	422.3	417.4	415.8	414.1	410.8	407.5	404.3	401.0	397.7
30°	410.8	407.5	404.3	399.3	399.3	396.0	392.8	387.8	386.2	382.9	378.0
32.5°	394.4	391.1	386.2	382.9	379.6	378.0	373.0	369.7	366.5	361.5	359.9
35°	376.3	371.4	368.1	363.2	361.5	358.2	355.0	350.0	346.7	341.8	336.9
37.5°	356.6	350.0	346.7	341.8	340.2	336.9	333.6	330.3	325.4	320.4	317.2
40°	335.2	328.7	323.7	320.4	317.2	313.9	312.2	305.7	302.4	299.1	295.8
42.5°	310.6	305.7	300.7	297.4	294.2	292.5	287.6	284.3	279.4	276.1	272.8
45°	287.6	282.7	277.7	272.8	271.1	269.5	266.2	261.3	256.4	253.1	249.8
47.5°	262.9	259.6	253.1	251.4	248.1	246.5	241.6	238.3	236.6	231.7	228.4
50°	238.3	235.0	231.7	226.8	225.1	223.5	220.2	216.9	213.6	210.3	207.1
52.5°	213.6	212.0	208.7	203.8	203.8	202.1	198.8	195.6	192.3	189.0	185.7
55°	192.3	189.0	185.7	182.4	180.8	179.1	175.8	174.2	170.9	167.6	164.3
57.5°	169.3	166.0	164.3	161.0	159.4	157.8	154.5	152.8	149.5	146.3	143.0
60°	147.9	144.6	143.0	139.7	138.0	138.0	134.8	131.5	129.8	126.5	123.2
62.5°	126.5	123.2	121.6	118.3	118.3	116.7	115.0	111.7	110.1	106.8	105.2
65°	106.8	105.2	101.9	100.2	98.6	97.0	95.3	93.7	90.4	88.7	85.5
67.5°	88.7	85.5	83.8	82.2	80.5	78.9	77.2	75.6	72.3	70.7	67.4
70°	70.7	69.0	67.4	65.7	64.1	64.1	60.8	59.2	55.9	54.2	50.9
72.5°	55.9	54.2	52.6	49.3	49.3	47.7	46.0	44.4	41.1	39.4	36.2
75°	41.1	41.1	37.8	36.2	36.2	34.5	32.9	31.2	29.6	26.3	24.6
77.5°	29.6	27.9	26.3	24.6	23.0	23.0	21.4	19.7	18.1	16.4	13.1
80°	19.7	18.1	16.4	14.8	14.8	13.1	11.5	11.5	9.9	8.2	6.6
82.5°	9.9	9.9	8.2	8.2	6.6	6.6	6.6	4.9	4.9	3.3	3.3
85°	4.9	3.3	3.3	3.3	3.3	3.3	1.6	1.6	1.6	1.6	0.0
87.5°	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P644133

CATALOG NUMBER: ML5615LSWW9FS1E - 692H WW - 1500LM - 3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4
2.5°	512.7	511.1	512.7	512.7	511.1	511.1	511.1	511.1	509.4	511.1	509.4
5°	509.4	507.8	507.8	507.8	507.8	506.1	506.1	504.5	504.5	504.5	504.5
7.5°	502.9	501.2	501.2	499.6	499.6	499.6	499.6	497.9	497.9	496.3	496.3
10°	496.3	494.6	493.0	493.0	491.4	491.4	491.4	489.7	488.1	488.1	486.4
12.5°	484.8	484.8	483.1	483.1	481.5	481.5	479.8	478.2	478.2	476.6	476.6
15°	474.9	473.3	471.6	471.6	470.0	468.3	466.7	466.7	465.1	465.1	463.4
17.5°	461.8	458.5	458.5	456.8	455.2	455.2	453.6	451.9	450.3	450.3	450.3
20°	447.0	445.3	443.7	442.1	440.4	440.4	438.8	437.1	435.5	433.8	433.8
22.5°	430.5	428.9	427.3	425.6	425.6	424.0	422.3	420.7	419.0	417.4	417.4
25°	414.1	412.5	410.8	409.2	407.5	405.9	404.3	402.6	401.0	399.3	399.3
27.5°	396.0	392.8	391.1	389.5	387.8	386.2	386.2	382.9	382.9	381.2	379.6
30°	376.3	373.0	369.7	369.7	368.1	366.5	363.2	363.2	361.5	359.9	358.2
32.5°	355.0	353.3	350.0	350.0	346.7	345.1	343.5	341.8	340.2	338.5	338.5
35°	335.2	330.3	328.7	328.7	325.4	323.7	322.1	318.8	318.8	315.5	315.5
37.5°	313.9	310.6	308.9	305.7	304.0	302.4	300.7	297.4	295.8	294.2	292.5
40°	292.5	289.2	285.9	284.3	282.7	279.4	277.7	274.4	274.4	271.1	269.5
42.5°	269.5	266.2	262.9	261.3	259.6	256.4	254.7	251.4	249.8	248.1	246.5
45°	246.5	243.2	241.6	239.9	238.3	236.6	231.7	230.1	228.4	225.1	223.5
47.5°	225.1	221.8	218.6	218.6	215.3	213.6	210.3	207.1	205.4	202.1	200.5
50°	203.8	200.5	197.2	195.6	195.6	190.6	189.0	185.7	182.4	179.1	177.5
52.5°	182.4	179.1	175.8	174.2	172.5	169.3	166.0	164.3	161.0	157.8	156.1
55°	161.0	157.8	154.5	152.8	151.2	147.9	146.3	141.3	139.7	136.4	133.1
57.5°	141.3	138.0	134.8	133.1	131.5	128.2	124.9	121.6	120.0	116.7	113.4
60°	120.0	118.3	115.0	113.4	111.7	110.1	105.2	101.9	98.6	97.0	93.7
62.5°	101.9	98.6	95.3	93.7	92.0	90.4	87.1	83.8	82.2	77.2	73.9
65°	83.8	80.5	77.2	75.6	73.9	72.3	69.0	65.7	62.4	59.2	57.5
67.5°	64.1	62.4	59.2	59.2	57.5	54.2	50.9	49.3	46.0	44.4	41.1
70°	49.3	47.7	44.4	42.7	41.1	37.8	36.2	32.9	31.2	29.6	26.3
72.5°	34.5	32.9	29.6	27.9	26.3	24.6	21.4	19.7	18.1	16.4	14.8
75°	23.0	19.7	18.1	16.4	16.4	13.1	11.5	9.9	8.2	6.6	6.6
77.5°	13.1	11.5	8.2	8.2	8.2	6.6	4.9	4.9	3.3	3.3	3.3
80°	6.6	4.9	3.3	3.3	3.3	3.3	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	0.0	0.0	0.0	0.0	0.0	1.6	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P644133

CATALOG NUMBER: ML5615LSWW9FS1E - 692H WW - 1500LM - 3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4
2.5°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
5°	504.5	502.9	502.9	502.9	502.9	502.9	502.9	502.9
7.5°	496.3	496.3	494.6	496.3	494.6	494.6	494.6	494.6
10°	486.4	486.4	486.4	486.4	484.8	484.8	484.8	484.8
12.5°	476.6	474.9	474.9	474.9	473.3	474.9	473.3	473.3
15°	463.4	461.8	461.8	461.8	461.8	460.1	461.8	460.1
17.5°	448.6	448.6	447.0	448.6	447.0	447.0	447.0	447.0
20°	432.2	432.2	432.2	430.5	432.2	430.5	430.5	430.5
22.5°	415.8	415.8	414.1	414.1	414.1	414.1	414.1	414.1
25°	397.7	397.7	397.7	397.7	396.0	396.0	396.0	396.0
27.5°	379.6	378.0	378.0	378.0	376.3	378.0	376.3	376.3
30°	358.2	358.2	356.6	356.6	356.6	355.0	355.0	356.6
32.5°	335.2	335.2	335.2	335.2	333.6	333.6	333.6	333.6
35°	313.9	313.9	312.2	312.2	312.2	310.6	310.6	310.6
37.5°	290.9	290.9	289.2	289.2	289.2	287.6	287.6	289.2
40°	267.9	267.9	266.2	266.2	266.2	264.6	264.6	264.6
42.5°	244.9	243.2	243.2	241.6	241.6	241.6	239.9	239.9
45°	221.8	220.2	220.2	220.2	218.6	216.9	216.9	216.9
47.5°	198.8	197.2	195.6	195.6	193.9	193.9	193.9	195.6
50°	175.8	174.2	174.2	172.5	170.9	170.9	170.9	169.3
52.5°	152.8	151.2	151.2	149.5	149.5	147.9	146.3	146.3
55°	131.5	129.8	128.2	126.5	126.5	124.9	124.9	124.9
57.5°	110.1	108.5	106.8	106.8	105.2	105.2	103.5	101.9
60°	90.4	88.7	87.1	87.1	85.5	83.8	82.2	82.2
62.5°	72.3	70.7	69.0	67.4	65.7	64.1	62.4	64.1
65°	55.9	52.6	50.9	49.3	49.3	47.7	46.0	44.4
67.5°	39.4	37.8	36.2	34.5	32.9	31.2	29.6	29.6
70°	24.6	21.4	21.4	21.4	19.7	18.1	16.4	16.4
72.5°	13.1	11.5	9.9	9.9	8.2	8.2	8.2	8.2
75°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
77.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)