

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643595

Luminaire Tested: ML5615LSVWFL9FS1E - 692H - 1500LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643595
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-107)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 692H - 1500LM - 5000K
Description: ML56 RR, MILKY OPTIC, 6" HAZE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1724.1 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.1
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643595
CATALOG NUMBER: ML5615LSVWFL9FS1E - 692H - 1500LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P643595

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692H - 1500LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83																			
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75																			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	72	69	67																			
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61																			
6	81	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	57	56																			
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51																			
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47																			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																			
10	64	53	46	42	63	52	46	42	52	46	42	51	45	41	50	45	41	40																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69205
5°	68495
10°	66532
15°	63315
20°	59616
25°	55824
30°	52040
35°	48037
40°	41249
45°	29608
50°	17944
55°	10141
60°	5427
65°	2516
70°	1410
75°	1123
80°	568
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29608 cd/sqm



TEST NUMBER: P643595

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692H - 1500LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.2	6.8
10°-20°	313.0	18.2
20°-30°	424.4	24.6
30°-40°	443.9	25.7
40°-50°	295.4	17.1
50°-60°	101.5	5.9
60°-70°	22.8	1.3
70°-80°	5.1	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	854.6	49.6
0°-40°	1298.5	75.3
0°-60°	1695.5	98.3
0°-90°	1724.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1724.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1262	
5°	1245	117
15°	1116	313
25°	923	424
35°	718	444
45°	382	295
55°	106	102
65°	19	23
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P643595

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692H - 1500LM - 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1262.4
2.5°	1258.9
5°	1244.7
7.5°	1223.5
10°	1195.2
12.5°	1158.1
15°	1115.6
17.5°	1069.7
20°	1021.9
22.5°	972.4
25°	922.9
27.5°	873.4
30°	822.1
32.5°	772.6
35°	717.8
37.5°	655.9
40°	576.4
42.5°	482.7
45°	381.9
47.5°	288.2
50°	210.4
52.5°	150.3
55°	106.1
57.5°	72.5
60°	49.5
62.5°	31.8
65°	19.4
67.5°	12.4
70°	8.8
72.5°	5.3
75°	5.3
77.5°	3.5
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)