

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P#

Luminaire Tested: **RL56069S1EWH-3000K**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27974)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: RL56069S1EWH-3000K
Description: Halo RL 5/6in Downlight - SeleCCTable 3000K
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 665.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.21
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: RL56069S1EWH-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: RL56069S1EWH-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	98	100	98	95		97	94	92		93	91	90	88
2	102	95	89	85	100	93	88	84	90	86	82		87	83	80		84	81	78	76
3	94	85	78	73	92	84	77	72	81	75	71		78	74	70		76	72	68	66
4	87	77	69	63	85	75	68	63	73	67	62		71	65	61		69	64	60	58
5	81	69	61	56	79	68	61	55	66	60	55		64	59	54		63	58	54	52
6	75	63	55	49	73	62	55	49	61	54	49		59	53	48		57	52	48	46
7	70	58	50	44	69	57	49	44	56	49	44		54	48	43		53	47	43	41
8	66	53	45	40	64	52	45	40	51	44	40		50	44	39		49	43	39	37
9	62	49	41	36	60	49	41	36	47	41	36		46	40	36		45	40	36	34
10	58	46	38	33	57	45	38	33	44	38	33		43	37	33		42	37	33	31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18387
5°	18336
10°	18125
15°	17860
20°	17344
25°	16731
30°	15990
35°	14937
40°	13869
45°	12497
50°	10678
55°	8955
60°	7401
65°	6071
70°	4712
75°	3685
80°	2747
85°	2768



TEST NUMBER: P#

CATALOG NUMBER: RL56069S1EWH-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.6	4.7
10°-20°	88.4	13.3
20°-30°	127.1	19.1
30°-40°	139.7	21.0
40°-50°	123.4	18.5
50°-60°	84.4	12.7
60°-70°	46.6	7.0
70°-80°	19.1	2.9
80°-90°	4.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	247.1	37.2
0°-40°	386.8	58.2
0°-60°	594.6	89.4
0°-90°	665.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	665.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	335	
5°	333	32
15°	315	88
25°	277	127
35°	223	140
45°	161	123
55°	94	84
65°	47	47
75°	17	19
85°	4	5
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: RL56069S1EWH-3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	335.4
2.5°	333.2
5°	333.2
7.5°	331.0
10°	325.6
12.5°	320.2
15°	314.7
17.5°	307.1
20°	297.3
22.5°	286.4
25°	276.6
27.5°	265.7
30°	252.6
32.5°	238.5
35°	223.2
37.5°	209.1
40°	193.8
42.5°	177.5
45°	161.2
47.5°	142.7
50°	125.2
52.5°	108.9
55°	93.7
57.5°	79.5
60°	67.5
62.5°	56.6
65°	46.8
67.5°	37.0
70°	29.4
72.5°	22.9
75°	17.4
77.5°	13.1
80°	8.7
82.5°	6.5
85°	4.4
87.5°	2.2
90°	0.0

(END OF REPORT)