

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P388129

Luminaire Tested: **RL56069B4AWHVA-3000K**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P388129
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (1911601A-P0)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: RL56069B4AWHVA-3000K
Description: HALO VOICE RL 56 LED MOUDULE AT 3000K, 90 CRI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 827.0 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 12.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P388129

CATALOG NUMBER: RL56069B4AWHVA-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P388129

CATALOG NUMBER: RL56069B4AWHVA-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	105	102	98	107	103	100	96	99	96	93		95	93	91		92	90	88	86
2	100	93	86	81	98	91	85	80	87	83	78		84	80	77		81	78	75	73
3	92	82	74	68	90	81	73	68	78	72	67		75	70	65		72	68	64	62
4	85	73	65	58	82	72	64	58	69	63	57		67	61	56		65	60	56	54
5	78	66	57	51	76	64	56	50	62	55	50		60	54	49		59	53	49	47
6	72	59	51	44	70	58	50	44	57	49	44		55	48	43		53	48	43	41
7	67	54	45	39	65	53	45	39	52	44	39		50	44	39		49	43	38	36
8	62	49	41	35	61	49	41	35	47	40	35		46	39	35		45	39	35	33
9	58	45	37	32	57	45	37	32	44	36	32		42	36	31		41	36	31	29
10	55	42	34	29	53	41	34	29	40	33	29		39	33	29		38	33	28	27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21528
5°	21479
10°	21489
15°	21347
20°	21206
25°	20978
30°	20619
35°	20139
40°	19463
45°	18729
50°	17757
55°	16562
60°	15066
65°	13203
70°	10736
75°	8356
80°	6584
85°	4198



TEST NUMBER: P388129

CATALOG NUMBER: RL56069B4AWHVA-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.2	3.8
10°-20°	89.1	10.8
20°-30°	133.9	16.2
30°-40°	157.6	19.1
40°-50°	156.0	18.9
50°-60°	129.9	15.7
60°-70°	84.6	10.2
70°-80°	36.9	4.5
80°-90°	7.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.2	30.7
0°-40°	411.8	49.8
0°-60°	697.7	84.4
0°-90°	827.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	827.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	330	
5°	328	31
15°	316	89
25°	291	134
35°	252	158
45°	203	156
55°	145	130
65°	85	85
75°	33	37
85°	6	8
90°	0	



TEST NUMBER: P388129

CATALOG NUMBER: RL56069B4AWHVA-3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	329.5
5°	327.5
10°	323.9
15°	315.6
20°	305.0
25°	291.0
30°	273.3
35°	252.5
40°	228.2
45°	202.7
50°	174.7
55°	145.4
60°	115.3
65°	85.4
70°	56.2
75°	33.1
80°	17.5
85°	5.6
90°	0.0

(END OF REPORT)