

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P#

Luminaire Tested: **RL560WHZHA69-5000K**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27627)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: RL560WHZHA69-5000K
Description: RL56 Wireless
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 721.2 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.31
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 9.63276666666667
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: RL560WHZHA69-5000K

Luminous Intensity Polar Plot






TEST NUMBER: P#

CATALOG NUMBER: RL560WHZHA69-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	102	99	107	104	100	97	99	96	94		95	93	91		92	90	88	86
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82	79	76	74
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73	69	65	63
4	85	74	66	59	83	73	65	59	70	63	58		68	62	57		66	61	57	55
5	78	66	58	52	76	65	57	51	63	56	51		61	55	50		59	54	50	48
6	73	60	51	45	71	59	51	45	57	50	45		56	49	44		54	48	44	42
7	67	55	46	40	66	54	46	40	52	45	40		51	44	40		49	44	39	37
8	63	50	42	36	61	49	41	36	48	41	36		47	40	36		46	40	35	33
9	59	46	38	33	57	45	38	32	44	37	32		43	37	32		42	36	32	30
10	55	42	35	30	54	42	35	30	41	34	29		40	34	29		39	33	29	27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P#

CATALOG NUMBER: RL560WHZHA69-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.4	3.9
10°-20°	80.8	11.2
20°-30°	119.3	16.5
30°-40°	139.8	19.4
40°-50°	137.4	19.1
50°-60°	111.2	15.4
60°-70°	70.2	9.7
70°-80°	28.5	4.0
80°-90°	5.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	228.6	31.7
0°-40°	368.3	51.1
0°-60°	616.9	85.5
0°-90°	721.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	721.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	300	
5°	300	28
15°	287	81
25°	259	119
35°	224	140
45°	179	137
55°	124	111
65°	70	70
75°	26	29
85°	4	5
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: RL560WHZHA69-5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	299.5
2.5°	298.4
5°	299.5
7.5°	297.3
10°	293.9
12.5°	290.6
15°	287.2
17.5°	282.8
20°	273.8
22.5°	266.0
25°	259.3
27.5°	251.5
30°	242.5
32.5°	233.6
35°	223.5
37.5°	213.5
40°	202.3
42.5°	191.1
45°	178.8
47.5°	165.4
50°	152.0
52.5°	138.6
55°	124.1
57.5°	110.6
60°	97.2
62.5°	83.8
65°	70.4
67.5°	58.1
70°	46.9
72.5°	35.8
75°	25.7
77.5°	17.9
80°	11.2
82.5°	7.8
85°	4.5
87.5°	2.2
90°	0.0

(END OF REPORT)