

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P286932

Luminaire Tested: **HLC6099301EWH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P286932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1901-118-1)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: HLC6099301EWH
Description: HALO HLC 6 INCH SELECTABLE CCT LED FIXTURE
Light Source: (14) 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 925.0 lumens
Efficiency: N/A
Efficacy: 58.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.38
Luminous Opening: Vertical Cylinder (Dia: 0.38' x H: 0.04')
CIE Type: Direct

Input Watts (W): 15.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P286932
CATALOG NUMBER: HLC6099301EWH

Luminous Intensity Polar Plot





TEST NUMBER: P286932

CATALOG NUMBER: HLC6099301EWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	99
1	108	103	99	95	105	101	97	93	96	93	90		92	90	87		89	86	84	82
2	98	89	82	76	95	88	81	75	84	78	74		80	76	72		77	74	70	68
3	89	78	70	63	87	77	69	63	74	67	61		71	65	60		68	63	59	57
4	82	69	60	53	79	68	59	53	65	58	52		63	57	51		61	55	51	48
5	75	62	53	46	73	61	52	46	58	51	45		56	50	44		54	49	44	42
6	69	56	46	40	67	55	46	40	53	45	39		51	44	39		49	43	39	36
7	64	50	41	35	62	49	41	35	48	40	35		46	40	34		45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31		42	36	31		41	35	31	29
9	56	42	34	28	54	41	34	28	40	33	28		39	32	28		38	32	28	26
10	52	39	31	25	51	38	31	25	37	30	25		36	30	25		35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30358
5°	30005
10°	29507
15°	29047
20°	28594
25°	28064
30°	27518
35°	26825
40°	26179
45°	25429
50°	24534
55°	23535
60°	22387
65°	20789
70°	18693
75°	16166
80°	13110
85°	9614



TEST NUMBER: P286932

CATALOG NUMBER: HLC6099301EWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.5	3.2
10°-20°	84.4	9.1
20°-30°	128.2	13.9
30°-40°	155.2	16.8
40°-50°	162.3	17.5
50°-60°	148.9	16.1
60°-70°	116.0	12.5
70°-80°	69.8	7.5
80°-90°	26.0	2.8
90°-100°	4.4	0.5
100°-110°	0.4	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.1	26.2
0°-40°	397.2	42.9
0°-60°	708.4	76.6
0°-90°	920.2	99.5
90°-120°	4.8	0.5
90°-150°	4.8	0.5
90°-180°	5.0	0.5
0°-180°	925.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	312	
5°	310	29
15°	299	84
25°	278	128
35°	248	155
45°	211	162
55°	166	149
65°	118	116
75°	66	70
85°	22	22
90°	10	6
95°	3	2
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P286932

CATALOG NUMBER: HLC6099301EWH

CANDELA DISTRIBUTION (FULL):

0°	
0°	311.5
2.5°	311.5
5°	310.5
7.5°	308.6
10°	305.6
12.5°	302.7
15°	298.8
17.5°	294.8
20°	289.9
22.5°	284.1
25°	278.2
27.5°	271.3
30°	264.5
32.5°	256.6
35°	247.8
37.5°	239.0
40°	230.2
42.5°	220.4
45°	210.6
47.5°	199.8
50°	189.1
52.5°	178.3
55°	166.5
57.5°	154.8
60°	143.0
62.5°	130.3
65°	117.5
67.5°	103.8
70°	91.1
72.5°	78.4
75°	65.6
77.5°	53.9
80°	42.1
82.5°	31.3
85°	22.5
87.5°	15.7
90°	9.8
92.5°	5.9
95°	2.9
97.5°	2.0
100°	1.0
102.5°	1.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P286932

CATALOG NUMBER: HLC6099301EWH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)