

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P895717

Luminaire Tested: **RAWZC610-3500K**

Issue Date: 11/14/2024

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.


Test Information

Test Method: LM-79-08
 Report Number: P895717
 Test Lab:
 Issue Date: 11/14/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: RAWZC610-3500K
 Description: 6IN ADJUSTABLE WiZ SELECTABLE CCT
 Light Source: WiZ SELECTABLE 90CRI / 3500K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 1065.0 lumens
 Efficiency: N/A
 Efficacy: 105.4 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.2
 Luminous Opening: Circular (Dia: 0.5' x H: 0')
 CIE Type: Direct


Input Watts (W): 10.1
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Measurement		Calibration Due Date	
Instrument	Identification		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P895717
CATALOG NUMBER: RAWZC610-3500K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ···· 90°-270° - · - · 135°-315°

TEST NUMBER: P895717
 CATALOG NUMBER: RAWZC610-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	97	97	97	87		
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87	87	87	84	84	84	74		
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	74	74	74	71	71	71	64		
3	93	84	76	71	91	82	75	70	79	74	69	77	72	68	74	70	66	64	64	64	61	61	61	56		
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56	56	56	53	53	53	44		
5	80	68	60	53	78	67	59	53	65	58	53	63	57	52	61	56	52	50	50	50	47	47	47	36		
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44	44	44	42	42	42	32		
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40	40	40	38	38	38	27		
8	64	52	44	38	63	51	43	38	50	43	38	49	42	38	47	42	37	36	36	36	34	34	34	24		
9	60	48	40	35	59	47	40	35	46	39	34	45	39	34	44	38	34	32	32	32	32	32	32	20		
10	57	44	37	32	56	44	37	32	43	36	32	42	36	31	41	35	31	30	30	30	30	30	30	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28145	28145	28145	28145
5°	28054	28175	28109	27905
10°	27683	28017	27850	27493
15°	27100	27656	27424	26901
20°	26200	27075	26795	26048
25°	24951	26185	25907	24866
30°	23440	24979	24744	23428
35°	21670	23503	23316	21770
40°	19780	21834	21683	19980
45°	17831	20025	19777	18103
50°	15889	18149	17833	16196
55°	14078	16315	15971	14413
60°	12444	14626	14275	12773
65°	10935	13088	12686	11233
70°	9457	11653	11124	9617
75°	7900	10167	9447	7837
80°	6093	8587	7577	5714
85°	3837	6793	5284	2768

TEST NUMBER: P895717
 CATALOG NUMBER: RAWZC610-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.3	4.5
10°-20°	135.1	12.7
20°-30°	193.4	18.2
30°-40°	210.5	19.8
40°-50°	188.6	17.7
50°-60°	142.9	13.4
60°-70°	92.1	8.7
70°-80°	44.7	4.2
80°-90°	9.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	376.8	35.4
0°-40°	587.3	55.1
0°-60°	918.7	86.3
0°-90°	1065.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1065.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	513	513	513	513	513	
5°	510	512	511	507	510	48
15°	478	487	483	474	478	134
25°	412	433	428	411	412	189
35°	324	351	348	325	324	202
45°	230	258	255	234	230	177
55°	147	171	167	151	147	132
65°	84	101	98	87	84	84
75°	37	48	45	37	37	40
85°	6	11	8	4	6	8
90°	0	0	0	0	0	

TEST NUMBER: P895717
 CATALOG NUMBER: RAWZC610-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	513.4	513.4	513.4	513.4	513.4	513.4	513.4	513.4	513.4	513.4	513.4
0.5°	514.0	513.4	512.9	513.0	513.4	513.6	513.8	514.2	514.2	513.3	512.7
1°	513.8	513.4	513.0	513.0	513.4	513.8	514.1	514.3	514.0	513.3	512.5
1.5°	513.6	513.2	512.9	513.1	513.6	513.8	514.0	514.2	513.9	512.9	512.2
2°	513.2	513.1	512.9	513.0	513.4	513.8	514.1	514.1	513.7	512.8	511.8
2.5°	512.9	512.8	512.6	513.0	513.5	513.7	514.0	513.9	513.4	512.2	511.2
3°	512.4	512.4	512.4	512.8	513.2	513.7	513.9	513.5	513.0	511.9	510.7
3.5°	511.8	512.0	511.8	512.6	513.1	513.4	513.6	513.1	512.7	511.3	510.2
4°	511.2	511.4	511.5	512.2	512.7	513.1	513.3	512.7	512.1	510.8	509.4
4.5°	510.3	510.8	511.0	511.8	512.4	512.9	512.9	512.3	511.5	510.1	508.7
5°	509.8	510.1	510.4	511.4	512.0	512.4	512.5	511.5	510.8	509.4	507.7
5.5°	508.7	509.3	509.8	510.7	511.5	511.9	512.0	511.0	510.2	508.5	506.9
6°	507.9	508.4	509.0	510.2	510.8	511.3	511.3	510.2	509.3	507.6	505.9
6.5°	506.7	507.6	508.3	509.4	510.2	510.7	510.6	509.5	508.4	506.7	504.9
7°	505.7	506.5	507.3	508.6	509.5	509.9	510.0	508.5	507.6	505.6	503.7
7.5°	504.5	505.4	506.4	507.7	508.5	509.2	509.1	507.6	506.5	504.6	502.5
8°	503.3	504.3	505.2	506.8	507.6	508.2	508.2	506.6	505.4	503.4	500.9
8.5°	501.9	503.0	504.3	505.8	506.7	507.4	507.3	505.6	504.3	502.2	499.8
9°	500.4	501.8	503.0	504.8	505.6	506.2	506.2	504.4	503.0	500.9	498.6
9.5°	499.0	500.2	501.8	503.5	504.6	505.2	505.1	503.2	501.8	499.6	496.9
10°	497.3	498.8	500.3	502.3	503.3	503.9	504.0	502.1	500.3	498.1	495.6
10.5°	495.8	497.1	498.9	501.0	502.1	502.8	502.7	500.6	499.0	496.6	494.0
11°	494.1	495.6	497.4	499.6	500.7	501.4	501.4	499.2	497.3	495.1	492.4
11.5°	492.2	493.9	495.9	498.1	499.3	499.7	499.9	497.7	496.0	493.5	490.6
12°	490.3	492.1	494.3	496.2	497.8	498.6	498.5	496.2	494.2	491.7	488.9
12.5°	488.5	490.2	492.5	495.0	496.3	497.1	496.9	494.5	492.7	490.0	487.1
13°	486.3	488.2	490.7	493.3	494.6	495.5	495.3	492.9	490.8	488.3	485.3
13.5°	484.3	486.3	488.9	491.6	493.0	493.9	493.7	491.1	489.1	486.3	483.3
14°	482.0	484.1	487.1	489.8	491.3	492.1	491.8	489.2	487.1	484.4	481.2
14.5°	479.8	482.0	485.0	487.9	489.2	490.2	490.1	487.3	485.2	482.2	479.0
15°	477.5	479.6	482.9	486.0	487.3	488.4	488.2	485.4	483.2	480.3	476.9
15.5°	475.0	477.4	480.7	483.9	485.4	486.4	486.3	483.4	481.1	478.1	474.6
16°	472.5	474.9	478.3	481.8	483.4	484.5	484.2	481.2	478.9	475.8	472.3
16.5°	469.8	472.5	476.0	479.6	481.3	482.4	482.3	479.0	476.7	473.5	470.0
17°	467.2	469.8	473.6	477.4	479.0	480.2	480.1	476.8	474.5	471.1	467.4
17.5°	464.3	467.2	471.1	474.9	476.7	478.1	478.0	474.5	472.1	468.6	464.9
18°	461.5	464.2	468.5	472.6	474.3	475.7	475.6	472.1	469.7	466.1	462.3
18.5°	458.4	461.5	465.8	469.8	471.9	473.3	473.2	469.7	467.2	463.5	459.6
19°	455.5	458.5	462.9	467.4	469.4	470.8	470.7	467.2	464.6	460.8	456.8
19.5°	452.3	455.5	460.1	464.5	466.8	468.4	468.4	464.6	462.0	458.1	453.8
20°	449.1	452.4	457.1	461.9	464.1	465.7	465.7	461.9	459.3	455.2	450.9
20.5°	445.9	449.2	454.2	459.0	461.3	463.0	463.1	459.1	456.5	452.4	447.8
21°	442.4	446.0	451.0	456.0	458.5	460.2	460.1	456.3	453.6	449.4	444.7
21.5°	438.9	442.7	447.8	453.0	455.5	457.3	457.4	453.4	450.7	446.3	441.4
22°	435.3	439.3	444.6	449.9	452.6	454.3	454.4	450.4	447.7	443.2	438.3

TEST NUMBER: P895717
 CATALOG NUMBER: RAWZC610-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	431.8	435.7	441.0	446.8	449.5	451.4	451.5	447.3	444.7	440.2	434.9
23°	427.9	432.3	437.9	443.6	446.3	448.2	448.4	444.3	441.4	436.8	431.7
23.5°	424.3	428.5	434.4	440.3	443.2	445.1	445.3	441.0	438.3	433.6	428.2
24°	420.5	425.0	431.0	436.9	439.7	441.6	442.0	437.8	435.1	430.3	424.8
24.5°	416.7	421.2	427.3	433.4	436.3	438.3	438.6	434.4	431.7	426.9	421.1
25°	412.5	417.2	423.6	429.9	432.9	435.0	435.3	431.1	428.3	423.4	417.5
25.5°	408.8	413.4	419.7	426.3	429.4	431.5	431.9	427.7	424.9	419.8	413.9
26°	404.4	409.4	416.0	422.5	425.7	428.1	428.4	424.2	421.3	416.2	410.1
26.5°	400.6	405.4	412.1	418.9	422.0	424.4	424.9	420.4	417.7	412.5	406.3
27°	396.3	401.3	408.3	414.9	418.2	420.6	421.3	417.0	414.1	408.9	402.5
27.5°	392.1	397.2	404.1	411.3	414.5	416.6	417.6	413.3	410.3	404.7	398.6
28°	387.7	393.0	400.2	407.3	410.6	413.2	413.8	409.7	406.5	401.1	394.7
28.5°	383.5	388.7	396.0	403.3	406.7	409.2	410.1	405.8	402.8	397.3	390.7
29°	379.2	384.4	392.0	399.2	402.8	405.4	406.3	402.0	398.9	393.4	386.6
29.5°	374.7	380.1	387.7	395.2	398.6	401.3	402.5	398.0	394.9	389.4	382.5
30°	370.3	375.7	383.5	391.0	394.6	397.4	398.4	394.0	390.9	385.3	378.3
30.5°	365.9	371.4	379.3	386.9	390.4	393.2	394.5	390.1	386.9	381.2	374.3
31°	361.2	366.8	374.8	382.6	386.3	389.2	390.4	386.0	382.8	377.0	370.0
31.5°	356.6	362.3	370.5	378.2	382.2	385.0	386.3	381.9	378.7	372.9	365.8
32°	352.1	357.8	366.0	374.0	377.7	380.8	382.2	377.7	374.6	368.7	361.4
32.5°	347.5	353.1	361.5	369.6	373.4	376.6	377.9	373.5	370.3	364.2	357.1
33°	342.7	348.5	357.0	365.1	369.1	372.3	373.7	369.1	366.1	360.1	352.8
33.5°	338.2	343.9	352.6	360.8	364.7	367.9	369.4	364.9	361.7	355.7	348.4
34°	333.5	339.3	348.0	356.1	360.3	363.6	365.1	360.6	357.5	351.4	343.9
34.5°	328.8	334.6	343.4	351.8	355.8	359.1	360.7	356.3	353.1	347.0	339.5
35°	323.8	329.9	338.8	347.2	351.2	354.7	356.2	351.9	348.4	342.6	334.9
35.5°	319.2	325.2	334.1	342.5	346.8	350.3	351.8	347.5	344.3	338.1	330.6
36°	314.4	320.6	329.5	337.9	342.3	345.7	347.4	343.1	339.8	333.7	326.0
36.5°	309.7	315.8	324.7	333.4	337.6	341.2	342.8	338.5	335.3	329.1	321.3
37°	305.0	311.1	320.2	328.8	332.9	336.7	338.4	333.9	330.8	324.6	316.8
37.5°	300.2	306.4	315.5	324.1	328.4	332.0	333.8	329.4	326.4	320.0	312.3
38°	295.4	301.6	310.7	319.3	323.7	327.4	329.3	324.6	321.6	315.6	307.8
38.5°	290.6	296.9	305.7	314.7	319.1	322.8	324.6	320.3	317.1	310.8	303.2
39°	285.9	292.1	301.3	310.1	314.4	318.2	320.1	315.7	312.5	306.4	298.5
39.5°	281.1	287.5	296.7	305.3	309.6	313.5	315.5	311.0	307.8	301.7	293.9
40°	276.4	282.7	291.9	300.7	305.1	308.8	310.8	306.4	303.0	297.1	289.3
40.5°	271.7	278.0	287.1	295.9	300.3	304.3	306.1	301.7	298.3	292.2	284.7
41°	267.1	273.2	282.5	291.2	295.6	299.4	301.5	297.0	293.6	287.5	280.0
41.5°	262.3	268.6	277.9	286.5	291.0	294.8	296.9	292.2	288.9	282.9	275.4
42°	257.6	264.0	273.1	281.8	286.3	290.3	292.2	287.4	283.9	278.2	270.7
42.5°	253.0	259.3	268.3	277.1	281.6	285.5	287.5	282.8	279.3	273.3	266.1
43°	248.5	254.6	263.9	272.6	277.0	281.0	283.0	277.8	274.4	268.6	261.5
43.5°	243.8	250.0	259.4	267.9	272.3	276.1	278.2	273.1	269.7	264.0	256.8
44°	239.2	245.3	254.6	263.3	267.6	271.7	273.4	268.2	264.9	259.1	252.1
44.5°	234.7	240.9	250.1	258.6	262.9	267.0	268.8	263.5	260.1	254.5	247.5

TEST NUMBER: P895717
 CATALOG NUMBER: RAWZC610-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	230.0	236.3	245.6	254.2	258.3	262.4	264.2	258.7	255.1	249.7	242.9
45.5°	225.5	231.7	241.1	249.4	253.8	257.6	259.4	254.0	250.5	245.0	238.4
46°	221.0	227.2	236.5	244.8	249.1	253.1	254.6	249.1	245.8	240.3	233.8
46.5°	216.5	222.7	231.9	240.3	244.4	248.4	249.9	244.4	241.1	235.8	229.2
47°	212.0	218.2	227.4	235.8	239.9	243.7	245.2	239.7	236.2	231.1	224.7
47.5°	207.7	213.7	222.9	231.1	235.3	239.0	240.5	235.2	231.8	226.6	220.2
48°	203.3	209.3	218.5	226.6	230.7	234.6	236.0	230.5	227.2	222.1	215.8
48.5°	198.9	204.9	214.0	222.2	226.2	229.9	231.2	225.9	222.6	217.4	211.3
49°	194.7	200.6	209.6	217.6	221.7	225.3	226.8	221.3	218.1	213.1	206.9
49.5°	190.5	196.4	205.1	213.2	217.2	220.8	222.2	216.8	213.5	208.7	202.6
50°	186.3	192.0	201.0	209.0	212.8	216.4	217.5	212.2	209.1	204.3	198.4
50.5°	182.2	187.8	196.6	204.4	208.4	211.8	213.1	207.9	204.7	199.9	194.0
51°	178.0	183.7	192.4	200.1	203.9	207.4	208.7	203.6	200.3	195.7	190.0
51.5°	174.0	179.7	188.0	195.8	199.6	203.2	204.3	199.1	196.0	191.4	185.7
52°	170.0	175.6	184.1	191.7	195.5	198.8	200.0	194.9	191.6	187.3	181.6
52.5°	166.2	171.6	180.0	187.5	191.1	194.5	195.7	190.6	187.6	183.1	177.6
53°	162.1	167.6	176.0	183.3	186.9	190.3	191.3	186.4	183.3	179.0	173.6
53.5°	158.4	163.8	171.8	179.2	182.7	186.1	187.2	182.3	179.3	174.9	169.6
54°	154.6	159.9	167.9	175.2	178.8	182.0	183.0	178.1	175.1	170.9	165.7
54.5°	150.8	156.0	163.9	171.2	174.5	177.8	178.9	174.1	171.3	167.0	161.9
55°	147.3	152.3	160.2	167.2	170.7	174.0	174.8	170.1	167.1	163.1	158.1
55.5°	143.6	148.7	156.4	163.4	166.6	169.9	170.8	166.1	163.3	159.3	154.3
56°	140.1	145.1	152.6	159.5	162.9	165.9	166.8	162.2	159.4	155.4	150.5
56.5°	136.6	141.5	149.0	155.7	158.8	162.0	163.0	158.4	155.7	151.7	147.0
57°	133.1	138.0	145.3	152.0	155.1	158.2	159.0	154.6	151.8	147.9	143.3
57.5°	129.7	134.5	141.7	148.2	151.3	154.4	155.3	150.7	148.1	144.4	139.8
58°	126.3	131.0	138.2	144.6	147.7	150.6	151.5	147.1	144.5	140.7	136.3
58.5°	123.1	127.6	134.7	141.0	144.0	147.0	147.9	143.5	140.9	137.2	132.8
59°	119.8	124.3	131.2	137.4	140.4	143.3	144.2	139.9	137.2	133.7	129.2
59.5°	116.6	121.0	127.8	134.0	136.9	139.8	140.5	136.3	133.8	130.1	125.9
60°	113.5	117.8	124.5	130.5	133.4	136.2	137.1	132.8	130.2	126.6	122.5
60.5°	110.4	114.6	121.2	127.0	129.9	132.7	133.5	129.3	126.8	123.3	119.2
61°	107.3	111.5	118.0	123.7	126.6	129.2	130.1	126.0	123.5	120.0	115.9
61.5°	104.2	108.4	114.6	120.4	123.2	125.9	126.6	122.6	120.1	116.6	112.7
62°	101.3	105.3	111.5	117.1	119.9	122.6	123.4	119.3	116.8	113.3	109.5
62.5°	98.4	102.4	108.3	113.9	116.6	119.2	120.0	116.0	113.4	110.2	106.3
63°	95.5	99.4	105.3	110.6	113.3	115.9	116.6	112.9	110.4	106.9	103.2
63.5°	92.7	96.4	102.3	107.6	110.2	112.8	113.5	109.6	107.1	103.7	100.1
64°	89.8	93.6	99.3	104.5	107.0	109.5	110.4	106.5	103.9	100.7	97.2
64.5°	87.0	90.7	96.3	101.4	104.0	106.5	107.2	103.4	100.8	97.6	94.2
65°	84.3	87.9	93.4	98.4	100.9	103.3	104.1	100.3	97.8	94.6	91.2
65.5°	81.7	85.2	90.6	95.4	97.9	100.3	101.1	97.3	94.6	91.6	88.3
66°	79.0	82.4	87.7	92.5	94.9	97.3	98.0	94.3	91.8	88.7	85.4
66.5°	76.4	79.7	84.9	89.6	91.9	94.4	95.0	91.3	88.9	85.8	82.6
67°	73.8	77.1	82.1	86.7	89.2	91.5	92.1	88.4	86.0	83.0	79.8

TEST NUMBER: P895717
 CATALOG NUMBER: RAWZC610-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	71.3	74.5	79.4	83.9	86.4	88.6	89.3	85.6	83.2	80.2	77.1
68°	68.7	71.9	76.7	81.2	83.6	85.8	86.6	82.8	80.4	77.4	74.3
68.5°	66.3	69.4	74.1	78.5	80.9	83.1	83.7	80.0	77.6	74.6	71.5
69°	63.9	66.9	71.4	75.8	78.1	80.3	81.0	77.2	74.7	71.8	69.0
69.5°	61.5	64.4	68.9	73.2	75.4	77.6	78.2	74.4	71.9	69.2	66.2
70°	59.0	62.0	66.3	70.5	72.7	74.9	75.5	71.7	69.4	66.6	63.7
70.5°	56.8	59.6	63.9	67.9	70.1	72.1	72.7	69.0	66.7	63.9	61.1
71°	54.5	57.3	61.4	65.3	67.5	69.4	70.0	66.3	64.1	61.4	58.7
71.5°	52.2	54.8	59.0	62.8	64.9	67.0	67.4	63.7	61.5	58.9	56.1
72°	49.9	52.6	56.6	60.3	62.4	64.3	64.8	61.2	58.9	56.4	53.7
72.5°	47.8	50.3	54.2	57.9	59.9	61.9	62.2	58.7	56.5	53.9	51.2
73°	45.7	48.1	51.9	55.5	57.4	59.3	59.7	56.2	54.0	51.5	48.9
73.5°	43.5	46.0	49.5	53.1	55.0	57.0	57.2	53.8	51.7	49.1	46.5
74°	41.3	43.8	47.3	50.8	52.6	54.5	54.7	51.4	49.2	46.8	44.2
74.5°	39.3	41.6	45.1	48.5	50.3	52.1	52.3	49.0	46.8	44.4	41.9
75°	37.3	39.5	42.9	46.3	48.0	49.7	49.9	46.6	44.6	42.2	39.7
75.5°	35.4	37.5	40.8	44.0	45.7	47.5	47.6	44.3	42.3	40.0	37.5
76°	33.5	35.5	38.7	41.8	43.5	45.1	45.3	42.0	40.1	37.8	35.4
76.5°	31.6	33.6	36.6	39.7	41.3	42.9	43.1	39.9	37.9	35.7	33.3
77°	29.8	31.7	34.5	37.6	39.1	40.7	40.8	37.7	35.8	33.5	31.2
77.5°	27.9	29.9	32.6	35.5	37.1	38.6	38.6	35.6	33.7	31.5	29.2
78°	26.0	28.0	30.7	33.5	35.0	36.4	36.5	33.4	31.6	29.5	27.3
78.5°	24.3	26.1	28.8	31.6	33.0	34.3	34.3	31.4	29.7	27.6	25.3
79°	22.6	24.3	27.0	29.7	30.9	32.3	32.3	29.4	27.7	25.6	23.5
79.5°	20.9	22.6	25.1	27.8	29.0	30.3	30.3	27.5	25.8	23.8	21.7
80°	19.3	20.9	23.3	25.8	27.2	28.3	28.3	25.5	24.0	22.0	20.0
80.5°	17.6	19.3	21.6	24.0	25.3	26.4	26.4	23.7	22.2	20.2	18.3
81°	16.2	17.7	20.0	22.3	23.4	24.6	24.5	21.9	20.4	18.5	16.7
81.5°	14.7	16.2	18.3	20.5	21.7	22.7	22.7	20.1	18.7	16.9	15.0
82°	13.4	14.7	16.8	18.9	20.0	21.0	20.9	18.4	17.1	15.3	13.6
82.5°	12.1	13.4	15.3	17.3	18.3	19.4	19.3	16.9	15.4	13.8	12.0
83°	10.8	12.0	13.9	15.8	16.8	17.6	17.5	15.2	13.9	12.2	10.7
83.5°	9.5	10.8	12.4	14.3	15.1	16.1	16.0	13.7	12.4	10.9	9.4
84°	8.4	9.5	11.1	12.8	13.7	14.6	14.5	12.2	11.0	9.5	8.2
84.5°	7.2	8.3	9.7	11.5	12.1	13.0	12.9	10.8	9.6	8.3	6.9
85°	6.1	7.1	8.6	10.1	10.8	11.6	11.5	9.5	8.4	7.0	5.7
85.5°	5.0	6.0	7.3	8.8	9.5	10.2	10.2	8.3	7.1	5.8	4.4
86°	4.0	4.9	6.3	7.5	8.4	9.0	9.1	7.0	5.9	4.5	3.5
86.5°	3.3	4.0	5.1	6.4	7.1	7.8	7.8	5.8	4.6	3.6	2.6
87°	2.5	3.3	4.1	5.3	5.9	6.6	6.6	4.5	3.7	2.7	1.8
87.5°	1.8	2.5	3.3	4.2	4.7	5.4	5.3	3.6	2.8	1.9	1.2
88°	1.1	1.7	2.5	3.4	3.8	4.1	4.0	2.7	2.0	1.3	0.5
88.5°	0.3	1.1	1.8	2.6	2.9	3.3	3.1	1.9	1.3	0.5	0.1
89°	0.1	0.3	1.1	1.8	2.1	2.5	2.3	1.3	0.5	0.1	0.0
89.5°	0.0	0.1	0.3	1.1	1.3	1.6	1.5	0.4	0.1	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P895717
CATALOG NUMBER: RAWZC610-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P895717
 CATALOG NUMBER: RAWZC610-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	513.4	513.4	513.4	513.4	513.4	513.4
0.5°	512.6	512.9	513.0	513.2	513.9	514.0
1°	512.1	512.6	512.7	512.9	513.7	513.8
1.5°	511.8	512.2	512.3	512.4	513.3	513.6
2°	511.2	511.7	511.7	512.0	512.9	513.2
2.5°	510.8	511.0	511.1	511.2	512.5	512.9
3°	510.2	510.4	510.3	510.7	512.0	512.4
3.5°	509.1	509.7	509.7	509.9	511.3	511.8
4°	508.7	508.9	508.8	509.2	510.5	511.2
4.5°	507.8	508.0	507.9	508.2	509.8	510.3
5°	507.0	507.1	507.0	507.3	508.9	509.8
5.5°	505.9	506.1	505.8	505.7	508.0	508.7
6°	504.9	504.9	504.8	505.0	506.9	507.9
6.5°	503.7	503.9	503.5	503.9	505.8	506.7
7°	502.5	502.5	502.3	502.6	504.7	505.7
7.5°	501.3	501.4	500.9	501.3	503.4	504.5
8°	499.9	499.9	499.6	499.8	502.1	503.3
8.5°	498.6	498.5	497.9	498.4	500.6	501.9
9°	497.1	496.9	496.6	496.8	499.2	500.4
9.5°	495.6	495.5	494.8	495.2	497.6	499.0
10°	494.1	493.9	493.3	493.5	496.0	497.3
10.5°	492.4	492.1	491.6	491.8	494.3	495.8
11°	490.7	490.4	489.8	490.0	492.5	494.1
11.5°	488.9	488.7	487.9	488.2	490.5	492.2
12°	487.1	486.7	486.1	486.2	488.9	490.3
12.5°	485.2	484.7	484.0	484.1	486.7	488.5
13°	482.7	482.8	482.0	482.0	484.8	486.3
13.5°	481.0	480.7	479.7	479.9	482.2	484.3
14°	478.9	478.6	477.6	477.7	480.4	482.0
14.5°	476.7	476.2	475.3	475.3	478.1	479.8
15°	474.5	474.0	473.0	472.9	475.6	477.5
15.5°	472.1	471.5	470.4	470.3	473.1	475.0
16°	469.8	469.2	467.9	467.7	470.7	472.5
16.5°	467.1	466.6	465.4	465.0	468.0	469.8
17°	464.7	464.1	462.6	462.3	465.4	467.2
17.5°	462.0	461.4	459.9	459.5	462.6	464.3
18°	459.3	458.6	457.0	456.5	459.6	461.5
18.5°	456.3	455.7	454.2	453.5	456.7	458.4
19°	453.6	452.7	451.0	450.1	453.7	455.5
19.5°	450.4	449.6	447.9	447.1	450.5	452.3
20°	447.4	446.5	444.7	443.6	447.2	449.1
20.5°	444.1	443.3	441.3	440.4	443.9	445.9
21°	441.0	440.0	438.1	436.8	440.4	442.4
21.5°	437.6	436.5	434.6	433.2	436.9	438.9
22°	434.3	433.1	431.0	429.8	433.3	435.3

TEST NUMBER: P895717
 CATALOG NUMBER: RAWZC610-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	430.9	429.6	427.5	426.2	429.8	431.8
23°	427.6	426.0	423.8	422.4	426.0	427.9
23.5°	423.8	422.3	420.1	418.8	422.2	424.3
24°	420.1	418.7	416.3	414.8	418.4	420.5
24.5°	416.6	414.9	412.5	411.0	414.5	416.7
25°	412.8	411.1	408.5	407.0	410.6	412.5
25.5°	409.0	407.1	404.7	403.0	406.5	408.8
26°	405.3	403.4	400.6	399.0	402.4	404.4
26.5°	401.2	399.3	396.2	394.9	398.3	400.6
27°	397.5	395.4	392.5	390.7	394.2	396.3
27.5°	393.2	391.1	388.3	386.6	390.2	392.1
28°	389.3	387.1	384.1	382.3	385.6	387.7
28.5°	385.1	382.9	379.9	377.9	381.4	383.5
29°	381.0	378.5	375.6	373.6	377.0	379.2
29.5°	376.8	374.4	371.4	369.3	372.7	374.7
30°	372.5	370.1	366.9	364.9	368.1	370.3
30.5°	368.3	365.8	362.6	360.5	363.7	365.9
31°	364.0	361.4	358.1	355.8	359.0	361.2
31.5°	359.6	357.1	353.6	351.3	354.6	356.6
32°	355.2	352.6	349.1	346.8	350.0	352.1
32.5°	350.8	348.0	344.6	342.2	345.5	347.5
33°	346.4	343.6	340.1	337.7	340.7	342.7
33.5°	341.8	339.2	335.4	333.0	336.2	338.2
34°	337.3	334.5	331.0	328.4	331.4	333.5
34.5°	332.8	329.9	326.2	323.7	326.9	328.8
35°	328.3	325.3	321.5	319.0	322.1	323.8
35.5°	323.7	320.9	316.9	314.4	317.3	319.2
36°	319.0	316.2	312.4	309.6	312.6	314.4
36.5°	314.6	311.5	307.7	305.0	307.9	309.7
37°	310.0	306.9	303.0	300.2	303.2	305.0
37.5°	305.4	302.3	298.4	295.5	298.4	300.2
38°	300.7	297.6	293.7	290.9	293.7	295.4
38.5°	296.2	293.1	289.0	286.1	289.0	290.6
39°	291.6	288.5	284.5	281.5	284.2	285.9
39.5°	287.0	283.8	279.8	276.8	279.6	281.1
40°	282.4	279.2	275.2	272.1	274.9	276.4
40.5°	277.7	274.6	270.5	267.6	270.2	271.7
41°	273.2	270.1	266.0	263.0	265.5	267.1
41.5°	268.5	265.3	261.3	258.4	260.9	262.3
42°	264.0	260.7	256.8	253.9	256.4	257.6
42.5°	259.5	256.3	252.2	249.4	251.8	253.0
43°	254.7	251.8	247.7	244.8	247.1	248.5
43.5°	250.2	247.1	243.1	240.3	242.5	243.8
44°	245.7	242.6	238.6	235.8	238.0	239.2
44.5°	241.1	238.1	234.0	231.2	233.4	234.7

TEST NUMBER: P895717
 CATALOG NUMBER: RAWZC610-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	236.6	233.5	229.6	226.7	229.0	230.0
45.5°	232.1	229.0	225.1	222.3	224.3	225.5
46°	227.5	224.6	220.7	217.8	219.8	221.0
46.5°	222.9	220.0	216.1	213.4	215.3	216.5
47°	218.5	215.7	211.7	209.1	211.1	212.0
47.5°	214.2	211.3	207.4	204.6	206.5	207.7
48°	209.7	206.8	203.2	200.3	202.1	203.3
48.5°	205.5	202.5	198.7	196.1	197.9	198.9
49°	201.1	198.4	194.5	191.9	193.7	194.7
49.5°	196.9	194.1	190.5	187.8	189.4	190.5
50°	192.6	189.9	186.3	183.6	185.3	186.3
50.5°	188.5	185.8	182.3	179.5	181.2	182.2
51°	184.4	181.7	178.1	175.4	177.2	178.0
51.5°	180.2	177.6	174.3	171.5	173.0	174.0
52°	176.3	173.7	170.2	167.5	169.2	170.0
52.5°	172.3	169.7	166.4	163.8	165.3	166.2
53°	168.3	165.8	162.4	159.8	161.4	162.1
53.5°	164.4	162.0	158.6	156.0	157.6	158.4
54°	160.7	158.3	154.9	152.3	153.8	154.6
54.5°	156.9	154.5	151.1	148.7	150.2	150.8
55°	153.2	150.8	147.5	145.0	146.5	147.3
55.5°	149.5	147.2	144.0	141.6	142.9	143.6
56°	145.8	143.6	140.3	137.9	139.5	140.1
56.5°	142.3	139.9	137.0	134.6	135.9	136.6
57°	138.7	136.5	133.4	131.0	132.5	133.1
57.5°	135.2	133.0	130.0	127.7	129.1	129.7
58°	131.9	129.6	126.6	124.4	125.7	126.3
58.5°	128.4	126.4	123.4	121.2	122.4	123.1
59°	125.1	123.0	120.1	117.9	119.2	119.8
59.5°	121.8	119.7	116.8	114.7	116.0	116.6
60°	118.5	116.5	113.6	111.6	112.9	113.5
60.5°	115.3	113.2	110.5	108.3	109.8	110.4
61°	112.1	110.1	107.4	105.3	106.7	107.3
61.5°	109.0	107.0	104.4	102.4	103.6	104.2
62°	105.9	104.1	101.4	99.4	100.7	101.3
62.5°	102.7	101.0	98.3	96.5	97.8	98.4
63°	99.8	98.0	95.4	93.5	94.8	95.5
63.5°	96.8	95.1	92.5	90.7	92.0	92.7
64°	93.9	92.1	89.6	87.9	89.3	89.8
64.5°	91.0	89.3	86.9	85.0	86.5	87.0
65°	88.1	86.6	84.1	82.4	83.7	84.3
65.5°	85.3	83.8	81.3	79.6	81.1	81.7
66°	82.5	81.0	78.6	77.0	78.3	79.0
66.5°	79.7	78.3	75.9	74.3	75.7	76.4
67°	77.0	75.6	73.3	71.7	73.2	73.8

TEST NUMBER: P895717
 CATALOG NUMBER: RAWZC610-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	74.2	73.0	70.7	69.2	70.6	71.3
68°	71.4	70.3	68.1	66.6	68.0	68.7
68.5°	68.8	67.7	65.6	64.2	65.6	66.3
69°	66.2	65.1	63.1	61.7	63.1	63.9
69.5°	63.6	62.6	60.7	59.2	60.7	61.5
70°	61.1	60.0	58.2	57.0	58.3	59.0
70.5°	58.5	57.4	55.9	54.6	56.0	56.8
71°	56.1	55.1	53.5	52.2	53.7	54.5
71.5°	53.6	52.7	51.2	49.9	51.4	52.2
72°	51.2	50.3	48.9	47.7	49.2	49.9
72.5°	48.8	48.0	46.6	45.5	47.0	47.8
73°	46.5	45.8	44.3	43.3	44.8	45.7
73.5°	44.2	43.5	42.1	41.2	42.7	43.5
74°	42.0	41.3	40.0	39.0	40.6	41.3
74.5°	39.8	39.1	37.9	36.9	38.6	39.3
75°	37.6	37.0	35.8	35.0	36.4	37.3
75.5°	35.5	34.9	34.2	33.1	34.5	35.4
76°	33.3	33.0	32.2	31.2	32.7	33.5
76.5°	31.3	31.0	30.1	29.3	30.8	31.6
77°	29.4	29.0	28.0	27.4	28.9	29.8
77.5°	27.4	27.1	26.0	25.4	27.1	27.9
78°	25.4	25.2	24.2	23.7	25.2	26.0
78.5°	23.6	23.3	22.4	21.9	23.5	24.3
79°	21.8	21.5	20.7	20.2	21.8	22.6
79.5°	20.0	19.8	19.0	18.6	20.0	20.9
80°	18.4	18.1	17.3	17.1	18.5	19.3
80.5°	16.7	16.5	15.8	15.5	17.0	17.6
81°	15.1	14.8	14.3	14.0	15.5	16.2
81.5°	13.6	13.3	12.7	12.6	14.1	14.7
82°	12.1	11.9	11.4	11.3	12.7	13.4
82.5°	10.7	10.5	10.0	9.9	11.4	12.1
83°	9.4	9.2	8.7	8.7	10.1	10.8
83.5°	8.2	7.8	7.4	7.4	8.9	9.5
84°	6.9	6.7	6.3	6.3	7.7	8.4
84.5°	5.8	5.5	5.1	5.1	6.5	7.2
85°	4.5	4.4	4.0	4.1	5.4	6.1
85.5°	3.5	3.4	3.2	3.2	4.3	5.0
86°	2.6	2.7	2.4	2.4	3.5	4.0
86.5°	1.9	1.9	1.6	1.6	2.7	3.3
87°	1.3	1.2	1.0	1.2	1.9	2.5
87.5°	0.5	0.4	0.2	0.8	1.2	1.8
88°	0.1	0.1	0.0	0.4	0.4	1.1
88.5°	0.0	0.0	0.0	0.0	0.2	0.3
89°	0.0	0.0	0.0	0.0	0.0	0.1
89.5°	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P895717
CATALOG NUMBER: RAWZC610-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)