

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643853

Luminaire Tested: ML5615LSWFL559FS1E - 593WB - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643853
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-51)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 593WB - 900LM - 3500K
Description: ML56 RR, 55D TIR OPTIC, 5" WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1184.4 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643853
CATALOG NUMBER: ML5615LSWFL559FS1E - 593WB - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643853

CATALOG NUMBER: ML5615LSWFL559FS1E - 593WB - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93																			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79																			
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	72																			
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	68	67																			
6	85	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62																			
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58																			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54																			
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50																			
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99418
5°	95194
10°	90283
15°	85052
20°	76951
25°	65614
30°	53552
35°	41949
40°	30379
45°	18878
50°	6742
55°	3633
60°	1831
65°	1382
70°	1454
75°	1281
80°	1455
85°	1902

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18878 cd/sqm



TEST NUMBER: P643853

CATALOG NUMBER: ML5615LSWFL559FS1E - 593WB - 900LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	9.5
10°-20°	289.8	24.5
20°-30°	344.0	29.0
30°-40°	270.9	22.9
40°-50°	127.3	10.7
50°-60°	25.6	2.2
60°-70°	7.7	0.6
70°-80°	4.9	0.4
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	746.1	63.0
0°-40°	1017.1	85.9
0°-60°	1169.9	98.8
0°-90°	1184.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1184.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1259	
5°	1201	112
15°	1041	290
25°	753	344
35°	435	271
45°	169	127
55°	26	26
65°	7	8
75°	4	5
85°	2	2
90°	0	



TEST NUMBER: P643853

CATALOG NUMBER: ML5615LSWFL559FS1E - 593WB - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1259.4
2.5°	1243.6
5°	1201.3
7.5°	1162.2
10°	1126.3
12.5°	1087.2
15°	1040.7
17.5°	982.6
20°	916.0
22.5°	838.9
25°	753.3
27.5°	667.8
30°	587.5
32.5°	510.3
35°	435.3
37.5°	361.3
40°	294.8
42.5°	233.5
45°	169.1
47.5°	94.0
50°	54.9
52.5°	38.0
55°	26.4
57.5°	18.0
60°	11.6
62.5°	8.5
65°	7.4
67.5°	6.3
70°	6.3
72.5°	5.3
75°	4.2
77.5°	4.2
80°	3.2
82.5°	2.1
85°	2.1
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)