

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643861

Luminaire Tested: ML5615LSWFL559FS1E - 594SNB - 1500LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643861
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-56)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 594SNB - 1500LM - 2700K
Description: ML56 RR, 55D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1771.1 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643861

CATALOG NUMBER: ML5615LSWFL559FS1E - 594SNB - 1500LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P643861

CATALOG NUMBER: ML5615LSWFL559FS1E - 594\$NB - 1500LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94				92																
2	107	101	97	93	105	100	96	92	96	93	90	93	91	88	91	88	87				85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80				78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73				72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68				66																
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63				61																
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58				57																
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54				53																
9	72	62	56	51	71	61	55	51	60	55	51	59	54	51	59	54	51				49																
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	47				46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145591
5°	139491
10°	132382
15°	125179
20°	113258
25°	95629
30°	77535
35°	60240
40°	44549
45°	29160
50°	13939
55°	7487
60°	4910
65°	4072
70°	3601
75°	2379
80°	1409
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29160 cd/sqm



TEST NUMBER: P643861

CATALOG NUMBER: ML5615LSWFL559FS1E - 594\$NB - 1500LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.6	9.3
10°-20°	426.3	24.1
20°-30°	502.4	28.4
30°-40°	391.6	22.1
40°-50°	200.2	11.3
50°-60°	54.2	3.1
60°-70°	22.3	1.3
70°-80°	8.6	0.5
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1093.3	61.7
0°-40°	1484.9	83.8
0°-60°	1739.3	98.2
0°-90°	1771.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1771.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1844	
5°	1760	165
15°	1532	426
25°	1098	502
35°	625	392
45°	261	200
55°	54	54
65°	22	22
75°	8	9
85°	0	1
90°	0	



TEST NUMBER: P643861

CATALOG NUMBER: ML5615LSWFL559FS1E - 594\$NB - 1500LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1844.3
2.5°	1821.0
5°	1760.3
7.5°	1701.2
10°	1651.5
12.5°	1597.0
15°	1531.7
17.5°	1447.8
20°	1348.2
22.5°	1231.6
25°	1097.9
27.5°	971.9
30°	850.6
32.5°	735.5
35°	625.1
37.5°	524.1
40°	432.3
42.5°	343.7
45°	261.2
47.5°	174.2
50°	113.5
52.5°	77.8
55°	54.4
57.5°	40.4
60°	31.1
62.5°	26.4
65°	21.8
67.5°	18.7
70°	15.6
72.5°	10.9
75°	7.8
77.5°	4.7
80°	3.1
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)