

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P328431

Luminaire Tested: **L815MED10FL930MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P328431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1905-290-12)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L815MED10FL930MB
Description: Medium, 1000lm, 45D, 3000K, black finish
Light Source: (1) 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1104.0 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.66
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P328431
CATALOG NUMBER: L815MED10FL930MB

Luminous Intensity Polar Plot





TEST NUMBER: P328431

CATALOG NUMBER: L815MED10FL930MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	79
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		82	78	76	74
6	91	83	77	73	89	82	77	73	81	76	73		79	75	72		78	74	72	70
7	87	79	73	69	86	78	73	69	77	72	69		76	72	69		75	71	68	67
8	84	75	70	66	82	74	69	66	73	69	66		72	68	65		72	68	65	64
9	80	72	66	63	79	71	66	63	70	66	62		69	65	62		69	65	62	61
10	77	69	63	60	76	68	63	60	67	63	60		67	62	59		66	62	59	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	234085
5°	228132
10°	220249
15°	205388
20°	163080
25°	84516
30°	41874
35°	21186
40°	13155
45°	9891
50°	8194
55°	6494
60°	5279
65°	4203
70°	3174
75°	1573
80°	355
85°	0



TEST NUMBER: P328431

CATALOG NUMBER: L815MED10FL930MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.4	15.7
10°-20°	437.9	39.7
20°-30°	304.3	27.6
30°-40°	97.2	8.8
40°-50°	45.1	4.1
50°-60°	27.6	2.5
60°-70°	14.5	1.3
70°-80°	3.9	0.4
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	915.6	82.9
0°-40°	1012.8	91.7
0°-60°	1085.5	98.3
0°-90°	1104.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1104.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1898	
5°	1842	173
15°	1608	438
25°	621	304
35°	141	97
45°	57	45
55°	30	28
65°	14	14
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P328431

CATALOG NUMBER: L815MED10FL930MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1897.8
2.5°	1877.8
5°	1842.5
7.5°	1805.4
10°	1758.5
12.5°	1702.7
15°	1608.4
17.5°	1468.2
20°	1242.4
22.5°	929.9
25°	621.0
27.5°	425.0
30°	294.0
32.5°	202.5
35°	140.7
37.5°	104.0
40°	81.7
42.5°	67.3
45°	56.7
47.5°	48.8
50°	42.7
52.5°	36.2
55°	30.2
57.5°	25.5
60°	21.4
62.5°	17.6
65°	14.4
67.5°	11.6
70°	8.8
72.5°	5.6
75°	3.3
77.5°	1.4
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)