

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P328456

Luminaire Tested: **L815MED20FL935MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P328456
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1905-290-12)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L815MED20FL935MB
Description: Medium, 2000lm, 45D, 3500K, black finish
Light Source: (1) 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2052.0 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.66
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 24.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P328456

CATALOG NUMBER: L815MED20FL935MB

Luminous Intensity Polar Plot





TEST NUMBER: P328456

CATALOG NUMBER: L815MED20FL935MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	79
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		82	78	76	74
6	91	83	77	73	89	82	77	73	81	76	73		79	75	72		78	74	72	70
7	87	79	73	69	86	78	73	69	77	72	69		76	72	69		75	71	68	67
8	84	75	70	66	82	74	69	66	73	69	66		72	68	65		72	68	65	64
9	80	72	66	63	79	71	66	63	70	66	62		69	65	62		69	65	62	61
10	77	69	63	60	76	68	63	60	67	63	60		67	62	59		66	62	59	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	435102
5°	424035
10°	409375
15°	381762
20°	303123
25°	157083
30°	77836
35°	39391
40°	24458
45°	18368
50°	15236
55°	12064
60°	9794
65°	7822
70°	5914
75°	2859
80°	639
85°	0



TEST NUMBER: P328456

CATALOG NUMBER: L815MED20FL935MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	322.3	15.7
10°-20°	813.9	39.7
20°-30°	565.7	27.6
30°-40°	180.7	8.8
40°-50°	83.8	4.1
50°-60°	51.3	2.5
60°-70°	27.0	1.3
70°-80°	7.3	0.4
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1701.8	82.9
0°-40°	1882.5	91.7
0°-60°	2017.7	98.3
0°-90°	2052.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2052.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3528	
5°	3425	322
15°	2990	814
25°	1154	566
35°	262	181
45°	105	84
55°	56	51
65°	27	27
75°	6	7
85°	0	0
90°	0	



TEST NUMBER: P328456

CATALOG NUMBER: L815MED20FL935MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3527.5
2.5°	3490.3
5°	3424.7
7.5°	3355.7
10°	3268.5
12.5°	3164.9
15°	2989.6
17.5°	2728.9
20°	2309.3
22.5°	1728.3
25°	1154.2
27.5°	789.9
30°	546.5
32.5°	376.4
35°	261.6
37.5°	193.4
40°	151.9
42.5°	125.2
45°	105.3
47.5°	90.6
50°	79.4
52.5°	67.3
55°	56.1
57.5°	47.5
60°	39.7
62.5°	32.8
65°	26.8
67.5°	21.6
70°	16.4
72.5°	10.4
75°	6.0
77.5°	2.6
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)