

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643970

Luminaire Tested: ML5615LSWFL559FS1E - 692W - 1500LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P643970  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-62)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSWFL559FS1E - 692W - 1500LM - 5000K  
Description: ML56 RR, 55D TIR OPTIC, 6" WHITE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1998.2 lumens  
Efficiency: N/A  
Efficacy: 116.9 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 17.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P643970  
CATALOG NUMBER: ML5615LSWFL559FS1E - 692W - 1500LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P643970

CATALOG NUMBER: ML5615LSWFL559FS1E - 692W - 1500LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85																
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79			79																
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72																
5	90	81	75	71	89	80	75	70	79	73	70	77	72	69	75	71	68	67			67																
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62			62																
7	81	71	65	60	79	70	64	60	69	63	60	68	63	59	67	62	59	57			57																
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			53																
9	73	62	56	52	71	62	56	52	61	55	52	60	55	51	59	55	51	50			50																
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47			47																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	115227
5°	110510
10°	104607
15°	98724
20°	89415
25°	76135
30°	62218
35°	48626
40°	36053
45°	23576
50°	10098
55°	4224
60°	2324
65°	1375
70°	1138
75°	1123
80°	1105
85°	1132

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 23576 cd/sqm



TEST NUMBER: P643970

CATALOG NUMBER: ML5615LSWFL559FS1E - 692W - 1500LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.7	9.4
10°-20°	484.2	24.2
20°-30°	574.9	28.8
30°-40°	455.1	22.8
40°-50°	231.3	11.6
50°-60°	47.0	2.4
60°-70°	11.3	0.6
70°-80°	5.1	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1246.9	62.4
0°-40°	1702.0	85.2
0°-60°	1980.4	99.1
0°-90°	1998.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1998.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2102	
5°	2008	188
15°	1740	484
25°	1259	575
35°	727	455
45°	304	231
55°	44	47
65°	11	11
75°	5	5
85°	2	1
90°	0	



TEST NUMBER: P643970

CATALOG NUMBER: ML5615LSWFL559FS1E - 692W - 1500LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2101.9
2.5°	2077.2
5°	2008.2
7.5°	1941.1
10°	1879.2
12.5°	1815.5
15°	1739.5
17.5°	1642.3
20°	1532.7
22.5°	1401.9
25°	1258.7
27.5°	1115.5
30°	982.9
32.5°	853.9
35°	726.6
37.5°	611.7
40°	503.8
42.5°	401.3
45°	304.1
47.5°	199.8
50°	118.4
52.5°	67.2
55°	44.2
57.5°	31.8
60°	21.2
62.5°	14.1
65°	10.6
67.5°	7.1
70°	7.1
72.5°	5.3
75°	5.3
77.5°	3.5
80°	3.5
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)