

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P328494

Luminaire Tested: **L815MED30WF927MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P328494
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1905-290-13)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L815MED30WF927MB
Description: Medium, 3000lm, 60D, 2700K, black finish
Light Source: (1) 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2534.0 lumens
Efficiency: N/A
Efficacy: 67.2 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.88
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 37.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P328494

CATALOG NUMBER: L815MED30WF927MB

Luminous Intensity Polar Plot





TEST NUMBER: P328494

CATALOG NUMBER: L815MED30WF927MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92	91	89	87
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88	85	83	81
4	98	90	85	80	96	89	84	80	87	82	79		85	81	78		83	80	77	76
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	65	73	68	64		72	67	64		71	67	63	62
8	80	71	65	61	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	57		64	60	56		64	59	56	55
10	73	63	57	54	72	63	57	54	62	57	53		61	57	53		60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	350536
5°	348903
10°	343669
15°	335191
20°	316984
25°	273949
30°	207944
35°	101188
40°	37839
45°	21281
50°	14968
55°	9892
60°	7401
65°	6129
70°	4688
75°	2383
80°	710
85°	0



TEST NUMBER: P328494

CATALOG NUMBER: L815MED30WF927MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.8	10.5
10°-20°	735.0	29.0
20°-30°	907.8	35.8
30°-40°	451.4	17.8
40°-50°	102.5	4.0
50°-60°	43.8	1.7
60°-70°	20.9	0.8
70°-80°	5.8	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1909.6	75.4
0°-40°	2360.9	93.2
0°-60°	2507.2	98.9
0°-90°	2534.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2534.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2842	
5°	2818	267
15°	2625	735
25°	2013	908
35°	672	451
45°	122	103
55°	46	44
65°	21	21
75°	5	6
85°	0	0
90°	0	



TEST NUMBER: P328494

CATALOG NUMBER: L815MED30WF927MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2841.9
2.5°	2832.9
5°	2817.9
7.5°	2791.9
10°	2743.9
12.5°	2688.9
15°	2624.9
17.5°	2541.9
20°	2414.9
22.5°	2236.9
25°	2012.9
27.5°	1768.9
30°	1460.0
32.5°	1064.0
35°	672.0
37.5°	390.0
40°	235.0
42.5°	161.0
45°	122.0
47.5°	98.0
50°	78.0
52.5°	60.0
55°	46.0
57.5°	37.0
60°	30.0
62.5°	25.0
65°	21.0
67.5°	17.0
70°	13.0
72.5°	8.0
75°	5.0
77.5°	2.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)