

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P328495

Luminaire Tested: **L815MED30WF930MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P328495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1905-290-13)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L815MED30WF930MB
Description: Medium, 3000lm, 60D, 3000K, black finish
Light Source: (1) 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2700.0 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.88
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 37.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P328495
CATALOG NUMBER: L815MED30WF930MB

Luminous Intensity Polar Plot





TEST NUMBER: P328495

CATALOG NUMBER: L815MED30WF930MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92	91	89	87
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88	85	83	81
4	98	90	85	80	96	89	84	80	87	82	79		85	81	78		83	80	77	76
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	65	73	68	64		72	67	64		71	67	63	62
8	80	71	65	61	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	57		64	60	56		64	59	56	55
10	73	63	57	54	72	63	57	54	62	57	53		61	57	53		60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	373503
5°	371760
10°	366189
15°	357155
20°	337749
25°	291901
30°	221560
35°	107813
40°	40318
45°	22677
50°	15946
55°	10537
60°	7894
65°	6538
70°	5013
75°	2526
80°	781
85°	0



TEST NUMBER: P328495

CATALOG NUMBER: L815MED30WF930MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.2	10.5
10°-20°	783.1	29.0
20°-30°	967.3	35.8
30°-40°	480.9	17.8
40°-50°	109.2	4.0
50°-60°	46.6	1.7
60°-70°	22.2	0.8
70°-80°	6.1	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2034.7	75.4
0°-40°	2515.6	93.2
0°-60°	2671.5	98.9
0°-90°	2700.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2700.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3028	
5°	3002	284
15°	2797	783
25°	2145	967
35°	716	481
45°	130	109
55°	49	47
65°	22	22
75°	5	6
85°	0	0
90°	0	



TEST NUMBER: P328495

CATALOG NUMBER: L815MED30WF930MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3028.1
2.5°	3018.5
5°	3002.5
7.5°	2974.8
10°	2923.7
12.5°	2865.1
15°	2796.9
17.5°	2708.4
20°	2573.1
22.5°	2383.5
25°	2144.8
27.5°	1884.8
30°	1555.6
32.5°	1133.7
35°	716.0
37.5°	415.5
40°	250.4
42.5°	171.5
45°	130.0
47.5°	104.4
50°	83.1
52.5°	63.9
55°	49.0
57.5°	39.4
60°	32.0
62.5°	26.6
65°	22.4
67.5°	18.1
70°	13.9
72.5°	8.5
75°	5.3
77.5°	2.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)