

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P644035

Luminaire Tested: ML5615LSWFL559FS1E - 693WB - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P644035
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-63)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 693WB - 900LM - 5000K
Description: ML56 RR, 55D TIR OPTIC, 6" WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1283.9 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P644035
CATALOG NUMBER: ML5615LSWFL559FS1E - 693WB - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P644035

CATALOG NUMBER: ML5615LSWFL559FS1E - 693WB - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78	78	78	78
4	96	87	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	71	89	80	75	70	79	73	70	77	72	69	75	71	68	67	67	67	67
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	67	63	62	62	62	62
7	81	71	64	60	79	70	64	60	69	63	59	68	63	59	66	62	59	57	57	57	57
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
9	73	62	56	52	71	62	56	52	61	55	52	60	55	51	59	55	51	50	50	50	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73925
5°	70829
10°	67217
15°	63303
20°	57376
25°	48831
30°	39943
35°	31273
40°	23186
45°	15250
50°	6593
55°	2714
60°	1491
65°	739
70°	721
75°	720
80°	726
85°	692

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15250 cd/sqm



TEST NUMBER: P644035

CATALOG NUMBER: ML5615LSWFL559FS1E - 693WB - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.4	9.4
10°-20°	310.7	24.2
20°-30°	369.1	28.7
30°-40°	292.5	22.8
40°-50°	149.1	11.6
50°-60°	30.4	2.4
60°-70°	6.7	0.5
70°-80°	3.6	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	800.1	62.3
0°-40°	1092.6	85.1
0°-60°	1272.1	99.1
0°-90°	1283.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1283.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1348	
5°	1287	120
15°	1115	311
25°	807	369
35°	467	292
45°	197	149
55°	28	30
65°	6	7
75°	3	4
85°	1	2
90°	0	



TEST NUMBER: P644035
CATALOG NUMBER: ML5615LSWFL559FS1E - 693WB - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1348.5
2.5°	1331.4
5°	1287.1
7.5°	1245.0
10°	1207.5
12.5°	1164.3
15°	1115.4
17.5°	1054.0
20°	983.5
22.5°	900.5
25°	807.3
27.5°	716.3
30°	631.0
32.5°	548.0
35°	467.3
37.5°	393.4
40°	324.0
42.5°	258.1
45°	196.7
47.5°	128.5
50°	77.3
52.5°	43.2
55°	28.4
57.5°	20.5
60°	13.6
62.5°	8.0
65°	5.7
67.5°	4.5
70°	4.5
72.5°	3.4
75°	3.4
77.5°	3.4
80°	2.3
82.5°	2.3
85°	1.1
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)