

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P328527

Luminaire Tested: **L815SML10NF930MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P328527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1905-290-4)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L815SML10NF930MB
Description: Small, 1000lm, 25D, 3000K, black finish
Light Source: (1) 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1233.0 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.39
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 12.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P328527

CATALOG NUMBER: L815SML10NF930MB

Luminous Intensity Polar Plot





TEST NUMBER: P328527

CATALOG NUMBER: L815SML10NF930MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105		103	102	101		100	99	99	97
2	112	108	105	103	110	106	104	102	103	101	99		100	99	97		98	97	95	94
3	108	104	100	97	106	102	99	97	100	97	95		98	96	94		96	94	92	91
4	105	100	96	93	104	99	95	93	97	94	92		95	93	91		93	91	90	89
5	102	97	93	90	101	96	92	89	94	91	89		93	90	88		91	89	87	86
6	100	94	90	87	98	93	89	87	92	88	86		90	88	85		89	87	85	84
7	97	91	87	84	96	90	87	84	89	86	84		88	85	83		87	85	83	82
8	95	89	85	82	94	88	84	82	87	84	82		86	83	81		86	83	81	80
9	93	86	82	80	92	86	82	80	85	82	80		84	81	79		84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	78		83	80	78		82	79	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1419733
5°	1308273
10°	962307
15°	461932
20°	116747
25°	32687
30°	17547
35°	13572
40°	12080
45°	10203
50°	8290
55°	6270
60°	2807
65°	1868
70°	898
75°	0
80°	0
85°	0



TEST NUMBER: P328527

CATALOG NUMBER: L815SML10NF930MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	516.0	41.9
10°-20°	559.3	45.4
20°-30°	81.3	6.6
30°-40°	32.7	2.7
40°-50°	25.5	2.1
50°-60°	14.0	1.1
60°-70°	3.8	0.3
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1156.6	93.8
0°-40°	1189.3	96.5
0°-60°	1228.8	99.7
0°-90°	1233.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1233.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6474	
5°	5944	516
15°	2035	559
25°	135	81
35°	51	33
45°	33	25
55°	16	14
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P328527

CATALOG NUMBER: L815SML10NF930MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	6474.5
1°	6455.9
2°	6389.4
3°	6285.1
4°	6130.0
5°	5943.5
6°	5710.5
7°	5436.7
8°	5110.8
9°	4729.2
10°	4321.8
11°	3875.1
12°	3410.6
13°	2936.7
14°	2477.2
15°	2034.8
17.5°	1105.6
20°	500.3
22.5°	235.1
25°	135.1
27.5°	91.5
30°	69.3
32.5°	57.2
35°	50.7
37.5°	46.5
40°	42.2
42.5°	37.9
45°	32.9
47.5°	28.6
50°	24.3
52.5°	20.0
55°	16.4
57.5°	11.4
60°	6.4
62.5°	5.0
65°	3.6
67.5°	2.9
70°	1.4
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P328527

CATALOG NUMBER: L815SML10NF930MB

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$

(END OF REPORT)