

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: HALO

Report Number: P979198

Luminaire Tested: L820S10FL935XXXXBLSHBXXXX

Issue Date: 4/1/2025

Test Information

Test Method: LM-79-2019
Report Number: P979198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (LM79-2019)
Test Lab: INNOVATION CENTER
Issue Date: 4/1/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: L820S10FL935XXXXBLSHBXXXX
Description: 2IN Sustainable LED Track Luminaire with flood optic
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1029.9 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.58
Luminous Opening: Circular (Dia: 0.22' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9
Total Harmonic Distortion (THDi): 20
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979198
CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°



TEST NUMBER: P979198

CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	92	92	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	88	88	86
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	84	84	83
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	82	80	80	80	79
6	94	87	82	79	93	86	82	78	85	81	78	83	80	77	82	79	77	77	77	76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	74	74	72
8	88	80	75	72	87	79	75	72	78	74	71	77	74	71	77	73	71	71	71	70
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	71	68	68	68	67
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	71	68	65	65	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	654864	654864	654864	654864
5°	638751	644213	642311	636957
10°	583048	606744	600284	577221
15°	442121	487580	478471	435142
20°	276250	322201	311513	270921
25°	157058	184479	177967	153892
30°	92904	114817	106189	88090
35°	22407	42897	33081	18507
40°	4523	5442	4842	4241
45°	3139	3369	3178	3025
50°	2990	2948	2864	2822
55°	2926	2926	2879	2785
60°	2924	2924	2870	2761
65°	3075	3075	2883	2754
70°	3245	3245	2849	2770
75°	3347	3347	2720	2615
80°	4053	4209	3430	3118
85°	621	1553	932	621

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 52.5°
 Vertical Angle: 82.5°
 Luminance: 4770 cd/sqm



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.7	21.2
10°-20°	443.8	43.1
20°-30°	273.3	26.5
30°-40°	70.8	6.9
40°-50°	6.9	0.7
50°-60°	5.5	0.5
60°-70°	4.5	0.4
70°-80°	3.1	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.1	0.0
140°-150°	0.4	0.0
150°-160°	0.8	0.1
160°-170°	0.8	0.1
170°-180°	0.3	0.0
0°-30°	935.8	90.9
0°-40°	1006.7	97.7
0°-60°	1019.0	98.9
0°-90°	1027.5	99.8
90°-120°	0.0	0.0
90°-150°	0.5	0.0
90°-180°	2.0	0.2
0°-180°	1029.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2419	2419	2419	2419	2419	
5°	2350	2371	2364	2344	2350	218
15°	1578	1740	1707	1553	1578	426
25°	526	618	596	515	526	255
35°	68	130	100	56	68	62
45°	8	9	8	8	8	7
55°	6	6	6	6	6	6
65°	5	5	4	4	5	5
75°	3	3	3	2	3	3
85°	0	0	0	0	0	1
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	1	0	0	1	1	0
155°	2	2	2	2	2	1
165°	3	3	3	3	3	1
175°	4	4	4	4	4	0
180°	4	4	4	4	4	



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2396.4	2396.5	2396.6	2396.7	2396.8	2397.0	2397.3	2397.5	2397.8	2398.2	2398.6
5°	2350.5	2350.6	2350.8	2351.0	2351.3	2351.6	2351.9	2352.4	2352.9	2353.4	2354.1
7.5°	2273.3	2273.8	2274.5	2275.3	2276.2	2277.2	2278.3	2279.4	2280.6	2281.9	2283.2
10°	2121.0	2122.6	2124.4	2126.5	2128.8	2131.4	2134.3	2137.4	2140.9	2144.6	2148.5
12.5°	1881.3	1883.2	1885.6	1888.4	1891.5	1895.1	1899.1	1903.6	1908.4	1913.8	1919.5
15°	1577.5	1579.7	1582.5	1585.9	1589.7	1594.1	1599.1	1604.6	1610.6	1617.2	1624.3
17.5°	1256.1	1259.3	1262.9	1267.1	1271.8	1277.0	1282.6	1288.7	1295.2	1302.1	1309.5
20°	958.9	961.6	964.9	968.7	973.0	977.8	983.0	988.7	994.9	1001.4	1008.5
22.5°	707.2	708.9	710.9	713.5	716.4	719.8	723.8	728.2	733.2	738.7	744.4
25°	525.8	526.8	528.2	529.8	531.6	533.8	536.2	538.9	541.9	545.2	548.4
27.5°	419.8	420.6	421.5	422.7	423.9	425.3	426.9	428.6	430.4	432.3	434.0
30°	297.2	298.5	300.0	301.8	303.7	305.9	308.3	310.8	313.6	316.6	319.2
32.5°	175.7	176.9	178.3	180.0	181.8	183.9	186.1	188.6	191.2	194.0	196.2
35°	67.8	68.6	69.5	70.5	71.8	73.2	74.8	76.6	78.6	80.7	82.3
37.5°	17.3	17.4	17.6	17.8	18.1	18.3	18.7	19.1	19.5	20.0	20.4
40°	12.8	12.8	12.9	12.9	13.0	13.0	13.1	13.2	13.3	13.4	13.4
42.5°	9.3	9.4	9.4	9.4	9.5	9.5	9.6	9.7	9.8	9.8	9.9
45°	8.2	8.2	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.4	8.4
47.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.6	7.6	7.6	7.6
50°	7.1	7.1	7.1	7.1	7.2	7.2	7.2	7.2	7.2	7.2	7.2
52.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
55°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
57.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
60°	5.4	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
62.5°	5.1	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
65°	4.8	4.8	4.8	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
67.5°	4.4	4.4	4.4	4.4	4.5	4.5	4.5	4.5	4.5	4.5	4.5
70°	4.1	4.1	4.1	4.2	4.2	4.2	4.2	4.2	4.2	4.3	4.3
72.5°	3.5	3.5	3.6	3.6	3.6	3.6	3.7	3.7	3.7	3.7	3.7
75°	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.3	3.3	3.3	3.3
77.5°	2.9	3.0	3.0	3.0	3.0	3.0	3.1	3.1	3.1	3.1	3.1
80°	2.6	2.6	2.7	2.7	2.7	2.7	2.8	2.8	2.8	2.9	2.9
82.5°	1.2	1.2	1.3	1.3	1.4	1.4	1.5	1.6	1.6	1.7	1.8
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
140°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
142.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
145°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
147.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	0.9	0.9	0.9	0.9
150°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.2	1.2	1.2	1.2
152.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.5	1.5
155°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
157.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.7	2.7	2.7	2.7
165°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
167.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
170°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
172.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
175°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
177.5°	3.7	3.7	3.7	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2399.0	2399.5	2400.0	2400.6	2401.2	2401.8	2402.5	2403.3	2404.6	2404.0	2403.7
5°	2354.8	2355.6	2356.5	2357.2	2357.6	2359.9	2359.5	2359.3	2360.3	2361.3	2362.3
7.5°	2284.5	2285.7	2286.1	2286.7	2287.6	2290.4	2290.3	2292.7	2295.1	2297.5	2300.0
10°	2152.8	2154.9	2156.9	2159.2	2167.7	2166.6	2167.7	2170.5	2173.6	2176.9	2180.5
12.5°	1924.6	1927.2	1930.2	1933.8	1944.7	1942.9	1946.9	1951.7	1956.8	1962.3	1968.1
15°	1629.2	1632.5	1636.3	1640.4	1651.2	1649.7	1654.9	1660.6	1666.9	1673.7	1679.5
17.5°	1313.4	1316.8	1320.7	1337.1	1335.0	1335.3	1340.9	1346.8	1353.0	1359.5	1363.1
20°	1011.4	1014.7	1018.3	1032.9	1030.7	1031.7	1037.0	1042.8	1049.0	1055.3	1058.8
22.5°	747.5	750.8	754.5	767.4	765.5	767.0	771.5	776.4	781.6	786.2	798.8
25°	550.3	552.4	554.6	562.3	561.3	562.9	566.2	569.7	573.3	576.2	584.2
27.5°	434.8	435.7	436.9	441.2	440.5	441.4	443.2	445.2	447.2	448.6	453.0
30°	320.6	322.3	324.2	330.1	329.4	331.0	333.6	336.2	339.0	340.6	345.6
32.5°	197.4	198.8	200.5	205.9	205.1	206.8	209.4	212.1	215.1	216.8	222.0
35°	83.4	84.6	85.9	90.0	89.2	90.7	92.7	94.9	97.2	98.9	103.4
37.5°	20.7	21.0	21.3	22.2	22.0	22.6	23.3	24.1	24.9	25.5	26.8
40°	13.5	13.6	13.6	13.8	13.8	13.8	13.9	14.0	14.1	14.2	14.3
42.5°	9.9	10.0	10.0	10.2	10.1	10.2	10.3	10.3	10.4	10.5	10.6
45°	8.4	8.4	8.4	8.5	8.4	8.5	8.5	8.5	8.5	8.5	8.5
47.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
50°	7.2	7.1	7.1	7.1	7.1	7.1	7.1	7.0	7.0	7.0	7.0
52.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
55°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
57.5°	5.9	5.9	5.9	5.9	5.9	5.8	5.8	5.8	5.8	5.8	5.8
60°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
62.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
65°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
67.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
70°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.2	4.2
72.5°	3.7	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
75°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
77.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
80°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
82.5°	1.8	1.9	1.9	2.0	2.0	2.1	2.1	2.2	2.2	2.2	2.3
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.2	0.2
142.5°	0.5	0.5	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.7	0.7	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
147.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
150°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
152.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
155°	1.9	1.9	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
157.5°	2.2	2.2	2.2	2.2	2.2	2.1	2.1	2.1	2.1	2.1	2.1
160°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.4
162.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
165°	3.0	3.0	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
167.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
170°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
172.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
175°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
177.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2403.9	2404.2	2404.7	2405.2	2405.8	2406.6	2409.3	2409.0	2408.8	2408.6	2408.5
5°	2363.3	2364.2	2365.1	2366.7	2366.7	2367.4	2367.7	2367.8	2367.5	2367.5	2366.3
7.5°	2302.4	2308.6	2306.8	2306.3	2306.3	2306.6	2307.0	2310.6	2308.8	2309.7	2310.8
10°	2184.4	2187.8	2186.8	2188.4	2190.2	2192.2	2194.3	2197.3	2198.4	2200.7	2203.6
12.5°	1979.4	1973.7	1975.8	1978.4	1981.4	1984.7	1994.0	1992.5	1997.1	2002.1	2005.0
15°	1690.4	1686.6	1690.5	1694.9	1699.7	1704.9	1713.6	1715.8	1721.5	1725.9	1729.1
17.5°	1371.2	1370.7	1375.9	1381.3	1386.8	1405.0	1398.2	1403.6	1409.0	1411.7	1426.8
20°	1065.6	1066.2	1070.3	1074.5	1079.0	1092.5	1088.6	1094.6	1099.6	1103.1	1115.5
22.5°	794.0	796.1	800.0	804.2	808.5	819.4	817.7	822.6	825.6	828.3	837.1
25°	581.1	583.4	586.4	589.3	592.3	598.8	598.5	601.9	603.5	605.3	610.1
27.5°	451.3	452.9	454.5	456.3	458.0	461.5	461.8	463.7	464.7	465.8	468.2
30°	343.3	345.1	347.0	349.2	351.6	355.9	356.5	358.0	358.6	359.2	361.1
32.5°	220.1	222.0	223.9	226.0	228.2	231.8	232.8	234.4	235.4	236.4	238.2
35°	102.4	104.6	106.8	109.0	111.2	114.4	115.8	117.4	118.6	119.8	121.4
37.5°	26.5	27.5	28.4	29.2	29.9	30.7	31.5	32.6	33.4	34.0	34.5
40°	14.3	14.4	14.5	14.6	14.6	14.8	14.8	14.9	14.9	15.0	15.0
42.5°	10.6	10.6	10.7	10.7	10.8	10.9	10.9	11.0	11.0	11.2	11.1
45°	8.5	8.5	8.5	8.6	8.6	8.6	8.6	8.6	8.6	8.7	8.7
47.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.7	7.6
50°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
52.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
55°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
57.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.7	5.7	5.7
60°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
62.5°	5.2	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
65°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.8	4.8	4.8
67.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.4	4.4	4.4
70°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.1
72.5°	3.8	3.8	3.8	3.8	3.9	3.8	3.8	3.8	3.8	3.8	3.8
75°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.2	3.2	3.2
77.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.0	3.0	3.0	3.0	3.0
80°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.8	2.8	2.8
82.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
85°	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
147.5°	0.9	0.9	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
150°	1.2	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
152.5°	1.5	1.5	1.5	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
155°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.7	1.7	1.7
157.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
160°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
162.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
165°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
167.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
170°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
172.5°	3.5	3.5	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.6	3.6	3.6	3.6
177.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2408.3	2408.2	2408.1	2408.1	2407.4	2406.7	2406.0	2405.3	2404.7	2404.2	2404.3
5°	2366.5	2366.8	2367.5	2370.6	2369.5	2370.1	2370.1	2370.3	2371.9	2370.5	2370.8
7.5°	2312.1	2313.6	2314.5	2314.3	2314.3	2314.4	2316.9	2314.3	2313.6	2313.3	2313.3
10°	2205.6	2208.4	2207.5	2207.2	2206.8	2210.4	2205.8	2207.4	2209.9	2212.6	2217.8
12.5°	2013.5	2009.3	2010.9	2012.6	2014.5	2019.2	2018.3	2020.4	2022.2	2032.1	2023.9
15°	1735.0	1734.7	1737.0	1739.7	1753.6	1745.8	1748.4	1750.6	1751.9	1759.1	1755.0
17.5°	1417.8	1421.4	1425.0	1428.6	1440.4	1435.9	1439.7	1442.5	1444.9	1449.7	1448.6
20°	1109.6	1112.6	1115.5	1118.4	1125.9	1124.0	1126.3	1128.1	1129.8	1131.6	1134.5
22.5°	834.1	837.1	839.9	842.5	847.0	847.6	850.2	852.3	863.3	856.1	857.8
25°	609.6	612.6	615.3	617.6	620.2	621.4	623.0	624.4	630.9	627.0	628.5
27.5°	468.1	469.4	470.7	471.8	472.9	474.4	475.8	476.9	480.7	478.8	479.4
30°	360.7	361.4	362.2	367.3	363.8	364.7	365.4	366.0	368.9	367.0	367.3
32.5°	238.5	239.4	240.3	245.0	241.8	242.7	243.4	244.1	246.7	245.4	246.3
35°	122.4	123.8	125.1	129.8	127.8	128.7	129.4	130.0	132.0	131.1	131.5
37.5°	35.4	36.2	36.7	38.3	37.1	38.1	39.0	39.6	40.5	40.6	41.2
40°	15.1	15.2	15.2	15.4	15.3	15.3	15.4	15.4	15.4	15.4	15.4
42.5°	11.1	11.2	11.2	11.3	11.3	11.3	11.4	11.4	11.4	11.4	11.4
45°	8.7	8.7	8.7	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8
47.5°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
50°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
52.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
55°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
57.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
60°	5.5	5.5	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
62.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.0	5.0	5.0
65°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.7	4.7
67.5°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.3	4.3	4.3
70°	4.1	4.1	4.1	4.1	4.1	4.0	4.0	4.0	4.0	4.0	4.0
72.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.6	3.6	3.6
75°	3.2	3.2	3.2	3.2	3.2	3.1	3.1	3.1	3.1	3.1	3.0
77.5°	3.0	2.9	2.9	2.9	2.9	2.9	2.8	2.8	2.8	2.8	2.8
80°	2.8	2.8	2.7	2.7	2.7	2.7	2.7	2.7	2.6	2.6	2.6
82.5°	2.3	2.3	2.3	2.3	2.3	2.2	2.2	2.2	2.2	2.2	2.2
85°	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.7	0.7	0.7	0.7
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198

CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.6	0.6	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.7
150°	1.1	1.1	1.1	1.1	1.1	1.1	1.0	1.0	1.0	1.0	1.0
152.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.3	1.3
155°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
157.5°	2.1	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
160°	2.4	2.4	2.4	2.4	2.4	2.3	2.3	2.3	2.3	2.3	2.3
162.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.6	2.6
165°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
167.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
170°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.3	3.3	3.3
175°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
177.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2405.1	2405.9	2406.5	2408.4	2407.6	2407.2	2406.9	2406.7	2406.5	2406.5	2405.3
5°	2371.3	2372.0	2374.0	2373.0	2372.2	2370.4	2369.0	2367.7	2367.9	2368.5	2369.3
7.5°	2314.7	2312.5	2311.6	2311.1	2310.9	2311.3	2310.7	2309.7	2308.3	2308.7	2305.8
10°	2213.7	2212.0	2210.8	2210.1	2210.6	2209.5	2208.7	2207.7	2207.3	2208.0	2207.5
12.5°	2024.1	2024.5	2025.1	2031.4	2026.8	2028.0	2028.6	2028.8	2034.6	2027.7	2025.8
15°	1756.7	1758.4	1760.0	1763.7	1761.5	1760.5	1759.4	1758.5	1760.4	1757.5	1757.1
17.5°	1450.3	1452.0	1466.1	1456.0	1457.0	1456.9	1456.5	1467.9	1455.5	1453.5	1451.8
20°	1136.9	1138.8	1148.9	1140.7	1141.0	1141.2	1140.9	1149.3	1139.1	1138.7	1137.8
22.5°	859.0	859.7	865.5	859.9	860.8	861.8	862.6	870.2	863.1	862.5	861.4
25°	629.6	630.3	633.8	631.0	632.2	633.0	633.2	637.1	632.2	631.6	630.5
27.5°	479.7	479.7	480.8	479.5	480.3	480.8	481.1	483.1	480.9	480.6	479.9
30°	367.6	367.6	368.7	367.5	367.4	367.3	367.1	368.6	366.4	366.0	365.4
32.5°	247.1	247.9	249.5	248.8	248.6	248.3	247.9	249.2	246.9	246.2	245.3
35°	131.8	131.9	132.2	131.8	131.7	131.4	130.8	131.2	129.4	128.7	127.8
37.5°	41.5	41.7	41.7	42.1	42.4	42.5	42.2	42.2	41.3	40.8	40.0
40°	15.4	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.2	15.2	15.1
42.5°	11.4	11.6	11.4	11.4	11.4	11.4	11.4	11.4	11.3	11.3	11.3
45°	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8
47.5°	7.7	7.8	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
50°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	6.9	6.9	6.9	6.9
52.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
55°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.1	6.1
57.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
60°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.3	5.3	5.3
62.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
65°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.6	4.6
67.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.2	4.2	4.2	4.2
70°	4.0	4.0	4.0	3.9	3.9	3.9	3.9	3.9	3.9	3.8	3.8
72.5°	3.6	3.6	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.5	3.4
75°	3.0	3.0	3.0	3.0	2.9	2.9	2.9	2.9	2.9	2.8	2.8
77.5°	2.7	2.7	2.7	2.7	2.7	2.6	2.6	2.6	2.6	2.6	2.5
80°	2.6	2.6	2.6	2.5	2.5	2.5	2.5	2.5	2.4	2.4	2.4
82.5°	2.2	2.2	2.2	2.2	2.1	2.1	2.1	2.1	2.1	2.1	2.0
85°	0.6	0.6	0.6	0.7	0.7	0.7	0.7	0.6	0.6	0.6	0.6
87.5°	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198

CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
155°	1.7	1.7	1.7	1.7	1.7	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
160°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
162.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
165°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
167.5°	3.1	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
170°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.6	3.6	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
177.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2404.2	2403.3	2402.7	2402.3	2402.4	2402.4	2402.2	2401.8	2401.6	2401.6	2401.7
5°	2372.7	2371.1	2369.3	2367.8	2366.5	2367.0	2364.9	2363.9	2363.8	2363.7	2363.4
7.5°	2305.2	2304.4	2303.5	2302.4	2302.4	2300.1	2299.8	2299.4	2299.0	2298.6	2298.0
10°	2206.8	2205.5	2203.6	2204.3	2199.6	2198.7	2197.9	2196.8	2195.4	2193.8	2191.9
12.5°	2024.1	2022.7	2021.5	2026.0	2020.1	2017.9	2015.4	2012.7	2009.7	2006.3	2003.4
15°	1756.0	1754.3	1752.5	1755.1	1750.4	1748.6	1746.3	1743.5	1740.3	1736.5	1733.8
17.5°	1449.8	1447.5	1457.4	1446.7	1442.9	1440.7	1438.0	1434.6	1430.5	1425.8	1423.2
20°	1136.5	1134.8	1144.5	1134.5	1131.6	1129.1	1126.1	1122.6	1118.7	1114.2	1112.2
22.5°	859.9	858.2	864.2	855.7	853.9	851.8	849.2	846.2	842.6	838.9	837.5
25°	629.2	628.3	632.7	627.0	626.1	624.7	622.8	620.5	617.7	614.9	614.0
27.5°	478.9	478.4	480.6	477.7	477.3	476.7	475.8	474.6	473.2	471.8	471.1
30°	364.6	364.1	366.2	362.9	362.0	360.9	359.7	358.3	356.6	355.1	354.1
32.5°	244.4	243.8	245.6	242.2	241.0	239.7	238.1	236.4	234.5	232.8	231.6
35°	126.7	126.3	127.7	124.9	123.9	122.7	121.3	119.6	117.7	116.1	114.8
37.5°	39.1	39.1	39.8	38.5	38.1	37.5	36.5	35.4	34.0	33.0	32.5
40°	15.0	15.0	15.0	14.9	14.8	14.7	14.6	14.6	14.4	14.4	14.3
42.5°	11.2	11.2	11.2	11.1	11.1	11.0	11.0	10.9	10.8	10.8	10.7
45°	8.7	8.7	8.7	8.7	8.7	8.7	8.6	8.6	8.6	8.5	8.5
47.5°	7.6	7.6	7.7	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.5
50°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.8	6.8	6.8	6.8
52.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
55°	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1
57.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
60°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
62.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.8
65°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.5	4.5
67.5°	4.2	4.2	4.2	4.1	4.1	4.1	4.1	4.1	4.1	4.0	4.0
70°	3.8	3.8	3.8	3.8	3.8	3.7	3.7	3.7	3.7	3.7	3.7
72.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.3
75°	2.8	2.8	2.8	2.8	2.7	2.7	2.7	2.7	2.7	2.7	2.7
77.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.4	2.4	2.4
80°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.3	2.3	2.3	2.3
82.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	1.9	1.9	1.9	1.9
85°	0.6	0.6	0.6	0.6	0.6	0.5	0.5	0.5	0.5	0.4	0.4
87.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
155°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
160°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
162.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
165°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
167.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
170°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
177.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.6	3.6	3.6
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2401.9	2402.3	2402.2	2402.1	2402.1	2402.1	2402.3	2403.3	2404.4	2405.7	2407.0
5°	2362.9	2362.1	2363.0	2363.2	2363.3	2363.5	2363.6	2363.3	2363.0	2362.7	2362.4
7.5°	2297.3	2300.4	2298.5	2296.6	2294.6	2292.7	2290.8	2290.3	2289.8	2289.3	2288.8
10°	2191.5	2196.0	2193.5	2191.1	2188.6	2186.1	2183.7	2182.7	2181.7	2180.8	2179.8
12.5°	2002.5	2008.3	2004.2	2000.1	1995.9	1991.8	1987.7	1986.0	1984.2	1982.5	1980.8
15°	1731.9	1738.1	1731.9	1725.7	1719.5	1713.3	1707.2	1704.8	1702.5	1700.2	1697.9
17.5°	1433.6	1426.0	1418.5	1410.9	1403.3	1395.6	1388.0	1386.3	1384.6	1382.9	1381.3
20°	1121.5	1114.8	1108.1	1101.4	1094.7	1088.0	1081.3	1079.6	1078.0	1076.3	1074.6
22.5°	845.3	839.7	834.1	828.5	822.9	817.3	811.7	809.9	808.1	806.2	804.4
25°	619.5	615.6	611.6	607.7	603.7	599.8	595.8	594.6	593.4	592.2	591.0
27.5°	474.1	471.6	469.0	466.5	464.0	461.4	458.9	458.1	457.3	456.5	455.7
30°	357.5	354.5	351.6	348.6	345.6	342.7	339.7	338.9	338.1	337.3	336.5
32.5°	234.5	231.3	228.1	224.9	221.7	218.6	215.4	214.4	213.4	212.4	211.4
35°	117.1	114.2	111.4	108.6	105.8	102.9	100.1	99.0	97.9	96.8	95.8
37.5°	33.3	32.0	30.6	29.3	27.9	26.6	25.2	24.9	24.5	24.2	23.9
40°	14.4	14.3	14.2	14.0	13.9	13.8	13.7	13.7	13.6	13.6	13.5
42.5°	10.8	10.7	10.6	10.5	10.4	10.3	10.2	10.1	10.1	10.1	10.0
45°	8.5	8.5	8.5	8.4	8.4	8.3	8.3	8.3	8.3	8.2	8.2
47.5°	7.5	7.5	7.5	7.5	7.4	7.4	7.4	7.3	7.3	7.3	7.3
50°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.7	6.7	6.7	6.7
52.5°	6.7	6.7	6.7	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
55°	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.0
57.5°	5.7	5.7	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6
60°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.2	5.2
62.5°	4.9	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
65°	4.6	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.4
67.5°	4.0	4.0	4.0	4.0	4.0	4.0	3.9	3.9	3.9	3.9	3.9
70°	3.7	3.7	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.5	3.5
72.5°	3.3	3.3	3.3	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.1
75°	2.7	2.6	2.6	2.6	2.6	2.6	2.6	2.5	2.5	2.5	2.5
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.3	2.3	2.3	2.3
80°	2.3	2.3	2.3	2.3	2.3	2.2	2.2	2.2	2.2	2.2	2.2
82.5°	1.9	1.9	1.9	1.8	1.8	1.8	1.8	1.8	1.7	1.7	1.7
85°	0.5	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3	0.3
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198

CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
155°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
160°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
162.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
165°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
167.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
170°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
177.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2408.0	2407.8	2407.9	2408.1	2408.5	2409.0	2407.2	2406.3	2405.3	2404.3	2404.0
5°	2359.4	2359.9	2360.0	2359.9	2359.5	2359.0	2358.8	2360.6	2357.1	2356.7	2356.3
7.5°	2288.4	2284.4	2284.5	2284.2	2283.3	2281.7	2279.4	2276.4	2276.7	2273.9	2272.9
10°	2178.8	2170.0	2166.5	2164.6	2162.6	2160.7	2158.7	2156.9	2155.4	2157.6	2149.0
12.5°	1979.1	1966.3	1960.7	1957.6	1955.0	1951.8	1948.0	1943.6	1938.7	1938.5	1928.8
15°	1695.6	1681.2	1674.8	1670.1	1667.6	1664.4	1660.6	1656.1	1651.1	1648.9	1637.7
17.5°	1379.6	1377.9	1359.7	1353.9	1350.7	1347.0	1342.7	1337.9	1332.7	1329.0	1331.5
20°	1073.0	1071.3	1054.4	1048.4	1045.3	1041.6	1037.3	1032.5	1027.1	1021.9	1023.9
22.5°	802.6	800.8	786.3	780.6	777.9	775.0	771.8	768.3	764.4	760.3	762.4
25°	589.8	588.6	578.7	574.9	572.6	570.4	567.9	565.1	562.0	558.5	559.2
27.5°	454.9	454.1	447.8	445.2	443.8	442.5	441.1	439.4	437.6	435.6	435.9
30°	335.7	335.0	327.7	324.9	323.0	321.3	319.4	317.2	314.9	312.3	312.3
32.5°	210.5	209.5	202.4	199.5	197.3	195.4	193.3	191.0	188.5	185.7	185.2
35°	94.7	93.6	87.9	85.5	83.6	82.1	80.5	78.6	76.6	74.4	73.8
37.5°	23.5	23.2	21.6	21.0	20.5	20.1	19.7	19.3	18.8	18.3	18.1
40°	13.5	13.4	13.2	13.1	13.0	13.0	13.0	12.9	12.8	12.8	12.7
42.5°	10.0	9.9	9.7	9.7	9.6	9.5	9.5	9.4	9.4	9.3	9.3
45°	8.2	8.2	8.1	8.0	8.0	8.0	8.0	8.0	7.9	7.9	7.9
47.5°	7.3	7.2	7.2	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
50°	6.7	6.7	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
52.5°	6.6	6.6	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
55°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
57.5°	5.6	5.6	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
60°	5.2	5.2	5.2	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
62.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
65°	4.4	4.4	4.4	4.4	4.3	4.3	4.3	4.3	4.3	4.3	4.3
67.5°	3.9	3.9	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
70°	3.5	3.5	3.5	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.4
72.5°	3.1	3.1	3.0	3.0	3.0	3.0	2.9	2.9	2.9	2.8	2.8
75°	2.5	2.5	2.5	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
77.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.2	2.2	2.2	2.2	2.2
80°	2.2	2.2	2.1	2.1	2.1	2.1	2.1	2.1	2.0	2.0	2.0
82.5°	1.7	1.6	1.6	1.5	1.5	1.5	1.4	1.4	1.4	1.3	1.3
85°	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.8	0.8	0.8	0.8
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.1
152.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.4	1.4	1.4	1.4	1.4
155°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
157.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.1	2.1	2.1	2.1
160°	2.3	2.3	2.3	2.3	2.4	2.4	2.4	2.4	2.4	2.4	2.4
162.5°	2.6	2.6	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
165°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
167.5°	3.0	3.0	3.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
170°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
177.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2403.8	2403.6	2403.5	2403.4	2402.2	2401.3	2400.4	2399.5	2398.6	2399.1	2397.5
5°	2356.1	2357.0	2351.3	2349.4	2348.0	2347.3	2348.2	2349.0	2349.6	2350.0	2351.1
7.5°	2271.4	2269.5	2267.2	2268.8	2264.7	2265.0	2265.0	2264.9	2262.9	2261.1	2259.1
10°	2146.2	2143.4	2140.6	2138.6	2135.0	2132.2	2130.1	2129.2	2129.1	2125.1	2121.9
12.5°	1926.5	1923.8	1920.6	1917.1	1919.1	1907.3	1901.8	1896.6	1892.9	1895.4	1885.5
15°	1632.7	1628.7	1624.4	1620.0	1618.6	1610.3	1604.9	1599.1	1594.2	1592.9	1586.4
17.5°	1314.0	1310.4	1306.1	1301.1	1296.1	1302.3	1284.0	1277.6	1270.8	1267.6	1276.4
20°	1008.8	1005.8	1002.4	998.5	994.0	998.3	984.9	979.9	974.8	971.3	976.7
22.5°	749.8	746.0	742.9	739.5	736.1	739.0	729.3	725.3	720.9	716.7	719.5
25°	552.1	549.9	548.5	547.0	545.2	546.6	540.8	538.0	535.0	531.7	532.6
27.5°	430.4	428.0	426.7	425.4	424.0	424.9	421.1	419.4	417.6	415.7	415.9
30°	306.4	303.5	302.2	300.7	299.1	299.5	295.7	293.7	291.7	289.5	289.1
32.5°	179.6	176.6	175.5	174.3	172.9	173.0	169.5	167.5	165.4	163.2	162.4
35°	70.1	67.9	67.4	66.7	65.7	65.6	63.8	62.7	61.4	60.0	59.3
37.5°	17.7	17.4	17.4	17.3	17.1	16.9	16.8	16.6	16.5	16.2	16.0
40°	12.6	12.5	12.5	12.4	12.4	12.4	12.3	12.3	12.2	12.2	12.1
42.5°	9.2	9.1	9.1	9.1	9.1	9.1	9.1	9.0	9.0	9.0	8.9
45°	7.9	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
47.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
50°	6.5	6.5	6.5	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
52.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
55°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
57.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
60°	5.1	5.0	5.0	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
62.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
65°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
67.5°	3.8	3.7	3.7	3.7	3.7	3.8	3.8	3.8	3.8	3.8	3.8
70°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
72.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
75°	2.4	2.3	2.3	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
77.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.3
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	1.3	1.2	1.2	1.2	1.2	1.1	1.2	1.1	1.0	1.0	1.0
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6
147.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
150°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
152.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.5
155°	1.7	1.7	1.7	1.7	1.8	1.8	1.8	1.8	1.8	1.8	1.8
157.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
160°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
162.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.8	2.8
165°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
167.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
170°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
177.5°	3.6	3.6	3.6	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2397.0	2396.6	2396.3	2396.4	2395.2	2394.6	2394.0	2393.4	2392.8	2392.8	2392.3
5°	2348.4	2347.0	2345.5	2343.9	2344.8	2342.5	2342.5	2342.9	2342.6	2343.9	2342.4
7.5°	2257.1	2257.2	2257.9	2259.3	2260.2	2260.7	2263.4	2256.9	2255.4	2254.5	2254.4
10°	2118.7	2115.5	2116.2	2108.9	2106.4	2104.2	2101.9	2107.0	2100.1	2099.8	2099.9
12.5°	1882.3	1879.5	1877.1	1884.1	1868.4	1864.2	1861.0	1861.6	1855.3	1852.4	1849.5
15°	1582.2	1578.0	1573.9	1576.2	1565.9	1561.6	1558.6	1556.2	1565.8	1552.6	1550.7
17.5°	1263.0	1260.1	1256.8	1255.4	1248.1	1243.2	1238.6	1236.0	1241.5	1231.8	1229.7
20°	965.8	962.6	959.1	955.3	952.2	949.1	946.0	944.3	947.1	940.4	938.2
22.5°	712.2	709.6	706.6	703.3	707.9	697.8	695.0	692.8	693.4	690.2	688.8
25°	529.0	527.5	525.8	523.9	526.1	520.6	518.6	516.6	516.0	515.2	514.5
27.5°	412.6	411.0	409.5	408.1	409.7	405.7	404.6	403.4	402.7	401.7	400.8
30°	286.8	285.6	284.3	283.1	284.3	280.6	279.4	278.3	277.7	281.8	276.9
32.5°	160.8	159.8	158.7	157.5	158.2	155.2	154.1	152.9	152.2	155.9	152.1
35°	58.8	58.5	57.9	57.3	57.6	56.0	55.1	54.0	53.3	56.0	54.1
37.5°	16.3	16.4	16.3	16.2	16.1	16.0	15.9	15.9	15.9	16.2	16.1
40°	12.1	12.1	12.1	12.1	12.1	12.0	12.0	12.0	11.9	12.0	11.9
42.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	8.9	9.0	9.0
45°	7.8	7.8	7.8	7.8	7.9	7.9	7.9	7.9	7.9	7.9	7.9
47.5°	7.0	7.0	7.0	7.0	7.1	7.1	7.1	7.1	7.1	7.1	7.1
50°	6.6	6.6	6.6	6.6	6.6	6.7	6.7	6.7	6.7	6.7	6.7
52.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
55°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
57.5°	5.5	5.5	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6
60°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
62.5°	4.7	4.7	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
65°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
67.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.9	3.9	3.9	3.9
70°	3.5	3.4	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
72.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
75°	2.4	2.4	2.4	2.4	2.4	2.4	2.5	2.5	2.5	2.5	2.5
77.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
80°	2.0	2.0	2.0	2.0	1.9	1.9	1.9	2.0	2.0	2.0	2.0
82.5°	1.0	0.9	0.8	0.7	0.6	0.6	0.6	0.5	0.5	0.4	0.5
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
147.5°	0.8	0.8	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
150°	1.1	1.1	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
152.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
155°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.9	1.9	1.9	1.9
157.5°	2.1	2.1	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
167.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
170°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.6
177.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2392.2	2392.1	2392.0	2391.9	2391.8	2392.0	2392.8	2391.9	2391.9	2391.9	2391.8
5°	2342.5	2342.8	2343.1	2344.3	2341.2	2340.3	2339.8	2339.6	2339.5	2340.3	2338.6
7.5°	2253.8	2253.3	2252.9	2252.4	2251.9	2255.4	2250.8	2250.5	2250.2	2250.1	2250.7
10°	2101.1	2097.6	2095.4	2093.2	2091.3	2090.7	2089.5	2089.4	2089.7	2090.4	2091.3
12.5°	1846.7	1851.0	1842.0	1840.0	1838.5	1837.6	1843.3	1836.2	1835.6	1834.9	1834.4
15°	1548.8	1549.4	1544.0	1541.7	1539.4	1537.3	1538.6	1533.9	1532.5	1531.3	1530.3
17.5°	1227.6	1225.5	1235.4	1221.4	1219.5	1218.0	1216.9	1227.9	1215.0	1214.0	1213.2
20°	936.1	934.0	940.4	930.2	928.1	926.3	925.0	932.6	923.7	923.4	923.2
22.5°	687.2	685.5	688.9	682.9	681.6	680.4	679.6	684.2	677.8	677.3	677.0
25°	513.5	512.2	513.3	510.3	509.3	508.3	508.2	510.9	508.7	508.8	508.9
27.5°	400.1	399.5	400.7	398.4	397.9	397.5	396.9	398.3	395.9	395.8	396.0
30°	276.6	276.2	277.1	275.4	274.9	274.4	274.1	275.7	273.7	273.7	273.8
32.5°	152.1	152.0	152.6	151.5	151.1	150.7	150.5	152.0	151.4	151.9	152.3
35°	54.3	54.2	54.2	54.0	53.7	53.2	52.6	53.3	53.3	53.7	54.1
37.5°	16.2	16.1	15.9	15.9	15.9	15.9	15.9	16.1	16.2	16.2	16.2
40°	11.9	11.9	11.9	11.9	11.9	12.0	12.0	12.0	12.0	12.0	12.0
42.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0
45°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
47.5°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
50°	6.7	6.7	6.7	6.7	6.7	6.8	6.8	6.8	6.8	6.8	6.8
52.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.4	6.4
55°	5.9	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
57.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6
60°	5.1	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
62.5°	4.8	4.8	4.8	4.8	4.8	4.9	4.9	4.9	4.9	4.9	4.9
65°	4.3	4.3	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.5
67.5°	3.9	3.9	3.9	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
70°	3.5	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.7
72.5°	2.8	2.8	2.8	2.9	2.9	2.9	2.9	2.9	3.0	3.0	3.0
75°	2.5	2.5	2.6	2.6	2.6	2.6	2.6	2.6	2.7	2.7	2.7
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.5	2.5	2.5
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	0.5	0.5	0.5	0.4	0.4	0.4	0.4	0.3	0.4	0.4	0.4
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
140°	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5	0.5
145°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
147.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.0	1.0	0.9	1.0
150°	1.2	1.2	1.2	1.2	1.2	1.2	1.3	1.3	1.3	1.3	1.3
152.5°	1.5	1.5	1.5	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
155°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
157.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.5	2.5	2.5	2.5	2.5	2.5	2.6	2.6	2.6	2.6	2.6
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	2.9	2.9	2.9	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.9
167.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
170°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
177.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2391.8	2391.7	2391.5	2391.8	2392.3	2392.1	2392.3	2392.4	2392.6	2392.8	2393.0
5°	2338.3	2338.0	2337.8	2337.6	2337.6	2337.7	2339.2	2340.9	2340.4	2341.5	2342.4
7.5°	2254.1	2250.2	2250.3	2250.7	2251.3	2252.1	2253.0	2256.1	2255.1	2256.4	2258.0
10°	2095.2	2091.1	2089.4	2088.1	2087.3	2086.9	2087.0	2089.5	2095.3	2090.6	2092.7
12.5°	1834.0	1843.3	1833.6	1832.8	1832.2	1832.0	1832.1	1832.8	1840.6	1835.4	1837.4
15°	1529.7	1536.7	1530.7	1530.9	1530.9	1531.1	1531.6	1532.5	1539.6	1534.7	1536.6
17.5°	1212.5	1217.1	1211.6	1211.3	1210.6	1210.3	1210.3	1210.7	1216.9	1225.7	1217.0
20°	923.2	926.4	924.1	924.8	924.6	924.4	924.5	924.8	929.1	936.6	928.4
22.5°	676.9	678.5	686.0	678.0	677.8	677.5	677.3	677.4	680.2	686.1	680.5
25°	508.8	509.2	513.5	509.2	509.3	509.2	509.2	509.1	510.4	513.9	510.9
27.5°	396.5	397.2	401.8	398.2	398.4	398.3	398.4	398.9	400.5	404.1	401.3
30°	274.1	274.5	279.1	275.9	276.5	276.3	276.2	276.3	277.3	280.8	277.8
32.5°	152.8	153.2	157.0	154.5	155.1	155.2	155.3	155.7	156.7	160.1	157.4
35°	54.4	54.7	57.1	55.6	55.9	55.9	55.9	55.9	56.3	58.5	56.6
37.5°	16.1	16.0	16.1	16.0	16.0	16.1	16.2	16.2	16.2	16.4	16.3
40°	12.0	12.0	12.1	12.1	12.1	12.1	12.1	12.1	12.2	12.3	12.2
42.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.1	9.1
45°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	8.0	8.0	8.0	8.0
47.5°	7.1	7.1	7.1	7.1	7.1	7.1	7.2	7.2	7.2	7.2	7.2
50°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.9	6.9	6.9
52.5°	6.4	6.4	6.4	6.4	6.4	6.5	6.5	6.5	6.5	6.5	6.5
55°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
57.5°	5.6	5.6	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
60°	5.2	5.2	5.2	5.2	5.2	5.2	5.3	5.3	5.3	5.3	5.3
62.5°	4.9	4.9	4.9	4.9	4.9	5.0	5.0	5.0	5.0	5.0	5.0
65°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.6	4.6	4.6	4.6
67.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.2	4.2	4.2	4.2
70°	3.7	3.7	3.7	3.7	3.7	3.7	3.8	3.8	3.8	3.8	3.8
72.5°	3.0	3.0	3.1	3.1	3.1	3.1	3.1	3.1	3.2	3.2	3.2
75°	2.7	2.7	2.7	2.8	2.8	2.8	2.8	2.8	2.8	2.9	2.9
77.5°	2.5	2.5	2.5	2.6	2.6	2.6	2.6	2.6	2.6	2.7	2.7
80°	2.0	2.0	2.1	2.1	2.1	2.1	2.1	2.1	2.2	2.2	2.2
82.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
140°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
142.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
145°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
147.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
150°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
152.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
155°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
157.5°	2.2	2.2	2.2	2.2	2.3	2.3	2.3	2.3	2.3	2.3	2.2
160°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
167.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
170°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.3
172.5°	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.5	3.5	3.5	3.5
175°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
177.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0	2419.0
2.5°	2393.2	2393.4	2393.6	2393.8	2394.1	2394.3	2394.6	2394.8	2395.1	2395.4	2395.7
5°	2342.6	2342.9	2343.2	2343.4	2343.7	2344.1	2344.4	2344.9	2345.3	2345.8	2346.3
7.5°	2259.7	2260.1	2260.5	2260.9	2261.4	2262.0	2262.7	2263.5	2264.4	2265.5	2266.7
10°	2095.3	2097.8	2098.3	2099.0	2100.0	2101.3	2102.7	2104.5	2106.5	2108.8	2111.3
12.5°	1839.9	1842.9	1844.4	1845.7	1847.4	1849.5	1852.1	1855.0	1858.4	1862.2	1866.5
15°	1539.2	1542.3	1544.8	1545.9	1547.5	1549.4	1551.8	1554.7	1558.0	1561.8	1566.0
17.5°	1219.9	1223.1	1226.1	1227.6	1229.5	1231.9	1234.8	1238.1	1241.9	1246.2	1251.0
20°	930.4	932.8	935.3	936.4	937.7	939.3	941.3	943.8	946.6	949.9	953.6
22.5°	682.2	684.2	686.4	687.4	688.5	689.8	691.4	693.2	695.3	697.8	700.6
25°	511.9	513.1	514.4	515.1	515.8	516.6	517.5	518.6	519.9	521.3	523.0
27.5°	402.5	403.8	405.3	406.0	406.5	407.3	408.3	409.6	411.1	412.7	414.6
30°	278.7	279.8	281.0	282.0	282.8	283.8	285.0	286.4	288.1	290.0	292.0
32.5°	158.2	159.2	160.3	161.2	162.0	163.1	164.3	165.7	167.4	169.2	171.3
35°	57.0	57.4	58.0	58.4	58.9	59.5	60.2	61.1	62.1	63.2	64.5
37.5°	16.3	16.4	16.4	16.5	16.6	16.7	16.7	16.8	16.9	16.9	17.0
40°	12.2	12.2	12.3	12.3	12.3	12.4	12.4	12.4	12.5	12.5	12.6
42.5°	9.1	9.1	9.1	9.1	9.2	9.2	9.2	9.2	9.2	9.3	9.3
45°	8.0	8.0	8.0	8.0	8.1	8.1	8.1	8.1	8.1	8.1	8.2
47.5°	7.2	7.3	7.3	7.3	7.3	7.3	7.4	7.4	7.4	7.4	7.4
50°	6.9	6.9	6.9	7.0	7.0	7.0	7.0	7.0	7.0	7.1	7.1
52.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.6	6.6	6.6	6.6	6.6
55°	6.0	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.2	6.2
57.5°	5.7	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
60°	5.3	5.3	5.3	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
62.5°	5.0	5.0	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
65°	4.6	4.6	4.7	4.7	4.7	4.7	4.7	4.7	4.8	4.8	4.8
67.5°	4.2	4.2	4.3	4.3	4.3	4.3	4.3	4.3	4.4	4.4	4.4
70°	3.9	3.9	3.9	3.9	3.9	4.0	4.0	4.0	4.0	4.1	4.1
72.5°	3.2	3.3	3.3	3.3	3.3	3.4	3.4	3.4	3.4	3.5	3.5
75°	2.9	2.9	2.9	3.0	3.0	3.0	3.0	3.1	3.1	3.1	3.1
77.5°	2.7	2.7	2.7	2.8	2.8	2.8	2.8	2.9	2.9	2.9	2.9
80°	2.2	2.2	2.3	2.3	2.3	2.4	2.4	2.4	2.5	2.5	2.5
82.5°	0.6	0.6	0.6	0.6	0.6	0.7	0.7	0.7	0.8	0.8	0.8
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
140°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
142.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
145°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
147.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
150°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
152.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
155°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
157.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.2	2.2	2.2	2.2	2.2
160°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
167.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
170°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
172.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
175°	3.6	3.6	3.6	3.6	3.6	3.7	3.7	3.7	3.7	3.7	3.7
177.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
180°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6



TEST NUMBER: P979198
 CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2419.0	2419.0
2.5°	2396.1	2396.4
5°	2346.9	2350.5
7.5°	2268.1	2273.3
10°	2114.2	2121.0
12.5°	1871.1	1881.3
15°	1570.8	1577.5
17.5°	1256.2	1256.1
20°	957.8	958.9
22.5°	703.8	707.2
25°	524.9	525.8
27.5°	416.7	419.8
30°	294.3	297.2
32.5°	173.6	175.7
35°	66.0	67.8
37.5°	17.1	17.3
40°	12.7	12.8
42.5°	9.3	9.3
45°	8.2	8.2
47.5°	7.5	7.5
50°	7.1	7.1
52.5°	6.6	6.7
55°	6.2	6.2
57.5°	5.9	5.9
60°	5.4	5.4
62.5°	5.1	5.1
65°	4.8	4.8
67.5°	4.4	4.4
70°	4.1	4.1
72.5°	3.5	3.5
75°	3.2	3.2
77.5°	3.0	2.9
80°	2.6	2.6
82.5°	0.9	1.2
85°	0.1	0.2
87.5°	0.1	0.1
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



TEST NUMBER: P979198
CATALOG NUMBER: L820S10FL935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.1	0.1
135°	0.1	0.1
137.5°	0.2	0.2
140°	0.3	0.3
142.5°	0.5	0.5
145°	0.7	0.7
147.5°	1.0	1.0
150°	1.3	1.3
152.5°	1.6	1.6
155°	1.9	1.9
157.5°	2.2	2.2
160°	2.6	2.5
162.5°	2.8	2.8
165°	3.0	3.0
167.5°	3.1	3.1
170°	3.3	3.3
172.5°	3.5	3.5
175°	3.7	3.7
177.5°	3.7	3.7
180°	3.6	3.6

(END OF REPORT)